

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784565

Luminaire Tested: LER4DD35BD010-EC4DR6520359024-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P784565
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD35BD010-EC4DR6520359024-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2399.4 lumens
Efficiency: N/A
Efficacy: 77.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784565

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359024-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P784565

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359024-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	258118
5°	258336
10°	267425
15°	267868
20°	246615
25°	210129
30°	160858
35°	113642
40°	67079
45°	27226
50°	9876
55°	5505
60°	3147
65°	1732
70°	1821
75°	1435
80°	1447
85°	1254

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27226 cd/sqm



TEST NUMBER: P784565

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359024-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	227.5	9.5
10°-20°	656.2	27.3
20°-30°	787.3	32.8
30°-40°	529.1	22.0
40°-50°	158.4	6.6
50°-60°	28.0	1.2
60°-70°	7.9	0.3
70°-80°	3.9	0.2
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1670.9	69.6
0°-40°	2200.0	91.7
0°-60°	2386.3	99.5
0°-90°	2399.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2399.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2362	
5°	2355	227
15°	2368	656
25°	1743	787
35°	852	529
45°	176	158
55°	29	28
65°	7	8
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P784565

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359024-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2362.4
2.5°	2372.5
5°	2355.4
7.5°	2391.0
10°	2410.4
12.5°	2405.7
15°	2368.1
17.5°	2276.1
20°	2121.0
22.5°	1938.4
25°	1743.0
27.5°	1522.5
30°	1275.0
32.5°	1050.8
35°	852.0
37.5°	655.6
40°	470.3
42.5°	307.2
45°	176.2
47.5°	93.3
50°	58.1
52.5°	40.3
55°	28.9
57.5°	20.8
60°	14.4
62.5°	9.4
65°	6.7
67.5°	6.0
70°	5.7
72.5°	4.4
75°	3.4
77.5°	3.0
80°	2.3
82.5°	1.7
85°	1.0
87.5°	0.7
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)