

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784751

Luminaire Tested: LER4DD40BD010-EC4DR5040509040-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784751
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD40BD010-EC4DR5040509040-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3926.1 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784751

CATALOG NUMBER: LER4DD40BD010-EC4DR5040509040-4LBDP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P784751

CATALOG NUMBER: LER4DD40BD010-EC4DR5040509040-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	112	109	107	112	110	108	106		106	104	102			102	101	99			98
2	109	105	101	98	107	103	100	97		100	98	95			97	95	93			95
3	105	99	95	91	103	98	94	90		95	92	89			93	90	88			91
4	100	94	89	85	99	93	88	85		90	87	84			89	85	83			87
5	96	89	84	80	95	88	83	79		86	82	79			85	81	78			83
6	92	84	79	75	91	83	79	75		82	78	74			81	77	74			79
7	88	80	75	71	87	79	74	71		78	74	71			77	73	70			76
8	85	76	71	67	84	76	71	67		75	70	67			74	70	67			73
9	81	73	68	64	80	72	67	64		71	67	64			71	67	64			70
10	78	70	64	61	77	69	64	61		68	64	61			68	64	61			67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	691184
5°	683942
10°	672678
15°	612529
20°	509694
25°	361800
30°	191504
35°	78042
40°	28982
45°	13273
50°	5439
55°	2838
60°	1399
65°	414
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13273 cd/sqm



TEST NUMBER: P784751

CATALOG NUMBER: LER4DD40BD010-EC4DR5040509040-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	589.4	15.0
10°-20°	1489.6	37.9
20°-30°	1338.0	34.1
30°-40°	418.9	10.7
40°-50°	73.4	1.9
50°-60°	14.6	0.4
60°-70°	2.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3417.0	87.0
0°-40°	3836.0	97.7
0°-60°	3924.0	99.9
0°-90°	3926.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3926.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6326	
5°	6236	589
15°	5415	1490
25°	3001	1338
35°	585	419
45°	86	73
55°	15	15
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784751

CATALOG NUMBER: LER4DD40BD010-EC4DR5040509040-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6326.0
2.5°	6294.5
5°	6235.9
7.5°	6146.3
10°	6063.1
12.5°	5796.4
15°	5415.1
17.5°	4930.8
20°	4383.6
22.5°	3750.5
25°	3001.1
27.5°	2206.4
30°	1517.9
32.5°	988.3
35°	585.1
37.5°	336.0
40°	203.2
42.5°	132.3
45°	85.9
47.5°	52.3
50°	32.0
52.5°	21.9
55°	14.9
57.5°	10.1
60°	6.4
62.5°	3.7
65°	1.6
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)