

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784772

Luminaire Tested: LER4DD40BD010-EC4DR5540509040-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784772
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD40BD010-EC4DR5540509040-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3208.4 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784772

CATALOG NUMBER: LER4DD40BD010-EC4DR5540509040-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P784772

CATALOG NUMBER: LER4DD40BD010-EC4DR5540509040-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75		
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70		
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65		
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61		
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57		
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54		
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	393087
5°	377479
10°	376052
15°	365249
20°	327494
25°	270660
30°	204448
35°	148242
40°	94877
45°	43327
50°	14176
55°	6115
60°	2622
65°	336
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 43327 cd/sqm



TEST NUMBER: P784772

CATALOG NUMBER: LER4DD40BD010-EC4DR5540509040-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	327.5	10.2
10°-20°	893.8	27.9
20°-30°	1018.6	31.7
30°-40°	693.4	21.6
40°-50°	238.9	7.4
50°-60°	33.0	1.0
60°-70°	3.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2239.8	69.8
0°-40°	2933.2	91.4
0°-60°	3205.2	99.9
0°-90°	3208.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3208.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3598	
5°	3442	327
15°	3229	894
25°	2245	1019
35°	1111	693
45°	280	239
55°	32	33
65°	1	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784772

CATALOG NUMBER: LER4DD40BD010-EC4DR5540509040-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3597.7
2.5°	3515.2
5°	3441.7
7.5°	3405.6
10°	3389.5
12.5°	3336.0
15°	3229.0
17.5°	3059.2
20°	2816.6
22.5°	2536.7
25°	2245.1
27.5°	1941.5
30°	1620.5
32.5°	1348.6
35°	1111.4
37.5°	885.8
40°	665.2
42.5°	461.0
45°	280.4
47.5°	151.1
50°	83.4
52.5°	49.5
55°	32.1
57.5°	20.5
60°	12.0
62.5°	5.3
65°	1.3
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)