

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784584

Luminaire Tested: LER4DD35BD010-EC4DR6520359050-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P784584
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD35BD010-EC4DR6520359050-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2222.1 lumens
Efficiency: N/A
Efficacy: 72.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784584

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359050-4LBDP1B

Luminous Intensity Polar Plot



TEST NUMBER: P784584

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359050-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	239041
5°	239241
10°	247665
15°	248073
20°	228395
25°	194601
30°	148974
35°	105252
40°	62130
45°	25217
50°	9145
55°	5086
60°	2928
65°	1603
70°	1693
75°	1309
80°	1384
85°	1128

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25217 cd/sqm



TEST NUMBER: P784584

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359050-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	210.7	9.5
10°-20°	607.7	27.3
20°-30°	729.1	32.8
30°-40°	490.0	22.1
40°-50°	146.7	6.6
50°-60°	25.9	1.2
60°-70°	7.4	0.3
70°-80°	3.6	0.2
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1547.4	69.6
0°-40°	2037.4	91.7
0°-60°	2210.0	99.5
0°-90°	2222.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2222.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2188	
5°	2181	211
15°	2193	608
25°	1614	729
35°	789	490
45°	163	147
55°	27	26
65°	6	7
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P784584

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359050-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2187.8
2.5°	2197.1
5°	2181.3
7.5°	2214.2
10°	2232.3
12.5°	2227.9
15°	2193.1
17.5°	2107.9
20°	1964.3
22.5°	1795.1
25°	1614.2
27.5°	1409.9
30°	1180.8
32.5°	973.1
35°	789.1
37.5°	607.2
40°	435.6
42.5°	284.5
45°	163.2
47.5°	86.4
50°	53.8
52.5°	37.3
55°	26.7
57.5°	19.3
60°	13.4
62.5°	8.7
65°	6.2
67.5°	5.6
70°	5.3
72.5°	4.0
75°	3.1
77.5°	2.8
80°	2.2
82.5°	1.6
85°	0.9
87.5°	0.6
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)