

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784586

Luminaire Tested: LER4DD35BD010-EC4DR6520359050-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P784586
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD35BD010-EC4DR6520359050-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3132.3 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784586

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359050-4LBDP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P784586

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359050-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	336949
5°	337227
10°	349104
15°	349684
20°	321936
25°	274313
30°	209999
35°	148362
40°	87575
45°	35555
50°	12884
55°	7181
60°	4108
65°	2275
70°	2396
75°	1857
80°	1951
85°	1630

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 35555 cd/sqm



TEST NUMBER: P784586

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359050-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	297.0	9.5
10°-20°	856.6	27.3
20°-30°	1027.7	32.8
30°-40°	690.7	22.1
40°-50°	206.8	6.6
50°-60°	36.5	1.2
60°-70°	10.4	0.3
70°-80°	5.1	0.2
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2181.3	69.6
0°-40°	2872.0	91.7
0°-60°	3115.2	99.5
0°-90°	3132.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3132.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3084	
5°	3075	297
15°	3091	857
25°	2275	1028
35°	1112	691
45°	230	207
55°	38	36
65°	9	10
75°	4	5
85°	1	2
90°	0	



TEST NUMBER: P784586

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359050-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3083.9
2.5°	3097.1
5°	3074.7
7.5°	3121.2
10°	3146.6
12.5°	3140.5
15°	3091.4
17.5°	2971.3
20°	2768.8
22.5°	2530.4
25°	2275.4
27.5°	1987.5
30°	1664.5
32.5°	1371.7
35°	1112.3
37.5°	855.9
40°	614.0
42.5°	401.0
45°	230.1
47.5°	121.8
50°	75.8
52.5°	52.6
55°	37.7
57.5°	27.2
60°	18.8
62.5°	12.3
65°	8.8
67.5°	7.9
70°	7.5
72.5°	5.7
75°	4.4
77.5°	3.9
80°	3.1
82.5°	2.2
85°	1.3
87.5°	0.9
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)