

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784792

Luminaire Tested: LER4DD40BD010-EC4DR6040509035-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P784792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD40BD010-EC4DR6040509035-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3002.1 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784792

CATALOG NUMBER: LER4DD40BD010-EC4DR6040509035-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P784792

CATALOG NUMBER: LER4DD40BD010-EC4DR6040509035-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	96	90	86	100	94	89	86	91	88	84		89	86	83		87
4	97	89	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	78	73	69	77	72	68		75	71	68		74
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		71
8	80	71	65	61	79	70	65	61	69	64	60		68	64	60		67
9	77	67	61	57	75	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	389558
5°	399141
10°	403955
15°	384829
20°	339296
25°	274433
30°	185637
35°	93021
40°	15090
45°	14772
50°	15060
55°	15296
60°	15712
65°	16081
70°	16452
75°	16633
80°	16045
85°	13414

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 16633 cd/sqm



TEST NUMBER: P784792

CATALOG NUMBER: LER4DD40BD010-EC4DR6040509035-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	347.8	11.6
10°-20°	941.0	31.3
20°-30°	1012.5	33.7
30°-40°	440.1	14.7
40°-50°	73.9	2.5
50°-60°	71.9	2.4
60°-70°	61.5	2.0
70°-80°	41.1	1.4
80°-90°	12.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2301.3	76.7
0°-40°	2741.4	91.3
0°-60°	2887.2	96.2
0°-90°	3002.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3002.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3565	
5°	3639	348
15°	3402	941
25°	2276	1012
35°	697	440
45°	96	74
55°	80	72
65°	62	61
75°	39	41
85°	11	12
90°	0	



TEST NUMBER: P784792

CATALOG NUMBER: LER4DD40BD010-EC4DR6040509035-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3565.4
2.5°	3665.6
5°	3639.2
7.5°	3647.5
10°	3641.0
12.5°	3565.9
15°	3402.1
17.5°	3182.1
20°	2918.1
22.5°	2635.5
25°	2276.4
27.5°	1820.7
30°	1471.4
32.5°	1134.0
35°	697.4
37.5°	298.4
40°	105.8
42.5°	97.4
45°	95.6
47.5°	92.3
50°	88.6
52.5°	84.4
55°	80.3
57.5°	76.1
60°	71.9
62.5°	67.3
65°	62.2
67.5°	57.1
70°	51.5
72.5°	45.5
75°	39.4
77.5°	32.5
80°	25.5
82.5°	18.1
85°	10.7
87.5°	3.7
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)