

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784793

Luminaire Tested: LER4DD40BD010-EC4DR6040509035-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P784793
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD40BD010-EC4DR6040509035-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3812.3 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784793

CATALOG NUMBER: LER4DD40BD010-EC4DR6040509035-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P784793

CATALOG NUMBER: LER4DD40BD010-EC4DR6040509035-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	96	90	86	100	94	89	86	91	88	84		89	86	83		87
4	97	89	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	78	73	69	77	72	68		75	71	68		74
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		71
8	80	71	65	61	79	70	65	61	69	64	60		68	64	60		67
9	77	67	61	57	75	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	494689
5°	506855
10°	512982
15°	488680
20°	430872
25°	348503
30°	235724
35°	118124
40°	19155
45°	18758
50°	19123
55°	19411
60°	19951
65°	20424
70°	20892
75°	21150
80°	20386
85°	17049

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 21150 cd/sqm

TEST NUMBER: P784793

CATALOG NUMBER: LER4DD40BD010-EC4DR6040509035-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	441.7	11.6
10°-20°	1195.0	31.3
20°-30°	1285.7	33.7
30°-40°	558.9	14.7
40°-50°	93.9	2.5
50°-60°	91.2	2.4
60°-70°	78.1	2.0
70°-80°	52.2	1.4
80°-90°	15.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2922.4	76.7
0°-40°	3481.3	91.3
0°-60°	3666.4	96.2
0°-90°	3812.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3812.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4528	
5°	4621	442
15°	4320	1195
25°	2891	1286
35°	886	559
45°	121	94
55°	102	91
65°	79	78
75°	50	52
85°	14	16
90°	0	



TEST NUMBER: P784793

CATALOG NUMBER: LER4DD40BD010-EC4DR6040509035-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4527.6
2.5°	4654.9
5°	4621.3
7.5°	4631.9
10°	4623.7
12.5°	4528.2
15°	4320.2
17.5°	4040.9
20°	3705.7
22.5°	3346.8
25°	2890.8
27.5°	2312.1
30°	1868.4
32.5°	1440.1
35°	885.6
37.5°	378.9
40°	134.3
42.5°	123.7
45°	121.4
47.5°	117.3
50°	112.5
52.5°	107.2
55°	101.9
57.5°	96.6
60°	91.3
62.5°	85.4
65°	79.0
67.5°	72.5
70°	65.4
72.5°	57.7
75°	50.1
77.5°	41.2
80°	32.4
82.5°	23.0
85°	13.6
87.5°	4.7
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)