

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784804

Luminaire Tested: LER4DD40BD010-EC4DR6540509024-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P784804
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD40BD010-EC4DR6540509024-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2104.0 lumens
Efficiency: N/A
Efficacy: 59.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784804

CATALOG NUMBER: LER4DD40BD010-EC4DR6540509024-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P784804

CATALOG NUMBER: LER4DD40BD010-EC4DR6540509024-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	226345
5°	226529
10°	234507
15°	234895
20°	216256
25°	184258
30°	141063
35°	99650
40°	58821
45°	23888
50°	8652
55°	4819
60°	2775
65°	1525
70°	1597
75°	1224
80°	1321
85°	1128

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23888 cd/sqm



TEST NUMBER: P784804

CATALOG NUMBER: LER4DD40BD010-EC4DR6540509024-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.5	9.5
10°-20°	575.4	27.3
20°-30°	690.4	32.8
30°-40°	463.9	22.0
40°-50°	138.9	6.6
50°-60°	24.5	1.2
60°-70°	7.0	0.3
70°-80°	3.4	0.2
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1465.2	69.6
0°-40°	1929.2	91.7
0°-60°	2092.6	99.5
0°-90°	2104.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2104.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2072	
5°	2065	199
15°	2077	575
25°	1528	690
35°	747	464
45°	155	139
55°	25	25
65°	6	7
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P784804

CATALOG NUMBER: LER4DD40BD010-EC4DR6540509024-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2071.6
2.5°	2080.4
5°	2065.4
7.5°	2096.6
10°	2113.7
12.5°	2109.6
15°	2076.6
17.5°	1995.9
20°	1859.9
22.5°	1699.8
25°	1528.4
27.5°	1335.0
30°	1118.1
32.5°	921.4
35°	747.1
37.5°	574.9
40°	412.4
42.5°	269.4
45°	154.6
47.5°	81.8
50°	50.9
52.5°	35.3
55°	25.3
57.5°	18.3
60°	12.7
62.5°	8.2
65°	5.9
67.5°	5.3
70°	5.0
72.5°	3.8
75°	2.9
77.5°	2.6
80°	2.1
82.5°	1.5
85°	0.9
87.5°	0.6
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)