

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784628

Luminaire Tested: LER4DD40BD010-EC4DR2540509040-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784628
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD40BD010-EC4DR2540509040-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2801.7 lumens
Efficiency: N/A
Efficacy: 79.6 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784628

CATALOG NUMBER: LER4DD40BD010-EC4DR2540509040-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P784628

CATALOG NUMBER: LER4DD40BD010-EC4DR2540509040-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	97	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	93	89	86	98	93	89	86	91	87	85		89	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1161048
5°	1081371
10°	771376
15°	454304
20°	282683
25°	155131
30°	70942
35°	26863
40°	12166
45°	7309
50°	3043
55°	1962
60°	1377
65°	931
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7309 cd/sqm



TEST NUMBER: P784628

CATALOG NUMBER: LER4DD40BD010-EC4DR2540509040-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	847.3	30.2
10°-20°	1147.7	41.0
20°-30°	607.3	21.7
30°-40°	149.9	5.4
40°-50°	36.6	1.3
50°-60°	9.6	0.3
60°-70°	3.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2602.3	92.9
0°-40°	2752.2	98.2
0°-60°	2798.5	99.9
0°-90°	2801.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2801.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10626	
5°	9860	847
15°	4016	1148
25°	1287	607
35°	201	150
45°	47	37
55°	10	10
65°	4	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784628

CATALOG NUMBER: LER4DD40BD010-EC4DR2540509040-4LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	10626.4
2.5°	10451.8
5°	9859.5
7.5°	8669.6
10°	6952.7
12.5°	5255.8
15°	4016.3
17.5°	3130.2
20°	2431.2
22.5°	1823.3
25°	1286.8
27.5°	862.9
30°	562.3
32.5°	342.1
35°	201.4
37.5°	123.3
40°	85.3
42.5°	65.2
45°	47.3
47.5°	28.6
50°	17.9
52.5°	13.0
55°	10.3
57.5°	8.0
60°	6.3
62.5°	4.9
65°	3.6
67.5°	1.3
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)