

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784810

Luminaire Tested: LER4DD40BD010-EC4DR6540509027-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P784810
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD40BD010-EC4DR6540509027-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3359.7 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784810

CATALOG NUMBER: LER4DD40BD010-EC4DR6540509027-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P784810

CATALOG NUMBER: LER4DD40BD010-EC4DR6540509027-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	361413
5°	361718
10°	374455
15°	375067
20°	345319
25°	294229
30°	225240
35°	159126
40°	93936
45°	38135
50°	13819
55°	7696
60°	4414
65°	2430
70°	2556
75°	1984
80°	2076
85°	1755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 38135 cd/sqm



TEST NUMBER: P784810

CATALOG NUMBER: LER4DD40BD010-EC4DR6540509027-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	318.5	9.5
10°-20°	918.8	27.3
20°-30°	1102.4	32.8
30°-40°	740.8	22.1
40°-50°	221.8	6.6
50°-60°	39.1	1.2
60°-70°	11.1	0.3
70°-80°	5.4	0.2
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2339.6	69.6
0°-40°	3080.5	91.7
0°-60°	3341.3	99.5
0°-90°	3359.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3359.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3308	
5°	3298	319
15°	3316	919
25°	2441	1102
35°	1193	741
45°	247	222
55°	40	39
65°	9	11
75°	5	5
85°	1	2
90°	0	



TEST NUMBER: P784810

CATALOG NUMBER: LER4DD40BD010-EC4DR6540509027-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3307.8
2.5°	3321.9
5°	3298.0
7.5°	3347.8
10°	3375.1
12.5°	3368.5
15°	3315.8
17.5°	3187.0
20°	2969.9
22.5°	2714.1
25°	2440.6
27.5°	2131.7
30°	1785.3
32.5°	1471.3
35°	1193.0
37.5°	918.0
40°	658.6
42.5°	430.1
45°	246.8
47.5°	130.7
50°	81.3
52.5°	56.4
55°	40.4
57.5°	29.1
60°	20.2
62.5°	13.2
65°	9.4
67.5°	8.5
70°	8.0
72.5°	6.1
75°	4.7
77.5°	4.2
80°	3.3
82.5°	2.4
85°	1.4
87.5°	0.9
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)