

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784669

Luminaire Tested: LER4DD40BD010-EC4DR3540509030-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784669
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD40BD010-EC4DR3540509030-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3593.2 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784669

CATALOG NUMBER: LER4DD40BD010-EC4DR3540509030-4LBDP1H

Luminous Intensity Polar Plot



TEST NUMBER: P784669

CATALOG NUMBER: LER4DD40BD010-EC4DR3540509030-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108	112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101	108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94	105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89	101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85	98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81	94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78	91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74	88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72	86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69	83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1080239
5°	1054851
10°	950710
15°	737895
20°	418524
25°	162823
30°	60748
35°	33292
40°	21765
45°	13242
50°	8431
55°	5962
60°	4349
65°	2379
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13242 cd/sqm



TEST NUMBER: P784669

CATALOG NUMBER: LER4DD40BD010-EC4DR3540509030-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	884.5	24.6
10°-20°	1727.0	48.1
20°-30°	704.4	19.6
30°-40°	168.6	4.7
40°-50°	70.2	2.0
50°-60°	29.1	0.8
60°-70°	9.1	0.3
70°-80°	0.2	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3315.9	92.3
0°-40°	3484.5	97.0
0°-60°	3583.8	99.7
0°-90°	3593.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3593.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9887	
5°	9618	885
15°	6523	1727
25°	1351	704
35°	250	169
45°	86	70
55°	31	29
65°	9	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784669

CATALOG NUMBER: LER4DD40BD010-EC4DR3540509030-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	9886.8
2.5°	9827.5
5°	9617.7
7.5°	9199.3
10°	8569.1
12.5°	7681.6
15°	6523.4
17.5°	5107.0
20°	3599.5
22.5°	2295.3
25°	1350.6
27.5°	763.5
30°	481.5
32.5°	338.1
35°	249.6
37.5°	193.0
40°	152.6
42.5°	117.5
45°	85.7
47.5°	64.2
50°	49.6
52.5°	39.4
55°	31.3
57.5°	25.3
60°	19.9
62.5°	14.6
65°	9.2
67.5°	3.2
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)