

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784674

Luminaire Tested: LER4DD40BD010-EC4DR3540509035-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784674
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD40BD010-EC4DR3540509035-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3812.7 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784674

CATALOG NUMBER: LER4DD40BD010-EC4DR3540509035-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P784674

CATALOG NUMBER: LER4DD40BD010-EC4DR3540509035-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108	112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101	108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94	105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89	101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85	98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81	94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78	91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74	88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72	86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69	83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1146200
5°	1119265
10°	1008757
15°	782960
20°	444081
25°	172769
30°	64457
35°	35333
40°	23092
45°	14061
50°	8941
55°	6324
60°	4633
65°	2508
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14061 cd/sqm



TEST NUMBER: P784674

CATALOG NUMBER: LER4DD40BD010-EC4DR3540509035-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	938.6	24.6
10°-20°	1832.5	48.1
20°-30°	747.4	19.6
30°-40°	178.9	4.7
40°-50°	74.5	2.0
50°-60°	30.9	0.8
60°-70°	9.6	0.3
70°-80°	0.2	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3518.4	92.3
0°-40°	3697.2	97.0
0°-60°	3802.7	99.7
0°-90°	3812.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3812.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10490	
5°	10205	939
15°	6922	1832
25°	1433	747
35°	265	179
45°	91	75
55°	33	31
65°	10	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784674

CATALOG NUMBER: LER4DD40BD010-EC4DR3540509035-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	10490.5
2.5°	10427.5
5°	10205.0
7.5°	9761.1
10°	9092.3
12.5°	8150.6
15°	6921.8
17.5°	5418.9
20°	3819.3
22.5°	2435.4
25°	1433.1
27.5°	810.1
30°	510.9
32.5°	358.7
35°	264.9
37.5°	204.8
40°	161.9
42.5°	124.7
45°	91.0
47.5°	68.1
50°	52.6
52.5°	41.8
55°	33.2
57.5°	26.9
60°	21.2
62.5°	15.4
65°	9.7
67.5°	3.4
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)