

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784843

Luminaire Tested: LER4DD40BD010-EC4DR7040509035-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P784843
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD40BD010-EC4DR7040509035-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2997.3 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784843

CATALOG NUMBER: LER4DD40BD010-EC4DR7040509035-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P784843

CATALOG NUMBER: LER4DD40BD010-EC4DR7040509035-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	74	69	87	79	73	69	77	72	68		75	71	67		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	77	66	60	56	75	66	60	56	65	59	55		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	70	59	53	49	69	59	53	49	58	53	49		57	52	49		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	368198
5°	357255
10°	347295
15°	342739
20°	320041
25°	240437
30°	169967
35°	60209
40°	31664
45°	33716
50°	34914
55°	35565
60°	35794
65°	35031
70°	33064
75°	30648
80°	27182
85°	22064

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 57.5°

Luminance: 35810 cd/sqm

TEST NUMBER: P784843

CATALOG NUMBER: LER4DD40BD010-EC4DR7040509035-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	307.2	10.3
10°-20°	842.7	28.1
20°-30°	928.1	31.0
30°-40°	354.6	11.8
40°-50°	167.4	5.6
50°-60°	166.5	5.6
60°-70°	133.3	4.4
70°-80°	76.6	2.6
80°-90°	20.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2078.1	69.3
0°-40°	2432.7	81.2
0°-60°	2766.6	92.3
0°-90°	2997.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2997.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3370	
5°	3257	307
15°	3030	843
25°	1994	928
35°	451	355
45°	218	167
55°	187	166
65°	136	133
75°	73	77
85°	18	21
90°	0	



TEST NUMBER: P784843

CATALOG NUMBER: LER4DD40BD010-EC4DR7040509035-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3369.9
2.5°	3334.6
5°	3257.3
7.5°	3192.7
10°	3130.3
12.5°	3077.5
15°	3030.0
17.5°	2915.3
20°	2752.5
22.5°	2401.5
25°	1994.4
27.5°	1736.1
30°	1347.2
32.5°	870.2
35°	451.4
37.5°	243.8
40°	222.0
42.5°	220.4
45°	218.2
47.5°	213.4
50°	205.4
52.5°	196.3
55°	186.7
57.5°	176.1
60°	163.8
62.5°	149.9
65°	135.5
67.5°	119.5
70°	103.5
72.5°	87.5
75°	72.6
77.5°	57.1
80°	43.2
82.5°	30.4
85°	17.6
87.5°	6.9
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)