

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784733

Luminaire Tested: LER4DD40BD010-EC4DR5040509024-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784733
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD40BD010-EC4DR5040509024-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3344.0 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784733

CATALOG NUMBER: LER4DD40BD010-EC4DR5040509024-4LBDP1H

Luminous Intensity Polar Plot



TEST NUMBER: P784733

CATALOG NUMBER: LER4DD40BD010-EC4DR5040509024-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	106	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	90	87	84		89	85	83		87
5	96	89	84	80	95	88	83	79	86	82	79		85	81	78		83
6	92	84	79	75	91	83	79	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	67	84	76	71	67	75	70	67		74	70	67		73
9	81	73	68	64	80	72	67	64	71	67	64		71	67	64		70
10	78	70	64	61	77	69	64	61	68	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	588697
5°	582522
10°	572938
15°	521698
20°	434116
25°	308153
30°	163104
35°	66465
40°	24689
45°	11295
50°	4640
55°	2419
60°	1202
65°	362
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11295 cd/sqm



TEST NUMBER: P784733

CATALOG NUMBER: LER4DD40BD010-EC4DR5040509024-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	502.0	15.0
10°-20°	1268.7	37.9
20°-30°	1139.6	34.1
30°-40°	356.8	10.7
40°-50°	62.5	1.9
50°-60°	12.4	0.4
60°-70°	1.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2910.4	87.0
0°-40°	3267.2	97.7
0°-60°	3342.1	99.9
0°-90°	3344.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3344.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5388	
5°	5311	502
15°	4612	1269
25°	2556	1140
35°	498	357
45°	73	62
55°	13	12
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784733

CATALOG NUMBER: LER4DD40BD010-EC4DR5040509024-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	5388.0
2.5°	5361.2
5°	5311.2
7.5°	5234.9
10°	5164.1
12.5°	4936.9
15°	4612.1
17.5°	4199.7
20°	3733.6
22.5°	3194.4
25°	2556.1
27.5°	1879.3
30°	1292.8
32.5°	841.7
35°	498.3
37.5°	286.2
40°	173.1
42.5°	112.7
45°	73.1
47.5°	44.5
50°	27.3
52.5°	18.6
55°	12.7
57.5°	8.6
60°	5.5
62.5°	3.2
65°	1.4
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)