

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784906

Luminaire Tested: LER4DD45BD010-EC4DR3540509027-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784906
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD45BD010-EC4DR3540509027-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4011.6 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784906

CATALOG NUMBER: LER4DD45BD010-EC4DR3540509027-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P784906

CATALOG NUMBER: LER4DD45BD010-EC4DR3540509027-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96			
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92			
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88			
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84			
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81			
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78			
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75			
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72			
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70			
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1205998
5°	1177669
10°	1061390
15°	823806
20°	467254
25°	181786
30°	67813
35°	37174
40°	24290
45°	14787
50°	9417
55°	6648
60°	4873
65°	2637
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14787 cd/sqm



TEST NUMBER: P784906

CATALOG NUMBER: LER4DD45BD010-EC4DR3540509027-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	987.5	24.6
10°-20°	1928.1	48.1
20°-30°	786.4	19.6
30°-40°	188.2	4.7
40°-50°	78.4	2.0
50°-60°	32.5	0.8
60°-70°	10.2	0.3
70°-80°	0.2	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3702.0	92.3
0°-40°	3890.1	97.0
0°-60°	4001.0	99.7
0°-90°	4011.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4011.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11038	
5°	10738	988
15°	7283	1928
25°	1508	786
35°	279	188
45°	96	78
55°	35	32
65°	10	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784906

CATALOG NUMBER: LER4DD45BD010-EC4DR3540509027-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	11037.8
2.5°	10971.6
5°	10737.5
7.5°	10270.3
10°	9566.7
12.5°	8575.9
15°	7282.9
17.5°	5701.6
20°	4018.6
22.5°	2562.5
25°	1507.9
27.5°	852.4
30°	537.5
32.5°	377.4
35°	278.7
37.5°	215.5
40°	170.3
42.5°	131.2
45°	95.7
47.5°	71.6
50°	55.4
52.5°	43.9
55°	34.9
57.5°	28.3
60°	22.3
62.5°	16.3
65°	10.2
67.5°	3.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)