

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784914

Luminaire Tested: LER4DD45BD010-EC4DR3540509035-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784914
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD45BD010-EC4DR3540509035-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4176.3 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784914

CATALOG NUMBER: LER4DD45BD010-EC4DR3540509035-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P784914

CATALOG NUMBER: LER4DD45BD010-EC4DR3540509035-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89		101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85		98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81		94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78		91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74		88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72		86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69		83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125537
5°	1226037
10°	1104981
15°	857638
20°	486439
25°	189249
30°	70601
35°	38694
40°	25288
45°	15390
50°	9808
55°	6915
60°	5070
65°	2766
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15390 cd/sqm



TEST NUMBER: P784914

CATALOG NUMBER: LER4DD45BD010-EC4DR3540509035-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1028.1	24.6
10°-20°	2007.3	48.1
20°-30°	818.6	19.6
30°-40°	195.9	4.7
40°-50°	81.6	2.0
50°-60°	33.8	0.8
60°-70°	10.6	0.3
70°-80°	0.2	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3854.0	92.3
0°-40°	4049.9	97.0
0°-60°	4165.3	99.7
0°-90°	4176.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4176.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11491	
5°	11178	###
15°	7582	2007
25°	1570	819
35°	290	196
45°	100	82
55°	36	34
65°	11	11
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784914

CATALOG NUMBER: LER4DD45BD010-EC4DR3540509035-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	11491.2
2.5°	11422.2
5°	11178.5
7.5°	10692.2
10°	9959.6
12.5°	8928.1
15°	7582.0
17.5°	5935.8
20°	4183.6
22.5°	2667.7
25°	1569.8
27.5°	887.4
30°	559.6
32.5°	392.9
35°	290.1
37.5°	224.3
40°	177.3
42.5°	136.6
45°	99.6
47.5°	74.6
50°	57.7
52.5°	45.7
55°	36.3
57.5°	29.5
60°	23.2
62.5°	16.9
65°	10.7
67.5°	3.8
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)