

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784764

Luminaire Tested: LER4DD40BD010-EC4DR5540509030-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784764
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD40BD010-EC4DR5540509030-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3033.2 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784764

CATALOG NUMBER: LER4DD40BD010-EC4DR5540509030-4LBDP1B

Luminous Intensity Polar Plot



TEST NUMBER: P784764

CATALOG NUMBER: LER4DD40BD010-EC4DR5540509030-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	371618
5°	356860
10°	355516
15°	345295
20°	309611
25°	255880
30°	193282
35°	140145
40°	89686
45°	40963
50°	13394
55°	5772
60°	2491
65°	336
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 40963 cd/sqm



TEST NUMBER: P784764

CATALOG NUMBER: LER4DD40BD010-EC4DR5540509030-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	309.6	10.2
10°-20°	845.0	27.9
20°-30°	962.9	31.7
30°-40°	655.5	21.6
40°-50°	225.9	7.4
50°-60°	31.2	1.0
60°-70°	3.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2117.5	69.8
0°-40°	2773.0	91.4
0°-60°	3030.1	99.9
0°-90°	3033.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3033.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3401	
5°	3254	310
15°	3053	845
25°	2122	963
35°	1051	656
45°	265	226
55°	30	31
65°	1	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784764

CATALOG NUMBER: LER4DD40BD010-EC4DR5540509030-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3401.2
2.5°	3323.2
5°	3253.7
7.5°	3219.5
10°	3204.4
12.5°	3153.8
15°	3052.6
17.5°	2892.1
20°	2662.8
22.5°	2398.1
25°	2122.5
27.5°	1835.5
30°	1532.0
32.5°	1274.9
35°	1050.7
37.5°	837.4
40°	628.8
42.5°	435.8
45°	265.1
47.5°	142.9
50°	78.8
52.5°	46.8
55°	30.3
57.5°	19.4
60°	11.4
62.5°	5.1
65°	1.3
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)