

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784786

Luminaire Tested: LER4DD40BD010-EC4DR6040509027-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P784786
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD40BD010-EC4DR6040509027-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3845.1 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784786

CATALOG NUMBER: LER4DD40BD010-EC4DR6040509027-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P784786

CATALOG NUMBER: LER4DD40BD010-EC4DR6040509027-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	96	90	86	100	94	89	86	91	88	84		89	86	83		87
4	97	89	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	78	73	69	77	72	68		75	71	68		74
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		71
8	80	71	65	61	79	70	65	61	69	64	60		68	64	60		67
9	77	67	61	57	75	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	498939
5°	511210
10°	517376
15°	492876
20°	434558
25°	351493
30°	237755
35°	119137
40°	19326
45°	18913
50°	19293
55°	19582
60°	20126
65°	20579
70°	21084
75°	21319
80°	20575
85°	17175

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 21319 cd/sqm



TEST NUMBER: P784786

CATALOG NUMBER: LER4DD40BD010-EC4DR6040509027-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	445.5	11.6
10°-20°	1205.2	31.3
20°-30°	1296.8	33.7
30°-40°	563.7	14.7
40°-50°	94.7	2.5
50°-60°	92.1	2.4
60°-70°	78.7	2.0
70°-80°	52.7	1.4
80°-90°	15.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2947.5	76.7
0°-40°	3511.1	91.3
0°-60°	3697.9	96.2
0°-90°	3845.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3845.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4566	
5°	4661	445
15°	4357	1205
25°	2916	1297
35°	893	564
45°	122	95
55°	103	92
65°	80	79
75°	50	53
85°	14	16
90°	0	



TEST NUMBER: P784786

CATALOG NUMBER: LER4DD40BD010-EC4DR6040509027-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4566.5
2.5°	4694.8
5°	4661.0
7.5°	4671.7
10°	4663.3
12.5°	4567.1
15°	4357.3
17.5°	4075.6
20°	3737.4
22.5°	3375.5
25°	2915.6
27.5°	2332.0
30°	1884.5
32.5°	1452.4
35°	893.2
37.5°	382.1
40°	135.5
42.5°	124.8
45°	122.4
47.5°	118.3
50°	113.5
52.5°	108.2
55°	102.8
57.5°	97.5
60°	92.1
62.5°	86.2
65°	79.6
67.5°	73.1
70°	66.0
72.5°	58.2
75°	50.5
77.5°	41.6
80°	32.7
82.5°	23.2
85°	13.7
87.5°	4.8
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)