

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785009

Luminaire Tested: LER4DD45BD010-EC4DR5540509035-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P785009
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD45BD010-EC4DR5540509035-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4258.2 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785009

CATALOG NUMBER: LER4DD45BD010-EC4DR5540509035-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P785009

CATALOG NUMBER: LER4DD45BD010-EC4DR5540509035-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106	111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96	106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87	100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80	95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74	91	83	77	73		81	76	73		79	75	72		78	74	71
6	88	79	73	68	86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	64	82	73	67	63		72	67	63		71	66	63		70	65	62
8	79	69	63	59	78	69	63	59		68	63	59		67	62	59		66	62	58
9	75	66	60	56	74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52	71	61	56	52		61	56	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	521698
5°	500988
10°	499092
15°	484755
20°	434651
25°	359220
30°	271352
35°	196753
40°	125914
45°	57512
50°	18800
55°	8115
60°	3496
65°	465
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 57512 cd/sqm

TEST NUMBER: P785009

CATALOG NUMBER: LER4DD45BD010-EC4DR5540509035-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	434.6	10.2
10°-20°	1186.2	27.9
20°-30°	1351.8	31.7
30°-40°	920.3	21.6
40°-50°	317.1	7.4
50°-60°	43.8	1.0
60°-70°	4.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2972.7	69.8
0°-40°	3893.0	91.4
0°-60°	4253.9	99.9
0°-90°	4258.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4258.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4775	
5°	4568	435
15°	4286	1186
25°	2980	1352
35°	1475	920
45°	372	317
55°	43	44
65°	2	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P785009

CATALOG NUMBER: LER4DD45BD010-EC4DR5540509035-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4774.8
2.5°	4665.4
5°	4567.8
7.5°	4519.8
10°	4498.5
12.5°	4427.5
15°	4285.5
17.5°	4060.1
20°	3738.2
22.5°	3366.6
25°	2979.7
27.5°	2576.8
30°	2150.8
32.5°	1789.8
35°	1475.1
37.5°	1175.7
40°	882.8
42.5°	611.8
45°	372.2
47.5°	200.6
50°	110.6
52.5°	65.7
55°	42.6
57.5°	27.2
60°	16.0
62.5°	7.1
65°	1.8
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)