

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784817

Luminaire Tested: LER4DD40BD010-EC4DR6540509035-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P784817
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD40BD010-EC4DR6540509035-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3331.1 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784817

CATALOG NUMBER: LER4DD40BD010-EC4DR6540509035-4LBDP1H

Luminous Intensity Polar Plot



TEST NUMBER: P784817

CATALOG NUMBER: LER4DD40BD010-EC4DR6540509035-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	358342
5°	358636
10°	371271
15°	371877
20°	342377
25°	291721
30°	223322
35°	157778
40°	93137
45°	37811
50°	13700
55°	7639
60°	4370
65°	2404
70°	2524
75°	1984
80°	2076
85°	1755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 37811 cd/sqm



TEST NUMBER: P784817

CATALOG NUMBER: LER4DD40BD010-EC4DR6540509035-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	315.8	9.5
10°-20°	911.0	27.3
20°-30°	1093.0	32.8
30°-40°	734.5	22.1
40°-50°	219.9	6.6
50°-60°	38.8	1.2
60°-70°	11.0	0.3
70°-80°	5.4	0.2
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2319.7	69.6
0°-40°	3054.3	91.7
0°-60°	3313.0	99.5
0°-90°	3331.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3331.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3280	
5°	3270	316
15°	3288	911
25°	2420	1093
35°	1183	735
45°	245	220
55°	40	39
65°	9	11
75°	5	5
85°	1	2
90°	0	



TEST NUMBER: P784817

CATALOG NUMBER: LER4DD40BD010-EC4DR6540509035-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3279.7
2.5°	3293.7
5°	3269.9
7.5°	3319.3
10°	3346.4
12.5°	3339.8
15°	3287.6
17.5°	3159.9
20°	2944.6
22.5°	2691.1
25°	2419.8
27.5°	2113.6
30°	1770.1
32.5°	1458.8
35°	1182.9
37.5°	910.2
40°	653.0
42.5°	426.5
45°	244.7
47.5°	129.6
50°	80.6
52.5°	55.9
55°	40.1
57.5°	28.9
60°	20.0
62.5°	13.0
65°	9.3
67.5°	8.4
70°	7.9
72.5°	6.1
75°	4.7
77.5°	4.2
80°	3.3
82.5°	2.3
85°	1.4
87.5°	0.9
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)