

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785045

Luminaire Tested: LER4DD45BD010-EC4DR6540509024-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P785045
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD45BD010-EC4DR6540509024-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3094.1 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785045

CATALOG NUMBER: LER4DD45BD010-EC4DR6540509024-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P785045

CATALOG NUMBER: LER4DD45BD010-EC4DR6540509024-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	332841
5°	333114
10°	344843
15°	345419
20°	318018
25°	270961
30°	207438
35°	146548
40°	86505
45°	35122
50°	12731
55°	7086
60°	4065
65°	2249
70°	2364
75°	1815
80°	1888
85°	1630

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 35122 cd/sqm



TEST NUMBER: P785045

CATALOG NUMBER: LER4DD45BD010-EC4DR6540509024-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.3	9.5
10°-20°	846.1	27.3
20°-30°	1015.2	32.8
30°-40°	682.3	22.1
40°-50°	204.2	6.6
50°-60°	36.0	1.2
60°-70°	10.3	0.3
70°-80°	5.0	0.2
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2154.7	69.6
0°-40°	2836.9	91.7
0°-60°	3077.2	99.5
0°-90°	3094.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3094.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3046	
5°	3037	293
15°	3054	846
25°	2248	1015
35°	1099	682
45°	227	204
55°	37	36
65°	9	10
75°	4	5
85°	1	2
90°	0	



TEST NUMBER: P785045

CATALOG NUMBER: LER4DD45BD010-EC4DR6540509024-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3046.3
2.5°	3059.3
5°	3037.2
7.5°	3083.1
10°	3108.2
12.5°	3102.2
15°	3053.7
17.5°	2935.1
20°	2735.1
22.5°	2499.6
25°	2247.6
27.5°	1963.2
30°	1644.2
32.5°	1355.0
35°	1098.7
37.5°	845.5
40°	606.5
42.5°	396.1
45°	227.3
47.5°	120.3
50°	74.9
52.5°	51.9
55°	37.2
57.5°	26.8
60°	18.6
62.5°	12.1
65°	8.7
67.5°	7.8
70°	7.4
72.5°	5.6
75°	4.3
77.5°	3.9
80°	3.0
82.5°	2.2
85°	1.3
87.5°	0.9
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)