

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785061

Luminaire Tested: LER4DD45BD010-EC4DR6540509040-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P785061
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD45BD010-EC4DR6540509040-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3819.5 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785061

CATALOG NUMBER: LER4DD45BD010-EC4DR6540509040-4LBDP1H

Luminous Intensity Polar Plot



TEST NUMBER: P785061

CATALOG NUMBER: LER4DD45BD010-EC4DR6540509040-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	410875
5°	411216
10°	425690
15°	426399
20°	392572
25°	334494
30°	256061
35°	180907
40°	106787
45°	43358
50°	15706
55°	8763
60°	5026
65°	2766
70°	2907
75°	2237
80°	2328
85°	2006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 43358 cd/sqm



TEST NUMBER: P785061

CATALOG NUMBER: LER4DD45BD010-EC4DR6540509040-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	362.1	9.5
10°-20°	1044.5	27.3
20°-30°	1253.2	32.8
30°-40°	842.2	22.1
40°-50°	252.1	6.6
50°-60°	44.5	1.2
60°-70°	12.7	0.3
70°-80°	6.2	0.2
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2659.8	69.6
0°-40°	3502.0	91.7
0°-60°	3798.7	99.5
0°-90°	3819.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3819.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3760	
5°	3749	362
15°	3770	1045
25°	2775	1253
35°	1356	842
45°	281	252
55°	46	44
65°	11	13
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P785061

CATALOG NUMBER: LER4DD45BD010-EC4DR6540509040-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3760.5
2.5°	3776.6
5°	3749.3
7.5°	3805.9
10°	3836.9
12.5°	3829.5
15°	3769.6
17.5°	3623.2
20°	3376.3
22.5°	3085.6
25°	2774.6
27.5°	2423.5
30°	2029.6
32.5°	1672.6
35°	1356.3
37.5°	1043.7
40°	748.7
42.5°	489.0
45°	280.6
47.5°	148.6
50°	92.4
52.5°	64.1
55°	46.0
57.5°	33.1
60°	23.0
62.5°	15.0
65°	10.7
67.5°	9.6
70°	9.1
72.5°	6.9
75°	5.3
77.5°	4.8
80°	3.7
82.5°	2.7
85°	1.6
87.5°	1.1
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)