

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785065

Luminaire Tested: LER4DD45BD010-EC4DR6540509050-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P785065
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD45BD010-EC4DR6540509050-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3846.8 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785065

CATALOG NUMBER: LER4DD45BD010-EC4DR6540509050-4LBDP1H

Luminous Intensity Polar Plot



TEST NUMBER: P785065

CATALOG NUMBER: LER4DD45BD010-EC4DR6540509050-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	413814
5°	414156
10°	428730
15°	429441
20°	395374
25°	336881
30°	257891
35°	182201
40°	107543
45°	43667
50°	15825
55°	8820
60°	5048
65°	2792
70°	2907
75°	2280
80°	2391
85°	2006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 43667 cd/sqm



TEST NUMBER: P785065

CATALOG NUMBER: LER4DD45BD010-EC4DR6540509050-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	364.7	9.5
10°-20°	1052.0	27.3
20°-30°	1262.2	32.8
30°-40°	848.2	22.1
40°-50°	253.9	6.6
50°-60°	44.8	1.2
60°-70°	12.7	0.3
70°-80°	6.2	0.2
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2678.8	69.6
0°-40°	3527.0	91.7
0°-60°	3825.8	99.5
0°-90°	3846.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3846.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3787	
5°	3776	365
15°	3796	1052
25°	2794	1262
35°	1366	848
45°	283	254
55°	46	45
65°	11	13
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P785065

CATALOG NUMBER: LER4DD45BD010-EC4DR6540509050-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3787.4
2.5°	3803.5
5°	3776.1
7.5°	3833.1
10°	3864.3
12.5°	3856.8
15°	3796.5
17.5°	3649.1
20°	3400.4
22.5°	3107.6
25°	2794.4
27.5°	2440.8
30°	2044.1
32.5°	1684.6
35°	1366.0
37.5°	1051.1
40°	754.0
42.5°	492.5
45°	282.6
47.5°	149.6
50°	93.1
52.5°	64.6
55°	46.3
57.5°	33.4
60°	23.1
62.5°	15.1
65°	10.8
67.5°	9.7
70°	9.1
72.5°	7.0
75°	5.4
77.5°	4.8
80°	3.8
82.5°	2.7
85°	1.6
87.5°	1.1
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)