

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785078

Luminaire Tested: LER4DD45BD010-EC4DR7040509030-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P785078
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD45BD010-EC4DR7040509030-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4367.6 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785078

CATALOG NUMBER: LER4DD45BD010-EC4DR7040509030-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P785078

CATALOG NUMBER: LER4DD45BD010-EC4DR7040509030-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	74	69	87	79	73	69	77	72	68		75	71	67		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	77	66	60	56	75	66	60	56	65	59	55		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	70	59	53	49	69	59	53	49	58	53	49		57	52	49		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	536514
5°	520565
10°	506059
15°	499414
20°	466359
25°	350348
30°	247671
35°	87726
40°	46126
45°	49137
50°	50875
55°	51832
60°	52161
65°	51060
70°	48174
75°	44621
80°	39640
85°	32218

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 57.5°

Luminance: 52180 cd/sqm

TEST NUMBER: P785078

CATALOG NUMBER: LER4DD45BD010-EC4DR7040509030-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	447.7	10.3
10°-20°	1228.0	28.1
20°-30°	1352.4	31.0
30°-40°	516.7	11.8
40°-50°	244.0	5.6
50°-60°	242.6	5.6
60°-70°	194.2	4.4
70°-80°	111.6	2.6
80°-90°	30.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3028.1	69.3
0°-40°	3544.8	81.2
0°-60°	4031.4	92.3
0°-90°	4367.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4367.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4910	
5°	4746	448
15°	4415	1228
25°	2906	1352
35°	658	517
45°	318	244
55°	272	243
65°	198	194
75°	106	112
85°	26	30
90°	0	



TEST NUMBER: P785078

CATALOG NUMBER: LER4DD45BD010-EC4DR7040509030-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4910.4
2.5°	4859.1
5°	4746.3
7.5°	4652.3
10°	4561.3
12.5°	4484.3
15°	4415.1
17.5°	4248.0
20°	4010.9
22.5°	3499.3
25°	2906.1
27.5°	2529.8
30°	1963.1
32.5°	1268.0
35°	657.7
37.5°	355.3
40°	323.4
42.5°	321.1
45°	318.0
47.5°	311.0
50°	299.3
52.5°	286.1
55°	272.1
57.5°	256.6
60°	238.7
62.5°	218.5
65°	197.5
67.5°	174.1
70°	150.8
72.5°	127.5
75°	105.7
77.5°	83.2
80°	63.0
82.5°	44.3
85°	25.7
87.5°	10.1
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)