

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785004

Luminaire Tested: LER4DD45BD010-EC4DR5540509030-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P785004
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD45BD010-EC4DR5540509030-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3322.4 lumens
Efficiency: N/A
Efficacy: 85.9 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785004

CATALOG NUMBER: LER4DD45BD010-EC4DR5540509030-4LBDP1B

Luminous Intensity Polar Plot



TEST NUMBER: P785004

CATALOG NUMBER: LER4DD45BD010-EC4DR5540509030-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	407062
5°	390893
10°	389421
15°	378234
20°	339145
25°	280280
30°	211715
35°	153510
40°	98243
45°	44872
50°	14669
55°	6324
60°	2732
65°	362
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 44872 cd/sqm



TEST NUMBER: P785004

CATALOG NUMBER: LER4DD45BD010-EC4DR5540509030-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	339.1	10.2
10°-20°	925.6	27.9
20°-30°	1054.8	31.7
30°-40°	718.0	21.6
40°-50°	247.4	7.4
50°-60°	34.2	1.0
60°-70°	3.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2319.5	69.8
0°-40°	3037.5	91.4
0°-60°	3319.1	99.9
0°-90°	3322.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3322.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3726	
5°	3564	339
15°	3344	926
25°	2325	1055
35°	1151	718
45°	290	247
55°	33	34
65°	1	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P785004

CATALOG NUMBER: LER4DD45BD010-EC4DR5540509030-4LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	3725.6
2.5°	3640.2
5°	3564.0
7.5°	3526.7
10°	3510.0
12.5°	3454.6
15°	3343.8
17.5°	3167.9
20°	2916.8
22.5°	2626.9
25°	2324.9
27.5°	2010.5
30°	1678.1
32.5°	1396.5
35°	1150.9
37.5°	917.3
40°	688.8
42.5°	477.4
45°	290.4
47.5°	156.5
50°	86.3
52.5°	51.2
55°	33.2
57.5°	21.2
60°	12.5
62.5°	5.5
65°	1.4
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)