

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785236

Luminaire Tested: LER4DD50D010-EC4DR5540509024-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P785236
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD50D010-EC4DR5540509024-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3343.6 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785236

CATALOG NUMBER: LER4DD50D010-EC4DR5540509024-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P785236

CATALOG NUMBER: LER4DD50D010-EC4DR5540509024-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74		91	83	77	73		81	76	73		79	75	72		78	74	71
6	88	79	73	68		86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	64		82	73	67	63		72	67	63		71	66	63		70	65	62
8	79	69	63	59		78	69	63	59		68	63	59		67	62	59		66	62	58
9	75	66	60	56		74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52		71	61	56	52		61	56	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	409640
5°	393372
10°	391896
15°	380632
20°	341296
25°	282065
30°	213065
35°	154484
40°	98871
45°	45150
50°	14771
55°	6381
60°	2732
65°	362
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 45150 cd/sqm



TEST NUMBER: P785236

CATALOG NUMBER: LER4DD50D010-EC4DR5540509024-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	341.3	10.2
10°-20°	931.4	27.9
20°-30°	1061.5	31.7
30°-40°	722.6	21.6
40°-50°	249.0	7.4
50°-60°	34.4	1.0
60°-70°	3.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2334.2	69.8
0°-40°	3056.8	91.4
0°-60°	3340.2	99.9
0°-90°	3343.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3343.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3749	
5°	3587	341
15°	3365	931
25°	2340	1061
35°	1158	723
45°	292	249
55°	34	34
65°	1	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P785236

CATALOG NUMBER: LER4DD50D010-EC4DR5540509024-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3749.2
2.5°	3663.3
5°	3586.6
7.5°	3549.0
10°	3532.3
12.5°	3476.5
15°	3365.0
17.5°	3188.0
20°	2935.3
22.5°	2643.5
25°	2339.7
27.5°	2023.3
30°	1688.8
32.5°	1405.4
35°	1158.2
37.5°	923.1
40°	693.2
42.5°	480.4
45°	292.2
47.5°	157.5
50°	86.9
52.5°	51.6
55°	33.5
57.5°	21.4
60°	12.5
62.5°	5.6
65°	1.4
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)