

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785033

Luminaire Tested: LER4DD45BD010-EC4DR6040509035-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P785033
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD45BD010-EC4DR6040509035-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4176.0 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785033

CATALOG NUMBER: LER4DD45BD010-EC4DR6040509035-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P785033

CATALOG NUMBER: LER4DD45BD010-EC4DR6040509035-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	96	90	86	100	94	89	86	91	88	84		89	86	83		87
4	97	89	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	78	73	69	77	72	68		75	71	68		74
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		71
8	80	71	65	61	79	70	65	61	69	64	60		68	64	60		67
9	77	67	61	57	75	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	541879
5°	555213
10°	561910
15°	535294
20°	471963
25°	381740
30°	258219
35°	129395
40°	20995
45°	20551
50°	20958
55°	21278
60°	21852
65°	22363
70°	22873
75°	23176
80°	22337
85°	18554

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 23176 cd/sqm



TEST NUMBER: P785033

CATALOG NUMBER: LER4DD45BD010-EC4DR6040509035-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	483.8	11.6
10°-20°	1309.0	31.3
20°-30°	1408.4	33.7
30°-40°	612.2	14.7
40°-50°	102.8	2.5
50°-60°	100.0	2.4
60°-70°	85.5	2.0
70°-80°	57.2	1.4
80°-90°	17.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3201.2	76.7
0°-40°	3813.4	91.3
0°-60°	4016.2	96.2
0°-90°	4176.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4176.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4960	
5°	5062	484
15°	4732	1309
25°	3166	1408
35°	970	612
45°	133	103
55°	112	100
65°	86	86
75°	55	57
85°	15	17
90°	0	



TEST NUMBER: P785033

CATALOG NUMBER: LER4DD45BD010-EC4DR6040509035-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4959.5
2.5°	5098.9
5°	5062.2
7.5°	5073.8
10°	5064.7
12.5°	4960.2
15°	4732.3
17.5°	4426.4
20°	4059.1
22.5°	3666.1
25°	3166.5
27.5°	2532.7
30°	2046.7
32.5°	1577.4
35°	970.1
37.5°	415.0
40°	147.2
42.5°	135.5
45°	133.0
47.5°	128.4
50°	123.3
52.5°	117.5
55°	111.7
57.5°	105.9
60°	100.0
62.5°	93.6
65°	86.5
67.5°	79.4
70°	71.6
72.5°	63.3
75°	54.9
77.5°	45.2
80°	35.5
82.5°	25.2
85°	14.8
87.5°	5.2
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)