

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785040

Luminaire Tested: LER4DD45BD010-EC4DR6040509050-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P785040
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD45BD010-EC4DR6040509050-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3466.8 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785040

CATALOG NUMBER: LER4DD45BD010-EC4DR6040509050-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P785040

CATALOG NUMBER: LER4DD45BD010-EC4DR6040509050-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86		
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80		
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62		
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	449859
5°	460922
10°	466485
15°	444395
20°	391816
25°	316917
30°	214364
35°	107413
40°	17429
45°	17059
50°	17389
55°	17658
60°	18159
65°	18563
70°	19008
75°	19208
80°	18562
85°	15420

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 19208 cd/sqm



TEST NUMBER: P785040

CATALOG NUMBER: LER4DD45BD010-EC4DR6040509050-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	401.6	11.6
10°-20°	1086.7	31.3
20°-30°	1169.2	33.7
30°-40°	508.2	14.7
40°-50°	85.4	2.5
50°-60°	83.0	2.4
60°-70°	71.0	2.0
70°-80°	47.5	1.4
80°-90°	14.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2657.5	76.7
0°-40°	3165.8	91.3
0°-60°	3334.1	96.2
0°-90°	3466.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3466.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4117	
5°	4202	402
15°	3929	1087
25°	2629	1169
35°	805	508
45°	110	85
55°	93	83
65°	72	71
75°	46	47
85°	12	14
90°	0	



TEST NUMBER: P785040

CATALOG NUMBER: LER4DD45BD010-EC4DR6040509050-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	4117.3
2.5°	4233.0
5°	4202.5
7.5°	4212.1
10°	4204.6
12.5°	4117.8
15°	3928.7
17.5°	3674.7
20°	3369.8
22.5°	3043.5
25°	2628.8
27.5°	2102.6
30°	1699.1
32.5°	1309.6
35°	805.3
37.5°	344.5
40°	122.2
42.5°	112.5
45°	110.4
47.5°	106.6
50°	102.3
52.5°	97.5
55°	92.7
57.5°	87.9
60°	83.1
62.5°	77.7
65°	71.8
67.5°	65.9
70°	59.5
72.5°	52.5
75°	45.5
77.5°	37.5
80°	29.5
82.5°	20.9
85°	12.3
87.5°	4.3
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)