

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785278

Luminaire Tested: LER4DD50D010-EC4DR6040509040-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P785278
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD50D010-EC4DR6040509040-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5390.3 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785278

CATALOG NUMBER: LER4DD50D010-EC4DR6040509040-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P785278

CATALOG NUMBER: LER4DD50D010-EC4DR6040509040-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105		111	108	106	104		104	102	100		100	99	97		97	96	95
2	107	102	98	95		105	101	97	94		97	94	92		94	92	90		92	90	88
3	102	96	90	86		100	94	89	86		91	88	84		89	86	83		87	84	82
4	97	89	84	80		95	88	83	79		86	82	78		84	80	77		82	79	76
5	92	84	78	74		91	83	78	74		81	77	73		80	76	72		78	75	72
6	88	79	73	69		87	78	73	69		77	72	68		75	71	68		74	70	67
7	84	75	69	65		83	74	68	64		73	68	64		72	67	64		71	67	63
8	80	71	65	61		79	70	65	61		69	64	60		68	64	60		67	63	60
9	77	67	61	57		75	67	61	57		66	61	57		65	60	57		64	60	57
10	73	64	58	54		72	63	58	54		62	58	54		62	57	54		61	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	699455
5°	716648
10°	725300
15°	690952
20°	609212
25°	492748
30°	333299
35°	167022
40°	27100
45°	26515
50°	27044
55°	27450
60°	28211
65°	28852
70°	29550
75°	29888
80°	28818
85°	24070

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 29888 cd/sqm

TEST NUMBER: P785278

CATALOG NUMBER: LER4DD50D010-EC4DR6040509040-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	624.5	11.6
10°-20°	1689.6	31.3
20°-30°	1817.9	33.7
30°-40°	790.2	14.7
40°-50°	132.7	2.5
50°-60°	129.0	2.4
60°-70°	110.4	2.0
70°-80°	73.8	1.4
80°-90°	22.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4132.0	76.7
0°-40°	4922.2	91.3
0°-60°	5184.0	96.2
0°-90°	5390.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5390.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6402	
5°	6534	624
15°	6108	1690
25°	4087	1818
35°	1252	790
45°	172	133
55°	144	129
65°	112	110
75°	71	74
85°	19	22
90°	0	



TEST NUMBER: P785278

CATALOG NUMBER: LER4DD50D010-EC4DR6040509040-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6401.7
2.5°	6581.6
5°	6534.1
7.5°	6549.1
10°	6537.4
12.5°	6402.5
15°	6108.4
17.5°	5713.5
20°	5239.5
22.5°	4732.1
25°	4087.3
27.5°	3269.1
30°	2641.8
32.5°	2036.1
35°	1252.2
37.5°	535.7
40°	190.0
42.5°	175.0
45°	171.6
47.5°	165.8
50°	159.1
52.5°	151.6
55°	144.1
57.5°	136.6
60°	129.1
62.5°	120.8
65°	111.6
67.5°	102.5
70°	92.5
72.5°	81.6
75°	70.8
77.5°	58.3
80°	45.8
82.5°	32.5
85°	19.2
87.5°	6.7
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)