

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785291

Luminaire Tested: LER4DD50D010-EC4DR6540509027-4LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P785291  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER4DD50D010-EC4DR6540509027-4LBDP1MW  
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3551.4 lumens  
Efficiency: N/A  
Efficacy: 75.6 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 47  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P785291

CATALOG NUMBER: LER4DD50D010-EC4DR6540509027-4LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P785291

CATALOG NUMBER: LER4DD50D010-EC4DR6540509027-4LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 |  | 101 | 99  | 98  |  | 97  |
| 2   | 108 | 103 | 99  | 95  | 106 | 101 | 97  | 94  | 98  | 95  | 92  |  | 95  | 92  | 90  |  | 92  |
| 3   | 102 | 96  | 91  | 87  | 100 | 94  | 90  | 86  | 92  | 88  | 85  |  | 89  | 86  | 83  |  | 87  |
| 4   | 97  | 89  | 84  | 79  | 95  | 88  | 83  | 79  | 86  | 82  | 78  |  | 84  | 80  | 77  |  | 82  |
| 5   | 92  | 83  | 78  | 73  | 90  | 83  | 77  | 73  | 81  | 76  | 72  |  | 79  | 75  | 72  |  | 77  |
| 6   | 87  | 78  | 72  | 68  | 86  | 77  | 72  | 68  | 76  | 71  | 67  |  | 74  | 70  | 67  |  | 73  |
| 7   | 83  | 73  | 67  | 63  | 81  | 73  | 67  | 63  | 71  | 66  | 62  |  | 70  | 66  | 62  |  | 69  |
| 8   | 79  | 69  | 63  | 59  | 77  | 68  | 63  | 59  | 67  | 62  | 58  |  | 66  | 62  | 58  |  | 65  |
| 9   | 75  | 65  | 59  | 55  | 74  | 65  | 59  | 55  | 64  | 58  | 55  |  | 63  | 58  | 55  |  | 62  |
| 10  | 71  | 61  | 56  | 52  | 70  | 61  | 55  | 52  | 60  | 55  | 51  |  | 59  | 55  | 51  |  | 59  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 382041 |
| 5°  | 382360 |
| 10° | 395823 |
| 15° | 396480 |
| 20° | 365027 |
| 25° | 311022 |
| 30° | 238096 |
| 35° | 168209 |
| 40° | 99285  |
| 45° | 40314  |
| 50° | 14618  |
| 55° | 8134   |
| 60° | 4676   |
| 65° | 2559   |
| 70° | 2683   |
| 75° | 2111   |
| 80° | 2202   |
| 85° | 1880   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 40314 cd/sqm



TEST NUMBER: P785291

CATALOG NUMBER: LER4DD50D010-EC4DR6540509027-4LBDP1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 336.7  | 9.5       |
| 10°-20°   | 971.2  | 27.3      |
| 20°-30°   | 1165.3 | 32.8      |
| 30°-40°   | 783.1  | 22.0      |
| 40°-50°   | 234.4  | 6.6       |
| 50°-60°   | 41.4   | 1.2       |
| 60°-70°   | 11.7   | 0.3       |
| 70°-80°   | 5.8    | 0.2       |
| 80°-90°   | 1.8    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2473.2 | 69.6      |
| 0°-40°    | 3256.3 | 91.7      |
| 0°-60°    | 3532.1 | 99.5      |
| 0°-90°    | 3551.4 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 3551.4 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3497 |      |
| 5°  | 3486 | 337  |
| 15° | 3505 | 971  |
| 25° | 2580 | 1165 |
| 35° | 1261 | 783  |
| 45° | 261  | 234  |
| 55° | 43   | 41   |
| 65° | 10   | 12   |
| 75° | 5    | 6    |
| 85° | 2    | 2    |
| 90° | 0    |      |



TEST NUMBER: P785291

CATALOG NUMBER: LER4DD50D010-EC4DR6540509027-4LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 3496.6 |
| 2.5°  | 3511.5 |
| 5°    | 3486.2 |
| 7.5°  | 3538.9 |
| 10°   | 3567.7 |
| 12.5° | 3560.7 |
| 15°   | 3505.1 |
| 17.5° | 3368.9 |
| 20°   | 3139.4 |
| 22.5° | 2869.0 |
| 25°   | 2579.9 |
| 27.5° | 2253.4 |
| 30°   | 1887.2 |
| 32.5° | 1555.3 |
| 35°   | 1261.1 |
| 37.5° | 970.4  |
| 40°   | 696.1  |
| 42.5° | 454.7  |
| 45°   | 260.9  |
| 47.5° | 138.1  |
| 50°   | 86.0   |
| 52.5° | 59.6   |
| 55°   | 42.7   |
| 57.5° | 30.8   |
| 60°   | 21.4   |
| 62.5° | 13.9   |
| 65°   | 9.9    |
| 67.5° | 8.9    |
| 70°   | 8.4    |
| 72.5° | 6.5    |
| 75°   | 5.0    |
| 77.5° | 4.5    |
| 80°   | 3.5    |
| 82.5° | 2.5    |
| 85°   | 1.5    |
| 87.5° | 1.0    |
| 90°   | 0.0    |



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

## Scaled Data Report







— 0°-180°







(END OF REPORT)