

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785304

Luminaire Tested: LER4DD50D010-EC4DR6540509050-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P785304
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD50D010-EC4DR6540509050-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3365.1 lumens
Efficiency: N/A
Efficacy: 71.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785304

CATALOG NUMBER: LER4DD50D010-EC4DR6540509050-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P785304

CATALOG NUMBER: LER4DD50D010-EC4DR6540509050-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	362003
5°	362300
10°	375065
15°	375678
20°	345877
25°	294699
30°	225605
35°	159392
40°	94079
45°	38197
50°	13853
55°	7715
60°	4414
65°	2430
70°	2556
75°	1984
80°	2076
85°	1755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 38197 cd/sqm



TEST NUMBER: P785304

CATALOG NUMBER: LER4DD50D010-EC4DR6540509050-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	319.0	9.5
10°-20°	920.3	27.3
20°-30°	1104.1	32.8
30°-40°	742.0	22.1
40°-50°	222.1	6.6
50°-60°	39.2	1.2
60°-70°	11.1	0.3
70°-80°	5.4	0.2
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2343.5	69.6
0°-40°	3085.5	91.7
0°-60°	3346.8	99.5
0°-90°	3365.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3365.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3313	
5°	3303	319
15°	3321	920
25°	2444	1104
35°	1195	742
45°	247	222
55°	40	39
65°	9	11
75°	5	5
85°	1	2
90°	0	



TEST NUMBER: P785304

CATALOG NUMBER: LER4DD50D010-EC4DR6540509050-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3313.2
2.5°	3327.3
5°	3303.3
7.5°	3353.2
10°	3380.6
12.5°	3374.0
15°	3321.2
17.5°	3192.2
20°	2974.7
22.5°	2718.6
25°	2444.5
27.5°	2135.2
30°	1788.2
32.5°	1473.7
35°	1195.0
37.5°	919.5
40°	659.6
42.5°	430.8
45°	247.2
47.5°	130.9
50°	81.5
52.5°	56.5
55°	40.5
57.5°	29.2
60°	20.2
62.5°	13.2
65°	9.4
67.5°	8.5
70°	8.0
72.5°	6.1
75°	4.7
77.5°	4.2
80°	3.3
82.5°	2.4
85°	1.4
87.5°	0.9
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)