

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785054

Luminaire Tested: LER4DD45BD010-EC4DR6540509030-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P785054
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD45BD010-EC4DR6540509030-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3791.4 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785054

CATALOG NUMBER: LER4DD45BD010-EC4DR6540509030-4LBDP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P785054

CATALOG NUMBER: LER4DD45BD010-EC4DR6540509030-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	407859
5°	408189
10°	422561
15°	423265
20°	389689
25°	332035
30°	254182
35°	179573
40°	106002
45°	43033
50°	15604
55°	8686
60°	4982
65°	2740
70°	2875
75°	2237
80°	2328
85°	2006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 43033 cd/sqm



TEST NUMBER: P785054

CATALOG NUMBER: LER4DD45BD010-EC4DR6540509030-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	359.4	9.5
10°-20°	1036.8	27.3
20°-30°	1244.0	32.8
30°-40°	836.0	22.1
40°-50°	250.3	6.6
50°-60°	44.2	1.2
60°-70°	12.6	0.3
70°-80°	6.2	0.2
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2640.3	69.6
0°-40°	3476.3	91.7
0°-60°	3770.8	99.5
0°-90°	3791.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3791.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3733	
5°	3722	359
15°	3742	1037
25°	2754	1244
35°	1346	836
45°	278	250
55°	46	44
65°	11	13
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P785054

CATALOG NUMBER: LER4DD45BD010-EC4DR6540509030-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3732.9
2.5°	3748.8
5°	3721.7
7.5°	3778.0
10°	3808.7
12.5°	3801.3
15°	3741.9
17.5°	3596.5
20°	3351.5
22.5°	3062.9
25°	2754.2
27.5°	2405.7
30°	2014.7
32.5°	1660.4
35°	1346.3
37.5°	1036.0
40°	743.2
42.5°	485.4
45°	278.5
47.5°	147.5
50°	91.8
52.5°	63.7
55°	45.6
57.5°	32.9
60°	22.8
62.5°	14.9
65°	10.6
67.5°	9.5
70°	9.0
72.5°	6.9
75°	5.3
77.5°	4.8
80°	3.7
82.5°	2.7
85°	1.6
87.5°	1.1
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)