

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785077

Luminaire Tested: LER4DD45BD010-EC4DR7040509030-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P785077
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD45BD010-EC4DR7040509030-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4159.6 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785077

CATALOG NUMBER: LER4DD45BD010-EC4DR7040509030-4LBDP1H

Luminous Intensity Polar Plot



TEST NUMBER: P785077

CATALOG NUMBER: LER4DD45BD010-EC4DR7040509030-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	74	69	87	79	73	69	77	72	68		75	71	67		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	77	66	60	56	75	66	60	56	65	59	55		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	70	59	53	49	69	59	53	49	58	53	49		57	52	49		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	510969
5°	495778
10°	481962
15°	475638
20°	444151
25°	333663
30°	235875
35°	83551
40°	43930
45°	46788
50°	48461
55°	49375
60°	49670
65°	48630
70°	45874
75°	42511
80°	37752
85°	30588

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 57.5°

Luminance: 49679 cd/sqm



TEST NUMBER: P785077

CATALOG NUMBER: LER4DD45BD010-EC4DR7040509030-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	426.4	10.3
10°-20°	1169.5	28.1
20°-30°	1288.0	31.0
30°-40°	492.1	11.8
40°-50°	232.4	5.6
50°-60°	231.0	5.6
60°-70°	185.0	4.4
70°-80°	106.3	2.6
80°-90°	28.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2883.9	69.3
0°-40°	3376.0	81.2
0°-60°	3839.4	92.3
0°-90°	4159.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4159.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4677	
5°	4520	426
15°	4205	1169
25°	2768	1288
35°	626	492
45°	303	232
55°	259	231
65°	188	185
75°	101	106
85°	24	29
90°	0	



TEST NUMBER: P785077

CATALOG NUMBER: LER4DD45BD010-EC4DR7040509030-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4676.6
2.5°	4627.7
5°	4520.3
7.5°	4430.7
10°	4344.1
12.5°	4270.8
15°	4204.9
17.5°	4045.7
20°	3819.9
22.5°	3332.7
25°	2767.7
27.5°	2409.4
30°	1869.6
32.5°	1207.6
35°	626.4
37.5°	338.4
40°	308.0
42.5°	305.8
45°	302.8
47.5°	296.2
50°	285.1
52.5°	272.5
55°	259.2
57.5°	244.3
60°	227.3
62.5°	208.1
65°	188.1
67.5°	165.9
70°	143.6
72.5°	121.4
75°	100.7
77.5°	79.2
80°	60.0
82.5°	42.2
85°	24.4
87.5°	9.6
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)