

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785079

Luminaire Tested: LER4DD45BD010-EC4DR7040509030-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P785079
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD45BD010-EC4DR7040509030-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3249.0 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785079

CATALOG NUMBER: LER4DD45BD010-EC4DR7040509030-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P785079

CATALOG NUMBER: LER4DD45BD010-EC4DR7040509030-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	74	69	87	79	73	69	77	72	68		75	71	67		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	77	66	60	56	75	66	60	56	65	59	55		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	70	59	53	49	69	59	53	49	58	53	49		57	52	49		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	399108
5°	387251
10°	376452
15°	371515
20°	346923
25°	260630
30°	184236
35°	65264
40°	34317
45°	36544
50°	37854
55°	38555
60°	38809
65°	37978
70°	35843
75°	33223
80°	29447
85°	23944

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 57.5°

Luminance: 38820 cd/sqm



TEST NUMBER: P785079

CATALOG NUMBER: LER4DD45BD010-EC4DR7040509030-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	333.0	10.3
10°-20°	913.5	28.1
20°-30°	1006.1	31.0
30°-40°	384.4	11.8
40°-50°	181.5	5.6
50°-60°	180.5	5.6
60°-70°	144.5	4.4
70°-80°	83.0	2.6
80°-90°	22.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2252.6	69.3
0°-40°	2637.0	81.2
0°-60°	2998.9	92.3
0°-90°	3249.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3249.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3653	
5°	3531	333
15°	3284	913
25°	2162	1006
35°	489	384
45°	236	181
55°	202	180
65°	147	144
75°	79	83
85°	19	23
90°	0	



TEST NUMBER: P785079

CATALOG NUMBER: LER4DD45BD010-EC4DR7040509030-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3652.8
2.5°	3614.7
5°	3530.8
7.5°	3460.8
10°	3393.1
12.5°	3335.9
15°	3284.4
17.5°	3160.1
20°	2983.7
22.5°	2603.1
25°	2161.9
27.5°	1881.9
30°	1460.3
32.5°	943.3
35°	489.3
37.5°	264.3
40°	240.6
42.5°	238.9
45°	236.5
47.5°	231.3
50°	222.7
52.5°	212.8
55°	202.4
57.5°	190.9
60°	177.6
62.5°	162.5
65°	146.9
67.5°	129.5
70°	112.2
72.5°	94.8
75°	78.7
77.5°	61.9
80°	46.8
82.5°	33.0
85°	19.1
87.5°	7.5
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)