

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785084

Luminaire Tested: LER4DD45BD010-EC4DR7040509040-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P785084
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD45BD010-EC4DR7040509040-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2559.9 lumens
Efficiency: N/A
Efficacy: 66.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785084

CATALOG NUMBER: LER4DD45BD010-EC4DR7040509040-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P785084

CATALOG NUMBER: LER4DD45BD010-EC4DR7040509040-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	74	69	87	79	73	69	77	72	68		75	71	67		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	77	66	60	56	75	66	60	56	65	59	55		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	70	59	53	49	69	59	53	49	58	53	49		57	52	49		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	314463
5°	305125
10°	296615
15°	292730
20°	273346
25°	205355
30°	145164
35°	51419
40°	27043
45°	28802
50°	29814
55°	30383
60°	30571
65°	29912
70°	28240
75°	26173
80°	23218
85°	18804

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 57.5°

Luminance: 30584 cd/sqm



TEST NUMBER: P785084

CATALOG NUMBER: LER4DD45BD010-EC4DR7040509040-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	262.4	10.3
10°-20°	719.8	28.1
20°-30°	792.7	31.0
30°-40°	302.9	11.8
40°-50°	143.0	5.6
50°-60°	142.2	5.6
60°-70°	113.8	4.4
70°-80°	65.4	2.6
80°-90°	17.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1774.9	69.3
0°-40°	2077.7	81.2
0°-60°	2362.9	92.3
0°-90°	2559.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2559.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2878	
5°	2782	262
15°	2588	720
25°	1703	793
35°	386	303
45°	186	143
55°	160	142
65°	116	114
75°	62	65
85°	15	18
90°	0	



TEST NUMBER: P785084

CATALOG NUMBER: LER4DD45BD010-EC4DR7040509040-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2878.1
2.5°	2848.1
5°	2782.0
7.5°	2726.8
10°	2673.5
12.5°	2628.4
15°	2587.9
17.5°	2489.9
20°	2350.9
22.5°	2051.1
25°	1703.4
27.5°	1482.8
30°	1150.6
32.5°	743.2
35°	385.5
37.5°	208.2
40°	189.6
42.5°	188.2
45°	186.4
47.5°	182.3
50°	175.4
52.5°	167.7
55°	159.5
57.5°	150.4
60°	139.9
62.5°	128.0
65°	115.7
67.5°	102.1
70°	88.4
72.5°	74.7
75°	62.0
77.5°	48.8
80°	36.9
82.5°	26.0
85°	15.0
87.5°	5.9
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)