

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785111

Luminaire Tested: LER4DD50D010-EC4DR2540509040-4LBDP1MW

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P785111  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER4DD50D010-EC4DR2540509040-4LBDP1MW  
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 25° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4050.4 lumens  
Efficiency: N/A  
Efficacy: 86.2 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 47  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P785111

CATALOG NUMBER: LER4DD50D010-EC4DR2540509040-4LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P785111

CATALOG NUMBER: LER4DD50D010-EC4DR2540509040-4LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 115 | 113 | 111 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 | 103 | 102 | 101 | 99  | 99  | 98  | 96  |    |    |
| 2   | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 100 | 102 | 100 | 98  | 99  | 97  | 96  | 97  | 95  | 94  | 92  |    |    |
| 3   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 98  | 95  | 93  | 96  | 93  | 91  | 94  | 92  | 90  | 89  |    |    |
| 4   | 103 | 97  | 93  | 90  | 102 | 96  | 93  | 90  | 94  | 91  | 89  | 93  | 90  | 88  | 91  | 89  | 87  | 85  |    |    |
| 5   | 100 | 93  | 89  | 86  | 98  | 93  | 89  | 86  | 91  | 87  | 85  | 89  | 86  | 84  | 88  | 85  | 83  | 82  |    |    |
| 6   | 97  | 90  | 85  | 82  | 95  | 89  | 85  | 82  | 88  | 84  | 81  | 87  | 83  | 81  | 85  | 83  | 80  | 79  |    |    |
| 7   | 93  | 87  | 82  | 79  | 92  | 86  | 82  | 79  | 85  | 81  | 78  | 84  | 80  | 78  | 83  | 80  | 78  | 77  |    |    |
| 8   | 91  | 84  | 79  | 76  | 90  | 83  | 79  | 76  | 82  | 78  | 76  | 81  | 78  | 75  | 80  | 77  | 75  | 74  |    |    |
| 9   | 88  | 81  | 76  | 73  | 87  | 80  | 76  | 73  | 80  | 76  | 73  | 79  | 75  | 73  | 78  | 75  | 73  | 72  |    |    |
| 10  | 85  | 78  | 74  | 71  | 85  | 78  | 74  | 71  | 77  | 73  | 71  | 76  | 73  | 71  | 76  | 73  | 70  | 69  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1678529 |
| 5°  | 1563341 |
| 10° | 1115177 |
| 15° | 656791  |
| 20° | 408664  |
| 25° | 224282  |
| 30° | 102571  |
| 35° | 38841   |
| 40° | 17586   |
| 45° | 10569   |
| 50° | 4385    |
| 55° | 2838    |
| 60° | 1967    |
| 65° | 1344    |
| 70° | 192     |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10569 cd/sqm



TEST NUMBER: P785111

CATALOG NUMBER: LER4DD50D010-EC4DR2540509040-4LBDP1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 1225.0 | 30.2      |
| 10°-20°   | 1659.2 | 41.0      |
| 20°-30°   | 878.0  | 21.7      |
| 30°-40°   | 216.7  | 5.4       |
| 40°-50°   | 52.9   | 1.3       |
| 50°-60°   | 13.9   | 0.3       |
| 60°-70°   | 4.7    | 0.1       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 3762.2 | 92.9      |
| 0°-40°    | 3978.9 | 98.2      |
| 0°-60°    | 4045.7 | 99.9      |
| 0°-90°    | 4050.4 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 4050.4 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 15363 |      |
| 5°  | 14254 | ###  |
| 15° | 5806  | 1659 |
| 25° | 1860  | 878  |
| 35° | 291   | 217  |
| 45° | 68    | 53   |
| 55° | 15    | 14   |
| 65° | 5     | 5    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P785111

CATALOG NUMBER: LER4DD50D010-EC4DR2540509040-4LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 15362.6 |
| 2.5°  | 15110.1 |
| 5°    | 14253.9 |
| 7.5°  | 12533.7 |
| 10°   | 10051.5 |
| 12.5° | 7598.3  |
| 15°   | 5806.4  |
| 17.5° | 4525.3  |
| 20°   | 3514.7  |
| 22.5° | 2635.9  |
| 25°   | 1860.4  |
| 27.5° | 1247.6  |
| 30°   | 813.0   |
| 32.5° | 494.6   |
| 35°   | 291.2   |
| 37.5° | 178.2   |
| 40°   | 123.3   |
| 42.5° | 94.3    |
| 45°   | 68.4    |
| 47.5° | 41.3    |
| 50°   | 25.8    |
| 52.5° | 18.7    |
| 55°   | 14.9    |
| 57.5° | 11.6    |
| 60°   | 9.0     |
| 62.5° | 7.1     |
| 65°   | 5.2     |
| 67.5° | 1.9     |
| 70°   | 0.6     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |
| 90°   | 0.0     |



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)