

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785154

Luminaire Tested: LER4DD50D010-EC4DR3540509035-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P785154
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD50D010-EC4DR3540509035-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4904.7 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785154

CATALOG NUMBER: LER4DD50D010-EC4DR3540509035-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P785154

CATALOG NUMBER: LER4DD50D010-EC4DR3540509035-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1474507
5°	1439865
10°	1297694
15°	1007222
20°	571283
25°	222257
30°	82915
35°	45444
40°	29710
45°	18079
50°	11508
55°	8134
60°	5944
65°	3232
70°	224
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18079 cd/sqm



TEST NUMBER: P785154

CATALOG NUMBER: LER4DD50D010-EC4DR3540509035-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1207.4	24.6
10°-20°	2357.4	48.1
20°-30°	961.4	19.6
30°-40°	230.1	4.7
40°-50°	95.9	2.0
50°-60°	39.7	0.8
60°-70°	12.4	0.3
70°-80°	0.3	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4526.2	92.3
0°-40°	4756.2	97.0
0°-60°	4891.8	99.7
0°-90°	4904.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4904.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13495	
5°	13128	###
15°	8904	2357
25°	1844	961
35°	341	230
45°	117	96
55°	43	40
65°	12	12
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P785154

CATALOG NUMBER: LER4DD50D010-EC4DR3540509035-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	13495.3
2.5°	13414.3
5°	13128.1
7.5°	12557.0
10°	11696.6
12.5°	10485.2
15°	8904.4
17.5°	6971.0
20°	4913.3
22.5°	3133.0
25°	1843.6
27.5°	1042.1
30°	657.2
32.5°	461.4
35°	340.7
37.5°	263.5
40°	208.3
42.5°	160.4
45°	117.0
47.5°	87.6
50°	67.7
52.5°	53.7
55°	42.7
57.5°	34.6
60°	27.2
62.5°	19.9
65°	12.5
67.5°	4.4
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)