

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212737

Luminaire Tested: **LDA4A10950D010TE LAR25NF 4LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212737
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26102)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A10950D010TE LAR25NF 4LLWW1
Description: PORTFOLIO 4" Lensed Wall Wash, Self-flanged, 25° Narrow Flood Optic,
at 30° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 974.7 lumens
Efficiency: N/A
Efficacy: 78.6 lumens/watt
Spacing Criteria (0/90/45): 2.11 / 1.09 / 1.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212737

CATALOG NUMBER: LDA4A10950D010TE LAR25NF 4LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212737

CATALOG NUMBER: LDA4A10950D010TE LAR25NF 4LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80		
3	97	89	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71		
4	90	80	73	67	88	79	72	67	77	71	66	74	69	65	72	68	65	63		
5	83	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56		
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	61	55	52	50		
7	72	60	53	47	71	60	52	47	58	52	47	57	51	47	56	50	46	44		
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40		
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36		
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	33328	33328	33328
5°	55458	33071	20814
10°	89778	31625	14065
15°	132754	29970	10931
20°	180340	28812	12903
25°	217129	28921	17529
30°	236244	27090	16351
35°	229329	22812	13085
40°	198630	18388	10740
45°	154918	14164	9175
50°	102720	10592	7062
55°	57288	7785	4236
60°	30195	5156	1752
65°	16257	2568	175
70°	7790	902	216
75°	2716	667	286
80°	994	994	0
85°	2689	1981	0



TEST NUMBER: P1212737

CATALOG NUMBER: LDA4A10950D010TE LAR25NF 4LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.8	3.0
10°-20°	113.8	11.7
20°-30°	234.0	24.0
30°-40°	279.5	28.7
40°-50°	206.4	21.2
50°-60°	86.9	8.9
60°-70°	21.3	2.2
70°-80°	3.0	0.3
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	376.5	38.6
0°-40°	656.0	67.3
0°-60°	949.2	97.4
0°-90°	974.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	974.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	270	270	270	270	270	
5°	448	386	267	192	168	51
15°	1040	667	235	106	86	305
25°	1595	847	212	128	129	730
35°	1523	757	152	91	87	934
45°	888	467	81	53	53	682
55°	266	173	36	23	20	254
65°	56	38	9	2	1	61
75°	6	3	1	1	1	8
85°	2	2	1	1	0	2
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212737

CATALOG NUMBER: LDA4A10950D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	270.2	270.2	270.2	270.2	270.2	270.2	270.2	270.2	270.2	270.2	270.2
2.5°	351.4	346.9	346.9	348.3	352.1	348.9	346.3	343.7	346.3	340.6	342.6
5°	447.9	447.2	447.2	442.1	446.6	447.2	442.1	437.6	439.0	430.7	430.7
7.5°	574.7	570.9	569.6	562.6	567.7	567.1	558.9	551.2	551.2	537.8	534.8
10°	716.8	711.7	709.1	700.2	704.7	702.2	690.1	678.8	675.6	656.6	649.5
12.5°	873.5	870.4	866.5	855.1	858.8	853.7	836.7	820.1	813.3	787.8	775.7
15°	1039.6	1044.7	1038.3	1025.0	1027.5	1018.7	996.4	973.6	962.9	928.6	910.8
17.5°	1210.9	1217.2	1210.2	1195.0	1194.3	1182.3	1152.0	1124.0	1108.1	1064.4	1040.9
20°	1373.9	1375.8	1367.0	1350.4	1346.7	1330.2	1293.3	1254.1	1238.8	1185.0	1155.1
22.5°	1502.1	1508.9	1498.2	1486.2	1474.1	1453.2	1410.0	1367.0	1345.3	1283.9	1247.7
25°	1595.4	1611.1	1598.5	1584.4	1571.2	1546.5	1498.2	1451.8	1425.2	1356.8	1315.6
27.5°	1656.8	1672.0	1658.2	1642.3	1628.3	1599.7	1547.1	1502.7	1470.2	1395.5	1351.1
30°	1658.7	1677.1	1662.5	1645.4	1632.1	1603.6	1549.6	1503.9	1467.8	1392.9	1346.7
32.5°	1613.0	1627.7	1613.0	1598.5	1583.3	1555.9	1502.1	1458.2	1420.2	1348.6	1302.2
35°	1523.0	1535.8	1521.0	1503.9	1493.2	1469.1	1417.7	1375.8	1337.9	1271.8	1231.2
37.5°	1398.6	1410.0	1396.7	1387.3	1371.3	1349.9	1302.8	1265.5	1229.3	1169.7	1133.5
40°	1233.6	1257.8	1245.1	1238.8	1224.2	1205.9	1164.6	1131.5	1098.6	1046.7	1016.8
42.5°	1068.8	1091.7	1080.2	1075.8	1063.1	1047.3	1013.0	985.1	954.6	911.6	886.1
45°	888.1	912.2	901.4	899.5	888.6	876.5	839.9	825.2	798.5	758.0	745.9
47.5°	718.0	722.5	712.3	712.9	705.4	697.0	667.3	658.4	645.1	614.0	600.1
50°	535.3	538.5	530.3	532.8	527.8	522.7	502.3	498.0	489.7	468.8	460.5
52.5°	368.6	383.1	377.4	379.9	377.4	375.5	367.2	359.6	355.8	342.6	338.7
55°	266.4	267.7	263.2	265.7	263.8	263.2	258.2	253.7	251.8	243.6	242.3
57.5°	184.5	185.8	185.8	184.5	184.0	182.7	179.5	177.0	175.7	173.8	169.9
60°	122.4	127.4	125.6	126.9	126.3	126.3	123.8	121.8	121.2	117.4	117.4
62.5°	83.7	86.9	85.6	86.2	85.6	85.6	83.7	82.4	82.4	81.8	79.9
65°	55.7	57.7	56.5	57.1	57.1	57.1	55.7	54.6	54.6	53.9	52.6
67.5°	35.5	36.8	36.2	36.8	36.2	36.8	35.5	34.8	34.3	34.3	33.7
70°	21.6	22.3	21.6	22.3	21.6	21.6	20.9	20.9	20.3	19.7	19.7
72.5°	11.4	12.1	12.1	12.1	12.1	12.1	11.4	10.7	10.7	10.7	10.2
75°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.0	5.0	5.0
77.5°	2.5	2.5	2.5	2.5	3.2	2.5	2.5	2.5	2.5	2.5	2.5
80°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
82.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
85°	1.9	1.9	1.9	1.9	1.9	1.9	2.5	2.5	2.5	2.5	1.9
87.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.2	3.2	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212737

CATALOG NUMBER: LDA4A10950D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	270.2	270.2	270.2	270.2	270.2	270.2	270.2	270.2	270.2	270.2	270.2
2.5°	337.4	334.3	333.0	330.5	327.3	325.3	323.4	324.2	319.7	316.5	312.1
5°	422.4	415.4	411.7	406.0	399.0	393.3	388.1	385.6	377.4	371.7	359.6
7.5°	522.7	510.6	502.9	493.0	480.9	470.7	460.5	453.5	440.9	430.0	411.7
10°	632.4	614.0	600.7	585.5	567.1	550.6	535.3	522.7	503.7	487.1	463.0
12.5°	752.3	726.3	707.3	685.0	659.0	636.3	608.9	594.4	568.3	545.5	514.4
15°	879.7	845.5	818.9	788.4	754.1	723.6	688.9	667.3	633.0	603.8	565.1
17.5°	1002.2	959.1	924.2	885.5	843.0	803.7	762.5	732.1	690.1	654.1	607.7
20°	1108.7	1057.4	1014.8	967.9	917.9	869.6	824.6	784.0	735.2	692.6	639.9
22.5°	1195.7	1136.1	1087.2	1032.6	975.0	920.4	869.0	822.6	766.9	720.0	662.2
25°	1258.5	1193.2	1138.6	1078.3	1014.8	952.7	898.1	847.4	786.7	736.4	675.0
27.5°	1291.5	1222.3	1164.6	1099.9	1032.6	967.9	909.0	855.1	791.0	738.4	675.0
30°	1285.8	1215.2	1155.6	1089.2	1021.2	956.6	894.9	841.0	775.1	721.9	658.4
32.5°	1242.1	1172.9	1114.5	1049.8	983.2	920.4	858.8	806.8	740.9	688.9	627.3
35°	1169.7	1104.3	1049.2	987.6	924.8	865.8	810.1	757.3	693.9	644.5	586.7
37.5°	1075.8	1016.2	966.1	909.0	851.2	798.0	742.8	697.7	641.3	594.9	538.5
40°	963.5	910.8	866.5	815.8	763.7	717.5	671.1	627.3	572.1	530.9	482.8
42.5°	839.9	794.8	756.7	712.3	667.3	628.0	588.0	549.8	504.3	466.9	421.8
45°	706.6	668.6	637.4	602.0	564.6	527.8	498.6	466.9	424.3	396.4	358.3
47.5°	569.0	539.9	516.4	489.1	459.3	436.4	408.5	383.1	352.1	326.0	295.0
50°	438.4	418.1	401.5	382.4	361.0	340.1	323.4	303.9	280.3	259.4	234.7
52.5°	324.2	310.8	300.7	288.0	273.4	262.6	247.3	232.8	215.0	199.3	180.1
55°	232.2	224.5	218.2	210.6	200.4	190.8	183.4	173.2	160.5	148.4	134.5
57.5°	166.8	158.6	157.9	149.7	145.8	138.9	132.0	124.4	115.3	107.1	97.1
60°	115.3	109.7	107.1	104.0	99.6	95.2	91.9	86.9	80.5	74.9	67.3
62.5°	78.0	74.2	73.0	71.7	67.8	65.9	62.1	59.0	54.6	50.0	45.0
65°	51.4	48.9	47.5	45.7	43.7	42.5	40.6	38.1	34.3	31.6	28.5
67.5°	32.3	30.5	29.1	28.5	26.6	26.0	24.1	22.8	20.3	19.0	17.1
70°	18.4	17.8	16.4	16.4	15.2	13.9	13.4	12.1	11.4	10.2	9.6
72.5°	9.6	9.6	8.8	8.2	7.6	7.6	7.1	6.3	5.7	5.0	5.0
75°	4.5	4.5	4.5	3.8	3.8	3.8	3.2	3.2	3.2	2.5	2.5
77.5°	2.5	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.4	1.4
80°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
82.5°	1.4	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
85°	1.9	1.4	1.4	1.4	1.4	1.9	1.9	1.9	1.9	1.9	1.9
87.5°	1.9	1.9	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212737

CATALOG NUMBER: LDA4A10950D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	270.2	270.2	270.2	270.2	270.2	270.2	270.2	270.2	270.2	270.2	270.2
2.5°	308.9	307.6	304.4	303.9	296.8	295.6	291.8	286.1	281.6	280.3	281.6
5°	355.2	349.4	340.1	338.1	326.7	322.8	314.6	305.8	298.2	293.7	291.8
7.5°	402.8	393.3	379.3	372.4	355.8	347.6	335.5	322.8	310.8	302.5	297.5
10°	448.4	433.2	407.9	402.2	381.9	368.6	352.1	334.9	319.7	308.3	300.0
12.5°	491.6	473.2	447.2	431.3	404.7	387.6	366.7	345.7	326.7	311.5	300.0
15°	536.0	511.9	479.5	457.3	426.9	404.0	378.8	354.6	332.4	313.2	299.4
17.5°	572.8	543.0	505.0	478.2	442.7	415.4	386.3	358.3	334.3	312.7	296.8
20°	600.1	565.1	522.1	491.0	451.6	421.1	389.5	359.0	332.4	308.9	291.8
22.5°	618.5	578.4	531.6	497.3	456.1	423.1	388.8	357.1	329.9	305.8	287.4
25°	627.3	584.2	535.3	498.6	455.4	421.1	385.6	353.3	325.3	300.7	283.0
27.5°	626.1	580.3	530.3	491.6	447.9	412.3	376.1	343.7	316.5	291.8	273.4
30°	607.7	562.6	511.9	472.5	429.4	394.0	357.8	326.0	299.4	274.0	256.9
32.5°	579.2	532.8	483.4	439.5	402.8	367.8	333.7	301.3	275.9	251.2	234.7
35°	540.5	496.0	448.4	411.0	371.1	337.4	304.4	274.0	250.0	225.9	210.6
37.5°	495.5	452.9	409.0	370.3	335.5	304.4	273.4	246.2	222.0	200.4	185.8
40°	443.4	404.0	364.0	331.1	296.8	268.2	239.7	213.1	193.4	173.8	161.1
42.5°	387.0	352.1	316.0	287.4	256.2	230.9	203.6	184.5	165.6	147.9	137.6
45°	328.0	297.5	267.1	241.1	215.7	193.4	169.9	152.3	137.6	123.0	114.2
47.5°	269.6	243.6	218.8	197.9	175.7	157.4	140.8	124.9	111.0	98.9	91.9
50°	210.6	193.4	173.8	156.7	138.9	123.8	108.5	97.1	86.2	77.4	73.0
52.5°	164.2	148.4	132.6	118.6	106.0	93.3	83.1	73.5	65.9	60.3	57.1
55°	122.4	109.7	97.7	86.9	76.8	68.5	61.5	55.7	50.8	46.4	45.0
57.5°	87.6	78.0	69.8	61.5	55.2	50.0	45.7	41.9	38.7	35.5	34.8
60°	60.9	53.9	48.9	43.7	40.0	36.2	33.7	31.1	28.5	26.6	26.0
62.5°	40.6	36.8	33.0	30.5	28.5	25.5	24.1	22.3	20.9	19.0	18.4
65°	26.0	23.4	21.6	19.7	18.4	17.1	15.9	14.6	13.4	12.1	12.1
67.5°	15.9	13.9	13.4	12.1	10.7	10.2	9.6	8.2	7.6	7.6	7.1
70°	8.8	7.6	7.1	6.3	5.7	5.7	5.0	4.5	4.5	3.8	3.8
72.5°	4.5	4.5	3.8	3.8	3.2	3.2	2.5	2.5	2.5	1.9	1.9
75°	2.5	2.5	1.9	1.9	1.9	1.9	1.9	1.9	1.4	1.4	1.4
77.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
80°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
82.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
85°	1.9	1.9	1.9	1.9	1.4	1.4	1.4	1.4	1.4	1.4	1.4
87.5°	1.9	1.9	1.9	1.9	1.9	1.4	1.4	1.4	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212737

CATALOG NUMBER: LDA4A10950D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	112.5°	135°	157.5°	180°
0°	270.2	270.2	270.2	270.2	270.2	270.2	270.2	270.2
2.5°	276.6	270.2	268.9	268.9	242.3	226.4	214.3	211.3
5°	283.0	274.0	269.6	267.1	219.5	191.6	173.2	168.1
7.5°	286.1	273.4	266.4	260.7	197.3	161.1	141.4	135.8
10°	284.9	269.6	260.0	252.5	177.0	137.6	117.4	112.3
12.5°	282.3	265.2	253.1	243.6	159.8	119.2	100.8	95.8
15°	279.8	260.0	246.2	234.7	145.8	106.5	90.1	85.6
17.5°	274.6	254.4	238.5	226.4	137.0	101.5	87.6	85.1
20°	268.9	247.9	231.6	219.5	134.5	106.5	98.3	98.3
22.5°	265.2	243.6	227.8	215.7	138.9	118.6	115.3	117.4
25°	260.0	239.7	223.9	212.5	143.3	128.1	126.3	128.8
27.5°	251.8	231.6	216.3	204.9	140.8	126.9	124.9	126.3
30°	235.2	215.7	202.3	190.2	130.6	117.4	114.2	114.8
32.5°	214.3	195.4	182.7	171.3	116.1	103.4	100.3	100.3
35°	191.6	173.8	161.7	151.5	102.1	90.8	87.6	86.9
37.5°	168.8	152.3	142.2	132.6	89.4	79.4	76.1	75.5
40°	145.8	131.2	121.8	114.2	78.7	70.5	67.3	66.7
42.5°	124.4	111.7	103.4	97.1	68.5	62.1	59.6	59.0
45°	102.8	92.6	86.2	81.2	59.6	53.2	52.6	52.6
47.5°	83.1	74.9	70.5	67.3	50.8	45.7	45.0	45.7
50°	66.7	60.9	57.7	55.2	43.2	38.7	36.8	36.8
52.5°	52.6	48.9	46.9	45.0	35.5	31.1	28.5	28.0
55°	41.9	38.7	37.4	36.2	28.0	22.8	20.3	19.7
57.5°	33.0	30.5	29.1	28.0	20.9	15.9	13.4	12.7
60°	24.8	22.8	21.6	20.9	14.6	9.6	7.6	7.1
62.5°	17.8	16.4	15.2	14.6	8.8	5.0	3.2	2.5
65°	10.7	10.7	9.6	8.8	4.5	1.9	1.4	0.6
67.5°	6.3	5.7	5.0	5.0	1.9	1.4	0.6	0.6
70°	3.2	3.2	2.5	2.5	1.4	0.6	0.6	0.6
72.5°	1.9	1.9	1.9	1.4	1.4	0.6	0.6	0.6
75°	1.4	1.4	1.4	1.4	1.4	0.6	0.6	0.6
77.5°	1.4	1.4	1.4	1.4	1.4	0.6	0.6	0.0
80°	1.4	1.4	1.4	1.4	1.4	0.6	0.6	0.0
82.5°	1.4	1.4	1.4	1.4	1.4	0.6	0.6	0.6
85°	1.4	1.4	1.4	1.4	1.4	0.6	0.6	0.0
87.5°	1.4	1.4	1.4	1.4	1.4	0.6	0.6	0.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)