

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785163

Luminaire Tested: LER4DD50D010-EC4DR3540509050-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P785163
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD50D010-EC4DR3540509050-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4617.9 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785163

CATALOG NUMBER: LER4DD50D010-EC4DR3540509050-4LBDP1MW

Luminous Intensity Polar Plot



CATALOG NUMBER: LER4DD50D010-EC4DR3540509050-4LBDP1MW

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96						
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92						
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88						
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84						
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81						
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78						
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75						
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72						
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70						
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68						

	0°
0°	1388267
5°	1355643
10°	1221796
15°	948311
20°	537867
25°	209249
30°	78070
35°	42789
40°	27970
45°	17028
50°	10828
55°	7658
60°	5594
65°	3051
70°	224
75°	0
80°	0
85°	0

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 17028 cd/sqm



TEST NUMBER: P785163

CATALOG NUMBER: LER4DD50D010-EC4DR3540509050-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1136.8	24.6
10°-20°	2219.5	48.1
20°-30°	905.2	19.6
30°-40°	216.6	4.7
40°-50°	90.3	2.0
50°-60°	37.4	0.8
60°-70°	11.7	0.3
70°-80°	0.3	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4261.4	92.3
0°-40°	4478.1	97.0
0°-60°	4605.7	99.7
0°-90°	4617.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4617.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12706	
5°	12360	###
15°	8384	2219
25°	1736	905
35°	321	217
45°	110	90
55°	40	37
65°	12	12
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P785163

CATALOG NUMBER: LER4DD50D010-EC4DR3540509050-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	12706.0
2.5°	12629.7
5°	12360.2
7.5°	11822.5
10°	11012.5
12.5°	9871.9
15°	8383.6
17.5°	6563.3
20°	4625.9
22.5°	2949.7
25°	1735.7
27.5°	981.2
30°	618.8
32.5°	434.5
35°	320.8
37.5°	248.1
40°	196.1
42.5°	151.1
45°	110.2
47.5°	82.5
50°	63.7
52.5°	50.6
55°	40.2
57.5°	32.6
60°	25.6
62.5°	18.7
65°	11.8
67.5°	4.2
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)