

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785246

Luminaire Tested: LER4DD50D010-EC4DR5540509030-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P785246
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD50D010-EC4DR5540509030-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5196.1 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785246

CATALOG NUMBER: LER4DD50D010-EC4DR5540509030-4LBDP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P785246

CATALOG NUMBER: LER4DD50D010-EC4DR5540509030-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75		
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70		
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65		
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61		
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57		
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54		
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	636619
5°	611335
10°	609028
15°	591535
20°	530402
25°	438341
30°	331116
35°	240089
40°	153641
45°	70167
50°	22947
55°	9905
60°	4261
65°	569
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 70167 cd/sqm

TEST NUMBER: P785246

CATALOG NUMBER: LER4DD50D010-EC4DR5540509030-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	530.4	10.2
10°-20°	1447.5	27.9
20°-30°	1649.6	31.7
30°-40°	1123.0	21.6
40°-50°	387.0	7.4
50°-60°	53.5	1.0
60°-70°	5.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3627.5	69.8
0°-40°	4750.5	91.4
0°-60°	5190.9	99.9
0°-90°	5196.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5196.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5827	
5°	5574	530
15°	5230	1448
25°	3636	1650
35°	1800	1123
45°	454	387
55°	52	53
65°	2	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P785246

CATALOG NUMBER: LER4DD50D010-EC4DR5540509030-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	5826.6
2.5°	5693.0
5°	5573.9
7.5°	5515.4
10°	5489.4
12.5°	5402.8
15°	5229.5
17.5°	4954.4
20°	4561.7
22.5°	4108.2
25°	3636.0
27.5°	3144.4
30°	2624.5
32.5°	2184.1
35°	1800.0
37.5°	1434.6
40°	1077.2
42.5°	746.6
45°	454.1
47.5°	244.8
50°	135.0
52.5°	80.1
55°	52.0
57.5°	33.2
60°	19.5
62.5°	8.7
65°	2.2
67.5°	0.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)