

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785272

Luminaire Tested: LER4DD50D010-EC4DR6040509035-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P785272
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD50D010-EC4DR6040509035-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3862.0 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785272

CATALOG NUMBER: LER4DD50D010-EC4DR6040509035-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P785272

CATALOG NUMBER: LER4DD50D010-EC4DR6040509035-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	96	90	86	100	94	89	86	91	88	84		89	86	83		87
4	97	89	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	78	73	69	77	72	68		75	71	68		74
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		71
8	80	71	65	61	79	70	65	61	69	64	60		68	64	60		67
9	77	67	61	57	75	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	501146
5°	513469
10°	519661
15°	495048
20°	436488
25°	353036
30°	238802
35°	119671
40°	19412
45°	19006
50°	19378
55°	19678
60°	20213
65°	20683
70°	21180
75°	21403
80°	20638
85°	17175

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 21403 cd/sqm



TEST NUMBER: P785272

CATALOG NUMBER: LER4DD50D010-EC4DR6040509035-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	447.4	11.6
10°-20°	1210.6	31.3
20°-30°	1302.5	33.7
30°-40°	566.2	14.7
40°-50°	95.1	2.5
50°-60°	92.5	2.4
60°-70°	79.1	2.0
70°-80°	52.9	1.4
80°-90°	15.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2960.5	76.7
0°-40°	3526.6	91.3
0°-60°	3714.2	96.2
0°-90°	3862.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3862.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4587	
5°	4682	447
15°	4376	1211
25°	2928	1302
35°	897	566
45°	123	95
55°	103	92
65°	80	79
75°	51	53
85°	14	16
90°	0	



TEST NUMBER: P785272

CATALOG NUMBER: LER4DD50D010-EC4DR6040509035-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	4586.7
2.5°	4715.6
5°	4681.6
7.5°	4692.3
10°	4683.9
12.5°	4587.2
15°	4376.5
17.5°	4093.6
20°	3754.0
22.5°	3390.4
25°	2928.4
27.5°	2342.3
30°	1892.8
32.5°	1458.8
35°	897.2
37.5°	383.8
40°	136.1
42.5°	125.4
45°	123.0
47.5°	118.8
50°	114.0
52.5°	108.6
55°	103.3
57.5°	97.9
60°	92.5
62.5°	86.6
65°	80.0
67.5°	73.4
70°	66.3
72.5°	58.5
75°	50.7
77.5°	41.8
80°	32.8
82.5°	23.3
85°	13.7
87.5°	4.8
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)