

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785277

Luminaire Tested: LER4DD50D010-EC4DR6040509040-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P785277
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD50D010-EC4DR6040509040-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5133.5 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785277

CATALOG NUMBER: LER4DD50D010-EC4DR6040509040-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P785277

CATALOG NUMBER: LER4DD50D010-EC4DR6040509040-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105		111	108	106	104		104	102	100		100	99	97		97	96	95
2	107	102	98	95		105	101	97	94		97	94	92		94	92	90		92	90	88
3	102	96	90	86		100	94	89	86		91	88	84		89	86	83		87	84	82
4	97	89	84	80		95	88	83	79		86	82	78		84	80	77		82	79	76
5	92	84	78	74		91	83	78	74		81	77	73		80	76	72		78	75	72
6	88	79	73	69		87	78	73	69		77	72	68		75	71	68		74	70	67
7	84	75	69	65		83	74	68	64		73	68	64		72	67	64		71	67	63
8	80	71	65	61		79	70	65	61		69	64	60		68	64	60		67	63	60
9	77	67	61	57		75	67	61	57		66	61	57		65	60	57		64	60	57
10	73	64	58	54		72	63	58	54		62	58	54		62	57	54		61	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	666141
5°	682527
10°	690763
15°	658047
20°	580202
25°	469276
30°	317427
35°	159059
40°	25802
45°	25248
50°	25752
55°	26154
60°	26878
65°	27482
70°	28144
75°	28453
80°	27433
85°	22816

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 28453 cd/sqm



TEST NUMBER: P785277

CATALOG NUMBER: LER4DD50D010-EC4DR6040509040-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	594.8	11.6
10°-20°	1609.2	31.3
20°-30°	1731.3	33.7
30°-40°	752.6	14.7
40°-50°	126.4	2.5
50°-60°	122.9	2.4
60°-70°	105.1	2.0
70°-80°	70.3	1.4
80°-90°	21.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3935.2	76.7
0°-40°	4687.8	91.3
0°-60°	4937.1	96.2
0°-90°	5133.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5133.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6097	
5°	6223	595
15°	5818	1609
25°	3893	1731
35°	1192	753
45°	163	126
55°	137	123
65°	106	105
75°	67	70
85°	18	21
90°	0	



TEST NUMBER: P785277

CATALOG NUMBER: LER4DD50D010-EC4DR6040509040-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	6096.8
2.5°	6268.2
5°	6223.0
7.5°	6237.3
10°	6226.1
12.5°	6097.6
15°	5817.5
17.5°	5441.4
20°	4990.0
22.5°	4506.8
25°	3892.6
27.5°	3113.5
30°	2516.0
32.5°	1939.2
35°	1192.5
37.5°	510.2
40°	180.9
42.5°	166.6
45°	163.4
47.5°	157.9
50°	151.5
52.5°	144.4
55°	137.3
57.5°	130.1
60°	123.0
62.5°	115.0
65°	106.3
67.5°	97.6
70°	88.1
72.5°	77.8
75°	67.4
77.5°	55.5
80°	43.6
82.5°	30.9
85°	18.2
87.5°	6.3
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)