

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785286

Luminaire Tested: LER4DD50D010-EC4DR6540509024-4LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P785286  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER4DD50D010-EC4DR6540509024-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3815.4 lumens  
Efficiency: N/A  
Efficacy: 81.2 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 47  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P785286

CATALOG NUMBER: LER4DD50D010-EC4DR6540509024-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P785286

CATALOG NUMBER: LER4DD50D010-EC4DR6540509024-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 |  | 101 | 99  | 98  |  | 97  |
| 2   | 108 | 103 | 99  | 95  | 106 | 101 | 97  | 94  | 98  | 95  | 92  |  | 95  | 92  | 90  |  | 92  |
| 3   | 102 | 96  | 91  | 87  | 100 | 94  | 90  | 86  | 92  | 88  | 85  |  | 89  | 86  | 83  |  | 87  |
| 4   | 97  | 89  | 84  | 79  | 95  | 88  | 83  | 79  | 86  | 82  | 78  |  | 84  | 80  | 77  |  | 82  |
| 5   | 92  | 83  | 78  | 73  | 90  | 83  | 77  | 73  | 81  | 76  | 72  |  | 79  | 75  | 72  |  | 77  |
| 6   | 87  | 78  | 72  | 68  | 86  | 77  | 72  | 68  | 76  | 71  | 67  |  | 74  | 70  | 67  |  | 73  |
| 7   | 83  | 73  | 67  | 63  | 81  | 73  | 67  | 63  | 71  | 66  | 62  |  | 70  | 66  | 62  |  | 69  |
| 8   | 79  | 69  | 63  | 59  | 77  | 68  | 63  | 59  | 67  | 62  | 58  |  | 66  | 62  | 58  |  | 65  |
| 9   | 75  | 65  | 59  | 55  | 74  | 65  | 59  | 55  | 64  | 58  | 55  |  | 63  | 58  | 55  |  | 62  |
| 10  | 71  | 61  | 56  | 52  | 70  | 61  | 55  | 52  | 60  | 55  | 51  |  | 59  | 55  | 51  |  | 59  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 410438 |
| 5°  | 410777 |
| 10° | 425246 |
| 15° | 425946 |
| 20° | 392153 |
| 25° | 334133 |
| 30° | 255796 |
| 35° | 180707 |
| 40° | 106673 |
| 45° | 43311  |
| 50° | 15706  |
| 55° | 8744   |
| 60° | 5026   |
| 65° | 2766   |
| 70° | 2907   |
| 75° | 2237   |
| 80° | 2328   |
| 85° | 2006   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 43311 cd/sqm



TEST NUMBER: P785286

CATALOG NUMBER: LER4DD50D010-EC4DR6540509024-4LBDP1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 361.7  | 9.5       |
| 10°-20°   | 1043.4 | 27.3      |
| 20°-30°   | 1251.9 | 32.8      |
| 30°-40°   | 841.3  | 22.1      |
| 40°-50°   | 251.9  | 6.6       |
| 50°-60°   | 44.5   | 1.2       |
| 60°-70°   | 12.6   | 0.3       |
| 70°-80°   | 6.2    | 0.2       |
| 80°-90°   | 2.0    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2657.0 | 69.6      |
| 0°-40°    | 3498.3 | 91.7      |
| 0°-60°    | 3794.6 | 99.5      |
| 0°-90°    | 3815.4 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 3815.4 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3756 |      |
| 5°  | 3745 | 362  |
| 15° | 3766 | 1043 |
| 25° | 2772 | 1252 |
| 35° | 1355 | 841  |
| 45° | 280  | 252  |
| 55° | 46   | 44   |
| 65° | 11   | 13   |
| 75° | 5    | 6    |
| 85° | 2    | 2    |
| 90° | 0    |      |



TEST NUMBER: P785286

CATALOG NUMBER: LER4DD50D010-EC4DR6540509024-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 3756.5 |
| 2.5°  | 3772.5 |
| 5°    | 3745.3 |
| 7.5°  | 3801.9 |
| 10°   | 3832.9 |
| 12.5° | 3825.4 |
| 15°   | 3765.6 |
| 17.5° | 3619.3 |
| 20°   | 3372.7 |
| 22.5° | 3082.3 |
| 25°   | 2771.6 |
| 27.5° | 2420.9 |
| 30°   | 2027.5 |
| 32.5° | 1670.9 |
| 35°   | 1354.8 |
| 37.5° | 1042.6 |
| 40°   | 747.9  |
| 42.5° | 488.4  |
| 45°   | 280.3  |
| 47.5° | 148.4  |
| 50°   | 92.4   |
| 52.5° | 64.1   |
| 55°   | 45.9   |
| 57.5° | 33.1   |
| 60°   | 23.0   |
| 62.5° | 14.9   |
| 65°   | 10.7   |
| 67.5° | 9.6    |
| 70°   | 9.1    |
| 72.5° | 6.9    |
| 75°   | 5.3    |
| 77.5° | 4.8    |
| 80°   | 3.7    |
| 82.5° | 2.7    |
| 85°   | 1.6    |
| 87.5° | 1.1    |
| 90°   | 0.0    |



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

## Scaled Data Report





— 0°-180°







(END OF REPORT)