

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1191610

Luminaire Tested: **LDA4A20927D010TE LAR25NF 4LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1191610
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26102)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A20927D010TE LAR25NF 4LLWW1
Description: PORTFOLIO 4" Lensed Wall Wash, Self-flanged, 25° Narrow Flood Optic,
at 30° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1570.4 lumens
Efficiency: N/A
Efficacy: 54.5 lumens/watt
Spacing Criteria (0/90/45): 2.11 / 1.09 / 1.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1191610

CATALOG NUMBER: LDA4A20927D010TE LAR25NF 4LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191610

CATALOG NUMBER: LDA4A20927D010TE LAR25NF 4LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80		
3	97	89	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71		
4	90	80	73	67	88	79	72	67	77	71	66	74	69	65	72	68	65	63		
5	83	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56		
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	61	55	52	50		
7	72	60	53	47	71	60	52	47	58	52	47	57	51	47	56	50	46	45		
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40		
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36		
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	53705	53705	53705
5°	89334	53278	33542
10°	144649	50939	22657
15°	213918	48295	17622
20°	290587	46414	20792
25°	349851	46600	28240
30°	380665	43682	26363
35°	369532	36786	21081
40°	320084	29627	17277
45°	249602	22834	14810
50°	165545	17059	11360
55°	92319	12516	6817
60°	48648	8313	2788
65°	26238	4174	292
70°	12550	1479	361
75°	4432	953	477
80°	1421	1421	0
85°	4246	2830	0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191610

CATALOG NUMBER: LDA4A20927D010TE LAR25NF 4LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.4	3.0
10°-20°	183.3	11.7
20°-30°	377.0	24.0
30°-40°	450.3	28.7
40°-50°	332.5	21.2
50°-60°	139.9	8.9
60°-70°	34.4	2.2
70°-80°	4.7	0.3
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	606.8	38.6
0°-40°	1057.1	67.3
0°-60°	1529.5	97.4
0°-90°	1570.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1570.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	435	435	435	435	435	
5°	722	622	430	309	271	83
15°	1675	1075	378	172	138	492
25°	2571	1366	342	206	208	1176
35°	2454	1220	244	146	140	1505
45°	1431	752	131	86	85	1099
55°	429	279	58	37	32	410
65°	90	61	14	3	1	98
75°	9	5	2	1	1	13
85°	3	3	2	1	0	3
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191610

CATALOG NUMBER: LDA4A20927D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	435.4	435.4	435.4	435.4	435.4	435.4	435.4	435.4	435.4	435.4	435.4
2.5°	566.3	559.1	559.1	561.1	567.3	562.1	558.1	554.0	558.1	548.9	552.0
5°	721.5	720.5	720.5	712.4	719.5	720.5	712.4	705.2	707.3	694.0	694.0
7.5°	926.0	919.9	917.9	906.6	914.8	913.7	900.5	888.2	888.2	866.8	861.6
10°	1154.9	1146.8	1142.8	1128.4	1135.5	1131.5	1112.1	1093.7	1088.5	1057.9	1046.6
12.5°	1407.4	1402.4	1396.2	1377.8	1383.8	1375.7	1348.1	1321.6	1310.3	1269.5	1250.0
15°	1675.2	1683.4	1673.2	1651.7	1655.8	1641.4	1605.7	1568.9	1551.5	1496.4	1467.7
17.5°	1951.2	1961.4	1950.2	1925.7	1924.5	1905.1	1856.2	1811.1	1785.7	1715.0	1677.2
20°	2213.8	2216.9	2202.5	2176.0	2170.0	2143.3	2084.1	2020.7	1996.2	1909.3	1861.2
22.5°	2420.3	2431.6	2414.2	2394.7	2375.3	2341.5	2272.0	2202.5	2167.8	2068.7	2010.4
25°	2570.6	2596.1	2575.7	2553.2	2531.7	2491.8	2414.2	2339.5	2296.7	2186.3	2119.9
27.5°	2669.7	2694.3	2671.7	2646.2	2623.8	2577.7	2492.9	2421.3	2369.2	2248.6	2177.1
30°	2672.7	2702.4	2678.9	2651.3	2629.8	2583.8	2496.9	2423.4	2365.1	2244.5	2170.0
32.5°	2599.1	2622.7	2599.1	2575.7	2551.1	2507.2	2420.3	2349.8	2288.4	2173.0	2098.3
35°	2454.1	2474.5	2451.0	2423.4	2406.0	2367.2	2284.3	2216.9	2155.6	2049.3	1983.9
37.5°	2253.7	2272.0	2250.6	2235.3	2209.8	2175.0	2099.4	2039.1	1980.9	1884.7	1826.5
40°	1987.9	2026.8	2006.3	1996.2	1972.6	1943.1	1876.6	1823.5	1770.3	1686.5	1638.4
42.5°	1722.2	1759.0	1740.6	1733.5	1713.0	1687.5	1632.3	1587.3	1538.2	1468.7	1427.9
45°	1430.9	1469.7	1452.3	1449.3	1431.9	1412.5	1353.3	1329.7	1286.8	1221.4	1202.0
47.5°	1156.9	1164.2	1147.8	1148.8	1136.5	1123.2	1075.3	1060.9	1039.5	989.4	967.0
50°	862.7	867.8	854.5	858.5	850.4	842.2	809.4	802.3	789.0	755.3	742.1
52.5°	593.8	617.3	608.2	612.2	608.2	605.1	591.8	579.5	573.4	552.0	545.7
55°	429.3	431.4	424.1	428.3	425.1	424.1	416.0	408.8	405.7	392.6	390.4
57.5°	297.4	299.4	299.4	297.4	296.4	294.4	289.3	285.1	283.1	280.0	274.0
60°	197.2	205.5	202.4	204.5	203.4	203.4	199.2	196.2	195.2	189.1	189.1
62.5°	135.0	140.0	138.0	139.0	138.0	138.0	135.0	132.9	132.9	131.9	128.7
65°	89.9	93.0	90.9	91.9	91.9	91.9	89.9	87.9	87.9	86.9	84.9
67.5°	57.2	59.2	58.2	59.2	58.2	59.2	57.2	56.2	55.2	55.2	54.2
70°	34.8	35.8	34.8	35.8	34.8	34.8	33.7	33.7	32.7	31.7	31.7
72.5°	18.4	19.4	19.4	19.4	19.4	19.4	18.4	17.4	17.4	17.4	16.4
75°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	8.1	8.1	8.1
77.5°	4.1	4.1	4.1	4.1	5.1	4.1	4.1	4.1	4.1	4.1	4.1
80°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
82.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
85°	3.0	3.0	3.0	3.0	3.0	3.0	4.1	4.1	4.1	4.1	3.0
87.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.1	5.1	4.1	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1191610

CATALOG NUMBER: LDA4A20927D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	435.4	435.4	435.4	435.4	435.4	435.4	435.4	435.4	435.4	435.4	435.4
2.5°	543.7	538.7	536.6	532.6	527.4	524.3	521.3	522.3	515.2	510.0	502.9
5°	680.7	669.4	663.3	654.2	642.9	633.6	625.5	621.5	608.2	598.9	579.5
7.5°	842.2	822.7	810.6	794.2	774.7	758.5	742.1	730.8	710.4	693.0	663.3
10°	1019.0	989.4	968.0	943.4	913.7	887.2	862.7	842.2	811.6	785.0	746.1
12.5°	1212.3	1170.3	1139.6	1103.8	1062.0	1025.2	981.2	957.7	915.9	878.9	829.0
15°	1417.6	1362.4	1319.6	1270.5	1215.3	1166.2	1110.0	1075.3	1020.1	973.0	910.6
17.5°	1614.9	1545.4	1489.1	1426.8	1358.4	1294.9	1228.6	1179.5	1112.1	1053.7	979.1
20°	1786.7	1703.8	1635.4	1559.8	1479.0	1401.2	1328.7	1263.4	1184.6	1116.1	1031.3
22.5°	1926.7	1830.5	1751.9	1664.0	1570.9	1483.0	1400.2	1325.6	1235.7	1160.1	1067.0
25°	2027.8	1922.5	1834.6	1737.6	1635.4	1535.2	1447.3	1365.5	1267.4	1186.6	1087.4
27.5°	2080.9	1969.6	1876.6	1772.3	1664.0	1559.8	1464.6	1377.8	1274.5	1189.7	1087.4
30°	2071.8	1958.3	1862.3	1755.0	1645.5	1541.2	1442.2	1355.3	1249.0	1163.2	1060.9
32.5°	2001.3	1889.8	1795.8	1691.5	1584.2	1483.0	1383.8	1300.2	1193.9	1110.0	1010.8
35°	1884.7	1779.4	1690.5	1591.3	1490.3	1395.1	1305.2	1220.4	1118.1	1038.5	945.4
37.5°	1733.5	1637.4	1556.6	1464.6	1371.7	1285.8	1196.9	1124.4	1033.3	958.7	867.8
40°	1552.5	1467.7	1396.2	1314.3	1230.6	1155.9	1081.4	1010.8	921.9	855.5	777.9
42.5°	1353.3	1280.7	1219.4	1147.8	1075.3	1011.9	947.4	886.2	812.6	752.2	679.7
45°	1138.6	1077.3	1027.2	970.0	909.6	850.4	803.3	752.2	683.7	638.9	577.5
47.5°	916.9	869.8	832.0	788.0	739.9	703.1	658.3	617.3	567.3	525.3	475.2
50°	706.3	673.6	647.0	616.3	581.5	547.8	521.3	489.6	451.8	418.0	378.2
52.5°	522.3	500.9	484.5	464.1	440.5	423.1	398.6	375.2	346.5	320.9	290.3
55°	374.0	361.9	351.6	339.3	323.0	307.7	295.4	279.0	258.6	239.2	216.6
57.5°	268.7	255.6	254.6	241.2	235.0	223.9	212.6	200.4	186.1	172.7	156.4
60°	186.1	176.8	172.7	167.7	160.4	153.3	148.3	140.0	129.7	120.6	108.3
62.5°	125.7	119.6	117.6	115.5	109.3	106.3	100.2	95.0	87.9	80.8	72.5
65°	82.8	78.8	76.6	73.6	70.5	68.5	65.4	61.4	55.2	51.1	46.0
67.5°	52.1	49.1	47.1	46.0	42.9	41.8	38.8	36.8	32.7	30.7	27.7
70°	29.7	28.7	26.6	26.6	24.5	22.4	21.4	19.4	18.4	16.4	15.3
72.5°	15.3	15.3	14.3	13.3	12.3	12.3	11.3	10.3	9.3	8.1	8.1
75°	7.1	7.1	7.1	6.1	6.1	6.1	5.1	5.1	5.1	4.1	4.1
77.5°	4.1	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	2.0	2.0
80°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
82.5°	2.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
85°	3.0	2.0	2.0	2.0	2.0	3.0	3.0	3.0	3.0	3.0	3.0
87.5°	3.0	3.0	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1191610

CATALOG NUMBER: LDA4A20927D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	435.4	435.4	435.4	435.4	435.4	435.4	435.4	435.4	435.4	435.4	435.4
2.5°	497.8	495.6	490.6	489.6	478.3	476.2	470.2	460.9	453.8	451.8	453.8
5°	572.4	563.1	547.8	544.7	526.3	520.3	506.9	492.6	480.4	473.2	470.2
7.5°	649.0	633.6	611.2	599.9	573.4	560.1	540.7	520.3	500.9	487.5	479.4
10°	722.5	698.1	657.2	648.0	615.3	593.8	567.3	539.7	515.2	496.8	483.5
12.5°	792.1	762.5	720.5	695.0	652.0	624.5	590.8	557.0	526.3	501.9	483.5
15°	863.7	824.8	772.6	736.9	687.8	651.0	610.2	571.4	535.6	504.9	482.5
17.5°	922.9	874.9	813.6	770.6	713.4	669.4	622.5	577.5	538.7	503.9	478.3
20°	967.0	910.6	841.1	791.0	727.8	678.7	627.6	578.5	535.6	497.8	470.2
22.5°	996.5	932.2	856.5	801.3	734.9	681.7	626.5	575.4	531.6	492.6	463.1
25°	1010.8	941.3	862.7	803.3	733.8	678.7	621.5	569.3	524.3	484.5	455.8
27.5°	1008.8	935.3	854.5	792.1	721.5	664.3	606.1	554.0	510.0	470.2	440.5
30°	979.1	906.6	824.8	761.5	692.0	634.7	576.4	525.3	482.5	441.5	414.0
32.5°	933.2	858.5	778.9	708.4	649.0	592.8	537.6	485.5	444.7	404.7	378.2
35°	870.8	799.3	722.5	662.3	597.9	543.7	490.6	441.5	402.7	363.9	339.3
37.5°	798.3	729.8	659.3	596.9	540.7	490.6	440.5	396.6	357.8	323.0	299.4
40°	714.4	651.0	586.7	533.6	478.3	432.4	386.3	343.5	311.8	280.0	259.6
42.5°	623.5	567.3	509.0	463.1	413.0	372.0	328.1	297.4	266.7	238.2	221.8
45°	528.4	479.4	430.3	388.4	347.5	311.8	274.0	245.3	221.8	198.2	184.0
47.5°	434.4	392.6	352.6	318.8	283.1	253.5	226.9	201.4	178.8	159.4	148.3
50°	339.3	311.8	280.0	252.4	223.9	199.2	174.8	156.4	139.0	124.7	117.6
52.5°	264.7	239.2	213.6	191.1	170.7	150.3	133.9	118.6	106.3	97.2	91.9
55°	197.2	176.8	157.4	140.0	123.7	110.3	99.2	89.9	81.8	74.6	72.5
57.5°	141.0	125.7	112.4	99.2	88.9	80.8	73.6	67.5	62.4	57.2	56.2
60°	98.2	86.9	78.8	70.5	64.4	58.2	54.2	50.1	46.0	42.9	41.8
62.5°	65.4	59.2	53.1	49.1	46.0	40.8	38.8	35.8	33.7	30.7	29.7
65°	41.8	37.8	34.8	31.7	29.7	27.7	25.5	23.5	21.4	19.4	19.4
67.5°	25.5	22.4	21.4	19.4	17.4	16.4	15.3	13.3	12.3	12.3	11.3
70°	14.3	12.3	11.3	10.3	9.3	9.3	8.1	7.1	7.1	6.1	6.1
72.5°	7.1	7.1	6.1	6.1	5.1	5.1	4.1	4.1	4.1	3.0	3.0
75°	4.1	4.1	3.0	3.0	3.0	3.0	3.0	3.0	2.0	2.0	2.0
77.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
80°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
82.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
85°	3.0	3.0	3.0	3.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
87.5°	3.0	3.0	3.0	3.0	3.0	2.0	2.0	2.0	2.0	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191610

CATALOG NUMBER: LDA4A20927D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	112.5°	135°	157.5°	180°
0°	435.4	435.4	435.4	435.4	435.4	435.4	435.4	435.4
2.5°	445.7	435.4	433.4	433.4	390.4	364.9	345.5	340.4
5°	455.8	441.5	434.4	430.3	353.6	308.7	279.0	270.9
7.5°	460.9	440.5	429.3	420.1	317.8	259.6	227.9	218.8
10°	458.9	434.4	419.0	406.7	285.1	221.8	189.1	180.9
12.5°	454.8	427.3	407.8	392.6	257.6	192.1	162.5	154.4
15°	450.8	419.0	396.6	378.2	235.0	171.7	145.1	138.0
17.5°	442.5	409.9	384.3	364.9	220.8	163.5	141.0	137.0
20°	433.4	399.6	373.0	353.6	216.6	171.7	158.4	158.4
22.5°	427.3	392.6	366.9	347.5	223.9	191.1	186.1	189.1
25°	419.0	386.3	360.8	342.4	231.0	206.5	203.4	207.5
27.5°	405.7	373.0	348.5	330.1	226.9	204.5	201.4	203.4
30°	379.2	347.5	326.1	306.7	210.5	189.1	184.0	185.1
32.5°	345.5	314.8	294.4	276.0	187.1	166.7	161.5	161.5
35°	308.7	280.0	260.6	244.3	164.5	146.1	141.0	140.0
37.5°	271.9	245.3	228.9	213.6	144.1	127.7	122.6	121.6
40°	235.0	211.6	196.2	184.0	126.7	113.5	108.3	107.3
42.5°	200.4	179.8	166.7	156.4	110.3	100.2	96.1	95.0
45°	165.7	149.3	139.0	130.9	96.1	85.9	84.9	84.9
47.5°	133.9	120.6	113.5	108.3	81.8	73.6	72.5	73.6
50°	107.3	98.2	93.0	88.9	69.5	62.4	59.2	59.2
52.5°	84.9	78.8	75.6	72.5	57.2	50.1	46.0	45.0
55°	67.5	62.4	60.2	58.2	45.0	36.8	32.7	31.7
57.5°	53.1	49.1	47.1	45.0	33.7	25.5	21.4	20.4
60°	39.8	36.8	34.8	33.7	23.5	15.3	12.3	11.3
62.5°	28.7	26.6	24.5	23.5	14.3	8.1	5.1	4.1
65°	17.4	17.4	15.3	14.3	7.1	3.0	2.0	1.0
67.5°	10.3	9.3	8.1	8.1	3.0	2.0	1.0	1.0
70°	5.1	5.1	4.1	4.1	2.0	1.0	1.0	1.0
72.5°	3.0	3.0	3.0	2.0	2.0	1.0	1.0	1.0
75°	2.0	2.0	2.0	2.0	2.0	1.0	1.0	1.0
77.5°	2.0	2.0	2.0	2.0	2.0	1.0	1.0	0.0
80°	2.0	2.0	2.0	2.0	2.0	1.0	1.0	0.0
82.5°	2.0	2.0	2.0	2.0	2.0	1.0	1.0	1.0
85°	2.0	2.0	2.0	2.0	2.0	1.0	1.0	0.0
87.5°	2.0	2.0	2.0	2.0	2.0	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)