

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1191646

Luminaire Tested: **LDA4A20935D010TE LAR25NF 4LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1191646
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26102)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A20935D010TE LAR25NF 4LLWW1
Description: PORTFOLIO 4" Lensed Wall Wash, Self-flanged, 25° Narrow Flood Optic,
at 30° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1824.3 lumens
Efficiency: N/A
Efficacy: 63.3 lumens/watt
Spacing Criteria (0/90/45): 2.11 / 1.09 / 1.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1191646

CATALOG NUMBER: LDA4A20935D010TE LAR25NF 4LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191646

CATALOG NUMBER: LDA4A20935D010TE LAR25NF 4LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95
2	104	98	93	88	102	96	91	87	93	89	85		90	86	84		87
3	97	89	82	77	95	87	81	76	84	79	75		82	77	74		79
4	90	80	73	67	88	79	72	67	77	71	66		74	69	65		72
5	83	73	65	60	82	72	65	59	70	63	59		68	62	58		66
6	78	66	58	53	76	65	58	53	64	57	52		62	56	52		61
7	72	60	53	47	71	60	52	47	58	52	47		57	51	47		56
8	67	55	48	43	66	55	47	42	53	47	42		52	46	42		51
9	63	51	43	38	62	50	43	38	49	43	38		48	42	38		47
10	59	47	40	35	58	46	39	35	45	39	35		45	39	34		44

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	62388	62388	62388
5°	103783	61884	38953
10°	168046	59180	26315
15°	248498	56097	20470
20°	337553	53922	24152
25°	406385	54139	32813
30°	442208	50733	30608
35°	429250	42734	24484
40°	371835	34409	20079
45°	289967	26514	17199
50°	192314	19803	13221
55°	107244	14537	7914
60°	56542	9670	3207
65°	30499	4874	350
70°	14570	1731	433
75°	5099	1096	572
80°	1634	1634	0
85°	5095	3255	0



TEST NUMBER: P1191646

CATALOG NUMBER: LDA4A20935D010TE LAR25NF 4LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	3.0
10°-20°	212.9	11.7
20°-30°	437.9	24.0
30°-40°	523.1	28.7
40°-50°	386.3	21.2
50°-60°	162.6	8.9
60°-70°	40.0	2.2
70°-80°	5.5	0.3
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	704.8	38.6
0°-40°	1227.9	67.3
0°-60°	1776.8	97.4
0°-90°	1824.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1824.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	506	506	506	506	506	
5°	838	722	500	358	315	96
15°	1946	1249	439	200	160	571
25°	2986	1586	398	240	241	1366
35°	2851	1418	284	170	163	1748
45°	1662	874	152	100	99	1276
55°	499	324	68	43	37	476
65°	104	71	17	4	1	114
75°	11	6	2	1	1	15
85°	4	4	2	1	0	3
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191646

CATALOG NUMBER: LDA4A20935D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	657.8	649.4	649.4	651.9	659.0	653.0	648.3	643.5	648.3	637.5	641.2
5°	838.2	837.1	837.1	827.5	835.9	837.1	827.5	819.3	821.6	806.2	806.2
7.5°	1075.7	1068.6	1066.2	1053.1	1062.7	1061.5	1046.0	1031.8	1031.8	1006.8	1000.9
10°	1341.7	1332.2	1327.4	1310.7	1319.1	1314.3	1291.8	1270.5	1264.5	1228.9	1215.7
12.5°	1634.9	1629.0	1621.9	1600.5	1607.6	1598.1	1566.0	1535.2	1522.1	1474.6	1452.0
15°	1946.0	1955.5	1943.6	1918.7	1923.4	1906.9	1865.3	1822.4	1802.3	1738.2	1705.0
17.5°	2266.5	2278.4	2265.4	2236.9	2235.7	2213.1	2156.2	2103.9	2074.2	1992.3	1948.4
20°	2571.6	2575.3	2558.6	2527.8	2520.7	2489.8	2420.9	2347.3	2318.8	2217.9	2162.1
22.5°	2811.6	2824.6	2804.5	2781.9	2759.3	2720.0	2639.4	2558.6	2518.2	2403.1	2335.5
25°	2986.0	3015.7	2992.0	2965.9	2941.0	2894.7	2804.5	2717.7	2667.9	2539.6	2462.5
27.5°	3101.3	3129.7	3103.6	3073.9	3047.9	2994.4	2895.8	2812.7	2752.2	2612.0	2528.9
30°	3104.8	3139.2	3111.9	3079.9	3055.0	3001.5	2900.6	2815.0	2747.4	2607.3	2520.7
32.5°	3019.3	3046.6	3019.3	2992.0	2963.5	2912.5	2811.6	2729.6	2658.4	2524.1	2437.5
35°	2850.7	2874.4	2847.2	2815.0	2794.9	2749.7	2653.6	2575.3	2504.0	2380.5	2304.6
37.5°	2618.0	2639.4	2614.5	2596.7	2567.0	2526.6	2438.7	2368.6	2301.0	2189.4	2121.7
40°	2309.3	2354.4	2330.7	2318.8	2291.4	2257.1	2179.9	2118.1	2056.4	1959.0	1903.2
42.5°	2000.5	2043.4	2022.0	2013.7	1990.0	1960.3	1896.1	1843.9	1786.8	1706.2	1658.7
45°	1662.3	1707.3	1687.2	1683.6	1663.5	1640.9	1571.9	1544.7	1494.8	1418.9	1396.3
47.5°	1344.0	1352.3	1333.3	1334.5	1320.3	1304.8	1249.0	1232.4	1207.5	1149.3	1123.2
50°	1002.2	1008.1	992.6	997.4	987.8	978.4	940.3	932.1	916.6	877.5	862.0
52.5°	689.8	717.2	706.5	711.3	706.5	702.9	687.5	673.2	666.1	641.2	634.1
55°	498.7	501.0	492.8	497.5	493.9	492.8	483.2	474.9	471.3	456.0	453.5
57.5°	345.5	348.0	348.0	345.5	344.3	342.0	336.1	331.3	328.8	325.4	318.3
60°	229.2	238.6	235.2	237.5	236.3	236.3	231.5	227.9	226.8	219.7	219.7
62.5°	156.7	162.6	160.3	161.5	160.3	160.3	156.7	154.4	154.4	153.2	149.6
65°	104.5	108.0	105.7	106.9	106.9	106.9	104.5	102.1	102.1	100.9	98.6
67.5°	66.5	68.9	67.6	68.9	67.6	68.9	66.5	65.3	64.1	64.1	63.0
70°	40.4	41.6	40.4	41.6	40.4	40.4	39.2	39.2	37.9	36.8	36.8
72.5°	21.4	22.6	22.6	22.6	22.6	22.6	21.4	20.1	20.1	20.1	19.0
75°	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	9.6	9.6	9.6
77.5°	4.8	4.8	4.8	4.8	5.9	4.8	4.8	4.8	4.8	4.8	4.8
80°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
82.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
85°	3.6	3.6	3.6	3.6	3.6	3.6	4.8	4.8	4.8	4.8	3.6
87.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	5.9	5.9	4.8	4.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191646

CATALOG NUMBER: LDA4A20935D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	631.6	625.7	623.4	618.6	612.6	609.0	605.5	606.7	598.5	592.5	584.1
5°	790.7	777.7	770.6	759.9	746.9	736.2	726.6	721.8	706.5	695.8	673.2
7.5°	978.4	955.8	941.5	922.5	899.9	881.0	862.0	849.0	825.2	804.9	770.6
10°	1183.7	1149.3	1124.4	1095.8	1061.5	1030.5	1002.2	978.4	942.8	911.8	866.8
12.5°	1408.2	1359.5	1323.9	1282.3	1233.5	1190.8	1139.9	1112.5	1063.8	1021.1	962.9
15°	1646.8	1582.7	1532.8	1475.8	1411.6	1354.7	1289.4	1249.0	1184.9	1130.3	1057.9
17.5°	1875.9	1795.2	1729.9	1657.5	1577.9	1504.3	1427.1	1370.1	1291.8	1224.1	1137.4
20°	2075.4	1979.3	1899.6	1811.9	1718.0	1627.8	1543.6	1467.5	1376.0	1296.5	1197.9
22.5°	2238.0	2126.5	2035.0	1932.9	1824.9	1722.8	1626.7	1539.9	1435.4	1347.6	1239.5
25°	2355.6	2233.4	2131.2	2018.4	1899.6	1783.3	1681.3	1586.3	1472.3	1378.5	1263.2
27.5°	2417.4	2288.0	2179.9	2058.8	1932.9	1811.9	1701.4	1600.5	1480.6	1382.0	1263.2
30°	2406.7	2274.9	2163.3	2038.6	1911.5	1790.4	1675.3	1574.4	1450.9	1351.1	1232.4
32.5°	2324.7	2195.3	2086.1	1964.9	1840.3	1722.8	1607.6	1510.3	1386.7	1289.4	1174.2
35°	2189.4	2067.2	1963.8	1848.6	1731.1	1620.7	1516.2	1417.6	1298.8	1206.3	1098.3
37.5°	2013.7	1902.1	1808.2	1701.4	1593.4	1493.6	1390.4	1306.1	1200.4	1113.6	1008.1
40°	1803.5	1705.0	1621.9	1526.9	1429.5	1342.9	1256.1	1174.2	1070.9	993.8	903.5
42.5°	1571.9	1487.7	1416.4	1333.3	1249.0	1175.5	1100.6	1029.4	943.9	873.9	789.6
45°	1322.6	1251.4	1193.3	1126.7	1056.7	987.8	933.2	873.9	794.4	742.1	670.9
47.5°	1065.0	1010.4	966.5	915.4	859.7	816.8	764.7	717.2	659.0	610.3	552.1
50°	820.4	782.5	751.5	715.9	675.6	636.4	605.5	568.8	524.8	485.7	439.3
52.5°	606.7	581.8	562.8	539.1	511.7	491.6	463.1	435.7	402.5	372.9	337.2
55°	434.5	420.4	408.5	394.1	375.2	357.4	343.2	324.2	300.5	277.9	251.7
57.5°	312.3	296.8	295.7	280.2	273.1	260.1	247.0	232.7	216.0	200.7	181.7
60°	216.0	205.5	200.7	194.8	186.4	178.1	172.2	162.6	150.7	140.2	125.8
62.5°	146.1	138.9	136.5	134.2	127.0	123.5	116.4	110.5	102.1	93.8	84.3
65°	96.1	91.4	89.1	85.4	82.0	79.5	76.0	71.2	64.1	59.4	53.4
67.5°	60.5	57.1	54.6	53.4	49.8	48.7	45.2	42.7	37.9	35.6	32.0
70°	34.5	33.3	30.8	30.8	28.5	26.1	24.9	22.6	21.4	19.0	17.8
72.5°	17.8	17.8	16.7	15.5	14.2	14.2	13.0	11.9	10.7	9.6	9.6
75°	8.3	8.3	8.3	7.1	7.1	7.1	5.9	5.9	5.9	4.8	4.8
77.5°	4.8	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	2.3	2.3
80°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
82.5°	2.3	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
85°	3.6	2.3	2.3	2.3	2.3	3.6	3.6	3.6	3.6	3.6	3.6
87.5°	3.6	3.6	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1191646

CATALOG NUMBER: LDA4A20935D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	578.2	575.9	569.9	568.8	555.6	553.3	546.2	535.5	527.2	524.8	527.2
5°	664.9	654.2	636.4	632.8	611.5	604.4	588.9	572.2	558.1	549.7	546.2
7.5°	754.0	736.2	709.9	696.9	666.1	650.6	628.1	604.4	581.8	566.3	556.9
10°	839.4	810.9	763.4	752.8	714.7	689.8	659.0	626.8	598.5	577.0	561.5
12.5°	920.2	885.7	837.1	807.4	757.4	725.4	686.2	647.1	611.5	583.0	561.5
15°	1003.3	958.1	897.6	856.1	799.0	756.3	708.8	663.8	622.2	586.6	560.4
17.5°	1072.1	1016.3	945.1	895.3	828.7	777.7	723.1	670.9	625.7	585.3	555.6
20°	1123.2	1057.9	977.1	919.0	845.3	788.4	729.1	672.0	622.2	578.2	546.2
22.5°	1157.7	1082.8	994.9	930.9	853.7	791.9	727.8	668.4	617.4	572.2	537.8
25°	1174.2	1093.5	1002.2	933.2	852.4	788.4	721.8	661.3	609.0	562.8	529.5
27.5°	1171.9	1086.4	992.6	920.2	838.2	771.8	704.0	643.5	592.5	546.2	511.7
30°	1137.4	1053.1	958.1	884.6	803.8	737.3	669.7	610.3	560.4	512.9	480.9
32.5°	1084.0	997.4	904.7	822.7	754.0	688.7	624.5	564.0	516.5	470.2	439.3
35°	1011.6	928.5	839.4	769.3	694.6	631.6	569.9	512.9	467.8	422.7	394.1
37.5°	927.3	847.8	765.8	693.4	628.1	569.9	511.7	460.6	415.6	375.2	348.0
40°	830.0	756.3	681.6	619.7	555.6	502.2	448.7	398.9	362.1	325.4	301.6
42.5°	724.3	659.0	591.2	537.8	479.7	432.2	381.1	345.5	309.9	276.7	257.6
45°	613.8	556.9	499.8	451.2	403.7	362.1	318.3	285.0	257.6	230.4	213.7
47.5°	504.6	456.0	409.6	370.4	328.8	294.5	263.5	233.9	207.8	185.2	172.2
50°	394.1	362.1	325.4	293.2	260.1	231.5	203.0	181.7	161.5	144.8	136.5
52.5°	307.6	277.9	248.2	222.0	198.2	174.5	155.5	137.7	123.5	112.8	106.9
55°	229.2	205.5	182.9	162.6	143.6	128.3	115.1	104.5	95.0	86.7	84.3
57.5°	163.9	146.1	130.6	115.1	103.2	93.8	85.4	78.3	72.4	66.5	65.3
60°	114.0	100.9	91.4	82.0	74.9	67.6	63.0	58.2	53.4	49.8	48.7
62.5°	76.0	68.9	61.7	57.1	53.4	47.5	45.2	41.6	39.2	35.6	34.5
65°	48.7	43.9	40.4	36.8	34.5	32.0	29.7	27.4	24.9	22.6	22.6
67.5°	29.7	26.1	24.9	22.6	20.1	19.0	17.8	15.5	14.2	14.2	13.0
70°	16.7	14.2	13.0	11.9	10.7	10.7	9.6	8.3	8.3	7.1	7.1
72.5°	8.3	8.3	7.1	7.1	5.9	5.9	4.8	4.8	4.8	3.6	3.6
75°	4.8	4.8	3.6	3.6	3.6	3.6	3.6	3.6	2.3	2.3	2.3
77.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
80°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
82.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
85°	3.6	3.6	3.6	3.6	2.3	2.3	2.3	2.3	2.3	2.3	2.3
87.5°	3.6	3.6	3.6	3.6	3.6	2.3	2.3	2.3	2.3	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191646

CATALOG NUMBER: LDA4A20935D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	112.5°	135°	157.5°	180°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	517.7	505.8	503.5	503.5	453.5	423.8	401.2	395.3
5°	529.5	512.9	504.6	499.8	410.8	358.5	324.2	314.6
7.5°	535.5	511.7	498.7	488.0	369.2	301.6	264.8	254.1
10°	533.1	504.6	486.8	472.5	331.3	257.6	219.7	210.1
12.5°	528.4	496.2	473.8	456.0	299.2	223.3	188.8	179.3
15°	523.6	486.8	460.6	439.3	273.1	199.5	168.5	160.3
17.5°	514.0	476.1	446.4	423.8	256.4	190.0	163.9	159.1
20°	503.5	464.2	433.4	410.8	251.7	199.5	184.0	184.0
22.5°	496.2	456.0	426.3	403.7	260.1	222.0	216.0	219.7
25°	486.8	448.7	419.0	397.8	268.3	239.8	236.3	241.1
27.5°	471.3	433.4	404.9	383.4	263.5	237.5	233.9	236.3
30°	440.5	403.7	378.8	356.2	244.6	219.7	213.7	214.9
32.5°	401.2	365.6	342.0	320.6	217.3	193.6	187.7	187.7
35°	358.5	325.4	302.8	283.8	191.1	169.8	163.9	162.6
37.5°	315.8	285.0	266.0	248.2	167.4	148.4	142.5	141.3
40°	273.1	245.7	227.9	213.7	147.3	131.8	125.8	124.7
42.5°	232.7	208.9	193.6	181.7	128.3	116.4	111.6	110.5
45°	192.3	173.3	161.5	152.0	111.6	99.8	98.6	98.6
47.5°	155.5	140.2	131.8	125.8	95.0	85.4	84.3	85.4
50°	124.7	114.0	108.0	103.2	80.8	72.4	68.9	68.9
52.5°	98.6	91.4	87.9	84.3	66.5	58.2	53.4	52.3
55°	78.3	72.4	70.1	67.6	52.3	42.7	37.9	36.8
57.5°	61.7	57.1	54.6	52.3	39.2	29.7	24.9	23.7
60°	46.3	42.7	40.4	39.2	27.4	17.8	14.2	13.0
62.5°	33.3	30.8	28.5	27.4	16.7	9.6	5.9	4.8
65°	20.1	20.1	17.8	16.7	8.3	3.6	2.3	1.2
67.5°	11.9	10.7	9.6	9.6	3.6	2.3	1.2	1.2
70°	5.9	5.9	4.8	4.8	2.3	1.2	1.2	1.2
72.5°	3.6	3.6	3.6	2.3	2.3	1.2	1.2	1.2
75°	2.3	2.3	2.3	2.3	2.3	1.2	1.2	1.2
77.5°	2.3	2.3	2.3	2.3	2.3	1.2	1.2	0.0
80°	2.3	2.3	2.3	2.3	2.3	1.2	1.2	0.0
82.5°	2.3	2.3	2.3	2.3	2.3	1.2	1.2	1.2
85°	2.3	2.3	2.3	2.3	2.3	1.2	1.2	0.0
87.5°	2.3	2.3	2.3	2.3	2.3	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)