

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1191520

Luminaire Tested: **LDA4A15927D010TE LAR25NF 4LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1191520
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26102)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A15927D010TE LAR25NF 4LLWW1
Description: PORTFOLIO 4" Lensed Wall Wash, Self-flanged, 25° Narrow Flood Optic,
at 30° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1193.7 lumens
Efficiency: N/A
Efficacy: 58.5 lumens/watt
Spacing Criteria (0/90/45): 2.11 / 1.09 / 1.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1191520

CATALOG NUMBER: LDA4A15927D010TE LAR25NF 4LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191520

CATALOG NUMBER: LDA4A15927D010TE LAR25NF 4LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80		
3	97	89	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71		
4	90	80	73	67	88	79	72	67	77	71	66	74	69	65	72	68	65	63		
5	83	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56		
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	61	55	52	50		
7	72	60	53	47	71	60	52	47	58	52	47	57	51	47	56	50	46	45		
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40		
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36		
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	40827	40827	40827
5°	67914	40500	25494
10°	109956	38739	17222
15°	162609	36713	13395
20°	220900	35283	15804
25°	265933	35426	21476
30°	289369	33186	20025
35°	280902	27962	16036
40°	243328	22526	13123
45°	189718	17339	11251
50°	125843	12972	8635
55°	70170	9527	5183
60°	37004	6315	2122
65°	19934	3181	233
70°	9557	1118	289
75°	3336	715	381
80°	1065	1065	0
85°	3255	2123	0

TEST NUMBER: P1191520

CATALOG NUMBER: LDA4A15927D010TE LAR25NF 4LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.3	3.0
10°-20°	139.3	11.7
20°-30°	286.6	24.0
30°-40°	342.3	28.7
40°-50°	252.8	21.2
50°-60°	106.4	8.9
60°-70°	26.1	2.2
70°-80°	3.6	0.3
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	461.2	38.6
0°-40°	803.5	67.3
0°-60°	1162.6	97.4
0°-90°	1193.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1193.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	331	331	331	331	331	
5°	548	472	327	235	206	63
15°	1273	817	288	130	105	374
25°	1954	1038	260	157	158	894
35°	1866	928	186	111	106	1144
45°	1088	572	99	65	64	835
55°	326	212	44	28	24	311
65°	68	47	11	2	1	74
75°	7	4	2	1	1	10
85°	2	2	2	1	0	2
90°	0	0	0	0	0	

TEST NUMBER: P1191520

CATALOG NUMBER: LDA4A15927D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	331.0	331.0	331.0	331.0	331.0	331.0	331.0	331.0	331.0	331.0	331.0
2.5°	430.4	425.0	425.0	426.5	431.2	427.4	424.2	421.1	424.2	417.3	419.6
5°	548.5	547.8	547.8	541.5	547.0	547.8	541.5	536.0	537.7	527.6	527.6
7.5°	703.9	699.3	697.6	689.2	695.3	694.6	684.4	675.1	675.1	658.8	655.0
10°	877.9	871.8	868.6	857.7	863.2	860.0	845.3	831.3	827.5	804.1	795.5
12.5°	1069.8	1066.0	1061.3	1047.3	1051.9	1045.8	1024.8	1004.6	996.0	964.9	950.2
15°	1273.4	1279.6	1271.9	1255.5	1258.6	1247.7	1220.6	1192.6	1179.4	1137.4	1115.7
17.5°	1483.1	1490.9	1482.4	1463.7	1462.9	1448.2	1411.0	1376.7	1357.2	1303.6	1275.0
20°	1682.9	1685.2	1674.3	1654.1	1649.5	1629.3	1584.1	1536.0	1517.3	1451.3	1414.8
22.5°	1839.8	1848.3	1835.1	1820.3	1805.6	1780.0	1727.1	1674.3	1647.8	1572.5	1528.2
25°	1954.0	1973.5	1957.9	1940.7	1924.5	1894.1	1835.1	1778.5	1745.7	1661.9	1611.4
27.5°	2029.4	2048.1	2030.9	2011.5	1994.3	1959.4	1894.9	1840.5	1801.0	1709.2	1654.9
30°	2031.7	2054.2	2036.3	2015.3	1999.1	1964.1	1898.1	1842.1	1797.8	1706.2	1649.5
32.5°	1975.8	1993.6	1975.8	1957.9	1939.2	1905.8	1839.8	1786.1	1739.6	1651.8	1595.0
35°	1865.5	1881.0	1863.1	1842.1	1828.9	1799.3	1736.5	1685.2	1638.5	1557.7	1508.0
37.5°	1713.1	1727.1	1710.8	1699.1	1679.7	1653.3	1595.9	1549.9	1505.7	1432.6	1388.3
40°	1511.2	1540.6	1525.1	1517.3	1499.5	1477.0	1426.5	1386.0	1345.6	1282.0	1245.4
42.5°	1309.1	1337.0	1323.1	1317.7	1302.1	1282.8	1240.8	1206.5	1169.3	1116.4	1085.3
45°	1087.6	1117.2	1104.0	1101.7	1088.5	1073.7	1028.6	1010.7	978.1	928.4	913.6
47.5°	879.5	884.9	872.5	873.3	864.0	853.9	817.4	806.5	790.1	752.0	735.0
50°	655.8	659.6	649.5	652.6	646.4	640.2	615.3	610.0	599.7	574.1	564.0
52.5°	451.4	469.2	462.3	465.4	462.3	460.0	449.9	440.5	435.8	419.6	414.8
55°	326.3	327.8	322.4	325.5	323.2	322.4	316.2	310.8	308.5	298.4	296.7
57.5°	226.1	227.6	227.6	226.1	225.3	223.8	219.8	216.8	215.2	212.9	208.2
60°	150.0	156.1	153.8	155.3	154.6	154.6	151.5	149.2	148.4	143.7	143.7
62.5°	102.5	106.5	104.9	105.7	104.9	104.9	102.5	101.0	101.0	100.2	97.9
65°	68.3	70.6	69.1	70.0	70.0	70.0	68.3	66.8	66.8	66.0	64.5
67.5°	43.5	45.0	44.3	45.0	44.3	45.0	43.5	42.7	42.0	42.0	41.2
70°	26.5	27.1	26.5	27.1	26.5	26.5	25.6	25.6	24.8	24.1	24.1
72.5°	14.0	14.7	14.7	14.7	14.7	14.7	14.0	13.2	13.2	13.2	12.4
75°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	6.3	6.3	6.3
77.5°	3.1	3.1	3.1	3.1	3.8	3.1	3.1	3.1	3.1	3.1	3.1
80°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
82.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
85°	2.3	2.3	2.3	2.3	2.3	2.3	3.1	3.1	3.1	3.1	2.3
87.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.8	3.8	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1191520

CATALOG NUMBER: LDA4A15927D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	331.0	331.0	331.0	331.0	331.0	331.0	331.0	331.0	331.0	331.0	331.0
2.5°	413.3	409.5	407.9	404.7	400.9	398.6	396.3	397.0	391.6	387.7	382.2
5°	517.5	508.9	504.3	497.2	488.7	481.6	475.5	472.4	462.3	455.3	440.5
7.5°	640.2	625.4	616.1	603.7	589.0	576.5	564.0	555.5	540.0	526.8	504.3
10°	774.5	752.0	735.8	717.1	694.6	674.3	655.8	640.2	616.9	596.7	567.1
12.5°	921.4	889.6	866.3	839.0	807.3	779.3	745.9	728.0	696.1	668.2	630.1
15°	1077.5	1035.7	1003.0	965.7	923.7	886.5	843.7	817.4	775.4	739.6	692.2
17.5°	1227.5	1174.8	1132.0	1084.6	1032.5	984.4	933.8	896.6	845.3	801.0	744.3
20°	1358.0	1295.2	1243.1	1185.5	1124.2	1065.1	1010.0	960.3	900.4	848.5	784.0
22.5°	1464.5	1391.5	1331.6	1264.8	1194.1	1127.3	1064.5	1007.7	939.3	881.9	811.1
25°	1541.5	1461.4	1394.6	1320.8	1243.1	1167.0	1100.2	1038.0	963.4	902.0	826.6
27.5°	1581.8	1497.1	1426.5	1347.1	1264.8	1185.5	1113.3	1047.3	968.9	904.4	826.6
30°	1574.9	1488.5	1415.6	1334.0	1250.9	1171.6	1096.2	1030.2	949.4	884.2	806.5
32.5°	1521.3	1436.6	1365.0	1285.8	1204.2	1127.3	1051.9	988.2	907.5	843.7	768.4
35°	1432.6	1352.6	1285.1	1209.7	1132.8	1060.5	992.2	927.7	850.0	789.4	718.6
37.5°	1317.7	1244.6	1183.2	1113.3	1042.6	977.3	909.8	854.6	785.5	728.7	659.6
40°	1180.1	1115.7	1061.3	999.1	935.5	878.7	822.0	768.4	700.8	650.3	591.3
42.5°	1028.6	973.5	926.9	872.5	817.4	769.2	720.3	673.6	617.6	571.8	516.7
45°	865.5	818.9	780.8	737.3	691.5	646.4	610.6	571.8	519.8	485.6	439.0
47.5°	697.0	661.2	632.5	599.0	562.5	534.5	500.3	469.2	431.2	399.4	361.2
50°	536.9	512.0	491.9	468.5	442.1	416.5	396.3	372.1	343.4	317.7	287.5
52.5°	397.0	380.7	368.3	352.8	334.9	321.7	303.0	285.1	263.3	244.0	220.6
55°	284.3	275.0	267.3	258.0	245.5	233.9	224.6	212.0	196.5	181.8	164.7
57.5°	204.3	194.2	193.5	183.4	178.6	170.2	161.6	152.3	141.4	131.3	118.9
60°	141.4	134.5	131.3	127.4	122.0	116.6	112.6	106.5	98.7	91.6	82.4
62.5°	95.6	91.0	89.3	87.8	83.2	80.9	76.1	72.3	66.8	61.4	55.2
65°	62.9	59.9	58.2	55.9	53.6	52.1	49.8	46.6	42.0	38.9	34.9
67.5°	39.7	37.2	35.7	34.9	32.6	31.9	29.6	28.0	24.8	23.3	21.0
70°	22.5	21.8	20.2	20.2	18.7	17.0	16.4	14.7	14.0	12.4	11.6
72.5°	11.6	11.6	10.9	10.1	9.3	9.3	8.6	7.8	7.0	6.3	6.3
75°	5.5	5.5	5.5	4.6	4.6	4.6	3.8	3.8	3.8	3.1	3.1
77.5°	3.1	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	1.5	1.5
80°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
82.5°	1.5	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
85°	2.3	1.5	1.5	1.5	1.5	2.3	2.3	2.3	2.3	2.3	2.3
87.5°	2.3	2.3	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191520

CATALOG NUMBER: LDA4A15927D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	331.0	331.0	331.0	331.0	331.0	331.0	331.0	331.0	331.0	331.0	331.0
2.5°	378.4	376.8	373.0	372.1	363.5	362.0	357.4	350.5	345.0	343.4	345.0
5°	435.1	428.0	416.5	414.1	400.1	395.5	385.4	374.5	365.2	359.7	357.4
7.5°	493.4	481.6	464.6	456.0	435.8	425.7	411.0	395.5	380.7	370.6	364.4
10°	549.3	530.6	499.5	492.5	467.7	451.4	431.2	410.2	391.6	377.6	367.5
12.5°	602.2	579.5	547.8	528.3	495.7	474.7	449.0	423.4	400.1	381.4	367.5
15°	656.5	627.0	587.3	560.2	522.8	494.9	463.8	434.3	407.0	383.9	366.7
17.5°	701.6	665.0	618.4	585.8	542.3	508.9	473.2	439.0	409.5	383.0	363.5
20°	735.0	692.2	639.4	601.4	553.2	515.9	477.0	439.8	407.0	378.4	357.4
22.5°	757.5	708.5	651.0	609.1	558.5	518.2	476.3	437.5	404.0	374.5	352.0
25°	768.4	715.5	655.8	610.6	557.9	515.9	472.4	432.7	398.6	368.3	346.5
27.5°	766.8	710.9	649.5	602.2	548.5	505.0	460.8	421.1	387.7	357.4	334.9
30°	744.3	689.2	627.0	578.9	526.0	482.5	438.1	399.4	366.7	335.6	314.6
32.5°	709.4	652.6	592.0	538.4	493.4	450.7	408.7	369.0	337.9	307.6	287.5
35°	661.9	607.5	549.3	503.5	454.5	413.3	373.0	335.6	306.1	276.5	258.0
37.5°	606.8	554.7	501.1	453.7	411.0	373.0	334.9	301.5	271.9	245.5	227.6
40°	543.1	494.9	445.9	405.5	363.5	328.6	293.7	261.0	237.0	212.9	197.3
42.5°	473.9	431.2	386.9	352.0	313.9	282.8	249.4	226.1	202.8	181.1	168.5
45°	401.7	364.4	327.1	295.2	264.1	237.0	208.2	186.4	168.5	150.7	139.9
47.5°	330.1	298.4	268.1	242.5	215.2	192.7	172.5	153.0	136.0	121.2	112.6
50°	258.0	237.0	212.9	191.9	170.2	151.5	132.8	118.9	105.7	94.8	89.3
52.5°	201.3	181.8	162.4	145.2	129.7	114.3	101.7	90.1	80.9	73.8	70.0
55°	150.0	134.5	119.6	106.5	94.0	83.9	75.4	68.3	62.2	56.7	55.2
57.5°	107.2	95.6	85.5	75.4	67.6	61.4	55.9	51.3	47.5	43.5	42.7
60°	74.6	66.0	59.9	53.6	49.0	44.3	41.2	38.0	34.9	32.6	31.9
62.5°	49.8	45.0	40.4	37.2	34.9	31.1	29.6	27.1	25.6	23.3	22.5
65°	31.9	28.8	26.5	24.1	22.5	21.0	19.4	17.9	16.4	14.7	14.7
67.5°	19.4	17.0	16.4	14.7	13.2	12.4	11.6	10.1	9.3	9.3	8.6
70°	10.9	9.3	8.6	7.8	7.0	7.0	6.3	5.5	5.5	4.6	4.6
72.5°	5.5	5.5	4.6	4.6	3.8	3.8	3.1	3.1	3.1	2.3	2.3
75°	3.1	3.1	2.3	2.3	2.3	2.3	2.3	2.3	1.5	1.5	1.5
77.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
80°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
82.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
85°	2.3	2.3	2.3	2.3	1.5	1.5	1.5	1.5	1.5	1.5	1.5
87.5°	2.3	2.3	2.3	2.3	2.3	1.5	1.5	1.5	1.5	1.5	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191520

CATALOG NUMBER: LDA4A15927D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	112.5°	135°	157.5°	180°
0°	331.0	331.0	331.0	331.0	331.0	331.0	331.0	331.0
2.5°	338.7	331.0	329.5	329.5	296.7	277.4	262.6	258.7
5°	346.5	335.6	330.1	327.1	268.8	234.7	212.0	205.9
7.5°	350.5	334.9	326.3	319.4	241.6	197.3	173.3	166.2
10°	348.8	330.1	318.5	309.3	216.8	168.5	143.7	137.5
12.5°	345.7	324.8	310.0	298.4	195.8	146.0	123.5	117.3
15°	342.7	318.5	301.5	287.5	178.6	130.5	110.3	104.9
17.5°	336.4	311.6	292.1	277.4	167.9	124.4	107.2	104.0
20°	329.5	303.8	283.6	268.8	164.7	130.5	120.4	120.4
22.5°	324.8	298.4	278.9	264.1	170.2	145.2	141.4	143.7
25°	318.5	293.7	274.2	260.3	175.6	157.0	154.6	157.8
27.5°	308.5	283.6	265.0	250.9	172.5	155.3	153.0	154.6
30°	288.3	264.1	247.8	233.0	160.1	143.7	139.9	140.6
32.5°	262.6	239.3	223.8	209.7	142.2	126.7	122.7	122.7
35°	234.7	212.9	198.1	185.7	125.0	111.1	107.2	106.5
37.5°	206.7	186.4	174.0	162.4	109.5	97.1	93.3	92.5
40°	178.6	160.8	149.2	139.9	96.3	86.2	82.4	81.5
42.5°	152.3	136.8	126.7	118.9	83.9	76.1	73.1	72.3
45°	125.9	113.5	105.7	99.4	73.1	65.3	64.5	64.5
47.5°	101.7	91.6	86.2	82.4	62.2	55.9	55.2	55.9
50°	81.5	74.6	70.6	67.6	52.8	47.5	45.0	45.0
52.5°	64.5	59.9	57.5	55.2	43.5	38.0	34.9	34.2
55°	51.3	47.5	45.8	44.3	34.2	28.0	24.8	24.1
57.5°	40.4	37.2	35.7	34.2	25.6	19.4	16.4	15.5
60°	30.3	28.0	26.5	25.6	17.9	11.6	9.3	8.6
62.5°	21.8	20.2	18.7	17.9	10.9	6.3	3.8	3.1
65°	13.2	13.2	11.6	10.9	5.5	2.3	1.5	0.8
67.5°	7.8	7.0	6.3	6.3	2.3	1.5	0.8	0.8
70°	3.8	3.8	3.1	3.1	1.5	0.8	0.8	0.8
72.5°	2.3	2.3	2.3	1.5	1.5	0.8	0.8	0.8
75°	1.5	1.5	1.5	1.5	1.5	0.8	0.8	0.8
77.5°	1.5	1.5	1.5	1.5	1.5	0.8	0.8	0.0
80°	1.5	1.5	1.5	1.5	1.5	0.8	0.8	0.0
82.5°	1.5	1.5	1.5	1.5	1.5	0.8	0.8	0.8
85°	1.5	1.5	1.5	1.5	1.5	0.8	0.8	0.0
87.5°	1.5	1.5	1.5	1.5	1.5	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)