

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1191538

Luminaire Tested: **LDA4A15930D010TE LAR25NF 4LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1191538
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26102)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A15930D010TE LAR25NF 4LLWW1
Description: PORTFOLIO 4" Lensed Wall Wash, Self-flanged, 25° Narrow Flood Optic,
at 30° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1376.2 lumens
Efficiency: N/A
Efficacy: 67.5 lumens/watt
Spacing Criteria (0/90/45): 2.11 / 1.09 / 1.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1191538

CATALOG NUMBER: LDA4A15930D010TE LAR25NF 4LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191538

CATALOG NUMBER: LDA4A15930D010TE LAR25NF 4LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	108	105	102	109	106	103	101		102	100	98		98	96	95		95	93	92
2	104	98	93	88	102	96	91	87		93	89	85		90	86	84		87	84	82
3	97	89	82	77	95	87	81	76		84	79	75		82	77	74		79	76	73
4	90	80	73	67	88	79	72	67		77	71	66		74	69	65		72	68	65
5	83	73	65	60	82	72	65	59		70	63	59		68	62	58		66	61	58
6	78	66	58	53	76	65	58	53		64	57	52		62	56	52		61	55	52
7	72	60	53	47	71	60	52	47		58	52	47		57	51	47		56	50	46
8	67	55	48	43	66	55	47	42		53	47	42		52	46	42		51	46	42
9	63	51	43	38	62	50	43	38		49	43	38		48	42	38		47	42	38
10	59	47	40	35	58	46	39	35		45	39	35		45	39	34		44	38	34

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	47056	47056	47056
5°	78289	46679	29382
10°	126764	44651	19852
15°	187433	42319	15451
20°	254635	40665	18219
25°	306558	40829	24742
30°	333579	38256	23087
35°	323786	32239	18476
40°	280474	25956	15152
45°	218727	20008	12961
50°	145051	14948	9978
55°	80879	10967	5978
60°	42653	7302	2418
65°	22999	3648	292
70°	10963	1262	361
75°	3813	858	477
80°	1279	1279	0
85°	3821	2547	0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191538

CATALOG NUMBER: LDA4A15930D010TE LAR25NF 4LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.7	3.0
10°-20°	160.6	11.7
20°-30°	330.3	24.0
30°-40°	394.6	28.7
40°-50°	291.4	21.2
50°-60°	122.6	8.9
60°-70°	30.2	2.2
70°-80°	4.2	0.3
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	531.7	38.6
0°-40°	926.2	67.3
0°-60°	1340.2	97.4
0°-90°	1376.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1376.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	382	382	382	382	382	
5°	632	544	377	270	237	72
15°	1468	942	331	150	121	431
25°	2252	1196	300	181	182	1030
35°	2150	1069	214	128	123	1319
45°	1254	659	115	75	74	963
55°	376	244	51	32	28	359
65°	79	54	12	3	1	86
75°	8	4	2	1	1	11
85°	3	3	2	1	0	2
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191538

CATALOG NUMBER: LDA4A15930D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	381.5	381.5	381.5	381.5	381.5	381.5	381.5	381.5	381.5	381.5	381.5
2.5°	496.2	490.0	490.0	491.7	497.0	492.5	489.0	485.5	489.0	481.0	483.7
5°	632.3	631.4	631.4	624.3	630.5	631.4	624.3	618.0	619.8	608.0	608.0
7.5°	811.4	806.0	804.3	794.5	801.5	800.7	789.0	778.2	778.2	759.4	755.0
10°	1012.1	1004.9	1001.3	988.8	995.0	991.4	974.5	958.2	953.9	927.0	917.0
12.5°	1233.3	1228.8	1223.3	1207.2	1212.7	1205.5	1181.3	1158.0	1148.2	1112.3	1095.3
15°	1467.8	1475.0	1466.0	1447.2	1450.9	1438.4	1407.0	1374.7	1359.5	1311.1	1286.0
17.5°	1709.7	1718.6	1708.8	1687.4	1686.4	1669.4	1626.4	1587.0	1564.6	1502.9	1469.7
20°	1939.9	1942.5	1930.0	1906.8	1901.3	1878.0	1826.2	1770.6	1749.1	1672.9	1630.9
22.5°	2120.7	2130.7	2115.4	2098.4	2081.3	2051.9	1990.9	1930.0	1899.6	1812.7	1761.7
25°	2252.5	2274.8	2257.0	2237.2	2218.4	2183.5	2115.4	2050.0	2012.5	1915.6	1857.4
27.5°	2339.3	2360.7	2341.1	2318.7	2299.0	2258.7	2184.4	2121.7	2076.0	1970.3	1907.6
30°	2342.1	2368.0	2347.4	2323.2	2304.4	2264.1	2188.0	2123.5	2072.5	1966.8	1901.3
32.5°	2277.6	2298.1	2277.6	2257.0	2235.4	2197.0	2120.7	2059.0	2005.2	1904.1	1838.7
35°	2150.3	2168.2	2147.6	2123.5	2108.2	2074.2	2001.7	1942.5	1888.8	1795.6	1738.4
37.5°	1974.8	1990.9	1972.1	1958.7	1936.2	1905.8	1839.6	1786.8	1735.6	1651.5	1600.4
40°	1741.9	1776.0	1758.0	1749.1	1728.6	1702.5	1644.3	1597.8	1551.1	1477.8	1435.6
42.5°	1509.1	1541.3	1525.2	1519.0	1501.0	1478.6	1430.3	1390.9	1347.8	1287.0	1251.1
45°	1253.9	1287.8	1272.7	1270.0	1254.7	1237.8	1185.8	1165.2	1127.6	1070.2	1053.3
47.5°	1013.9	1020.1	1005.8	1006.6	995.9	984.3	942.1	929.6	910.8	867.0	847.2
50°	755.9	760.4	748.8	752.3	745.1	738.0	709.4	703.1	691.4	661.9	650.2
52.5°	520.4	541.0	532.9	536.5	532.9	530.2	518.6	507.8	502.4	483.7	478.2
55°	376.1	378.0	371.7	375.3	372.5	371.7	364.5	358.2	355.5	343.9	342.1
57.5°	260.6	262.4	262.4	260.6	259.8	257.9	253.5	249.8	248.0	245.5	240.0
60°	172.9	180.0	177.3	179.2	178.2	178.2	174.7	172.0	171.0	165.7	165.7
62.5°	118.2	122.7	121.0	121.8	121.0	121.0	118.2	116.5	116.5	115.5	112.9
65°	78.8	81.5	79.8	80.6	80.6	80.6	78.8	77.0	77.0	76.1	74.3
67.5°	50.2	52.0	51.0	52.0	51.0	52.0	50.2	49.2	48.4	48.4	47.5
70°	30.4	31.4	30.4	31.4	30.4	30.4	29.6	29.6	28.6	27.8	27.8
72.5°	16.1	17.0	17.0	17.0	17.0	17.0	16.1	15.3	15.3	15.3	14.3
75°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	7.2	7.2	7.2
77.5°	3.5	3.5	3.5	3.5	4.5	3.5	3.5	3.5	3.5	3.5	3.5
80°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
82.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
85°	2.7	2.7	2.7	2.7	2.7	2.7	3.5	3.5	3.5	3.5	2.7
87.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	4.5	4.5	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1191538

CATALOG NUMBER: LDA4A15930D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	381.5	381.5	381.5	381.5	381.5	381.5	381.5	381.5	381.5	381.5	381.5
2.5°	476.5	472.0	470.2	466.6	462.1	459.4	456.8	457.6	451.4	446.9	440.6
5°	596.5	586.6	581.2	573.1	563.3	555.3	548.0	544.5	532.9	524.9	507.8
7.5°	738.0	721.0	710.2	695.9	678.8	664.5	650.2	640.4	622.5	607.2	581.2
10°	892.9	867.0	848.2	826.6	800.7	777.4	755.9	738.0	711.1	687.8	653.7
12.5°	1062.1	1025.5	998.6	967.2	930.5	898.2	859.8	839.2	802.5	770.2	726.3
15°	1242.1	1193.9	1156.2	1113.3	1064.9	1021.9	972.7	942.1	893.9	852.5	798.0
17.5°	1415.0	1354.1	1304.9	1250.3	1190.2	1134.7	1076.5	1033.5	974.5	923.3	858.0
20°	1565.5	1492.9	1432.9	1366.6	1295.9	1227.8	1164.3	1107.0	1038.0	978.0	903.7
22.5°	1688.2	1604.0	1535.0	1458.0	1376.6	1299.5	1227.0	1161.5	1082.7	1016.5	935.0
25°	1776.8	1684.6	1607.6	1522.5	1432.9	1345.2	1268.2	1196.5	1110.5	1039.8	952.9
27.5°	1823.5	1725.8	1644.3	1552.9	1458.0	1366.6	1283.5	1207.2	1116.8	1042.5	952.9
30°	1815.4	1716.0	1631.7	1537.8	1441.9	1350.5	1263.7	1187.6	1094.5	1019.2	929.6
32.5°	1753.6	1656.0	1573.5	1482.3	1388.2	1299.5	1212.7	1139.2	1046.0	972.7	885.7
35°	1651.5	1559.2	1481.3	1394.5	1305.8	1222.5	1143.7	1069.4	979.8	910.0	828.4
37.5°	1519.0	1434.7	1364.0	1283.5	1201.9	1126.6	1048.8	985.1	905.5	840.1	760.4
40°	1360.4	1286.0	1223.3	1151.7	1078.4	1012.9	947.6	885.7	807.8	749.6	681.5
42.5°	1185.8	1122.1	1068.4	1005.8	942.1	886.6	830.2	776.5	712.0	659.2	595.6
45°	997.6	943.9	900.1	850.0	797.0	745.1	703.9	659.2	599.2	559.8	506.0
47.5°	803.3	762.1	729.0	690.5	648.4	616.2	576.8	541.0	497.0	460.4	416.5
50°	618.8	590.2	566.9	540.0	509.6	480.0	456.8	429.0	395.9	366.3	331.4
52.5°	457.6	438.8	424.5	406.6	386.0	370.8	349.2	328.6	303.5	281.2	254.3
55°	327.8	317.0	308.0	297.3	283.0	269.6	258.8	244.5	226.6	209.6	189.8
57.5°	235.5	223.9	223.0	211.4	206.0	196.1	186.3	175.5	163.0	151.4	137.0
60°	163.0	154.9	151.4	146.9	140.6	134.3	129.8	122.7	113.7	105.7	94.9
62.5°	110.2	104.7	103.0	101.2	95.9	93.1	87.8	83.3	77.0	70.8	63.5
65°	72.5	69.0	67.2	64.5	61.8	60.0	57.3	53.7	48.4	44.7	40.4
67.5°	45.7	43.0	41.2	40.4	37.6	36.7	34.1	32.2	28.6	26.9	24.1
70°	25.9	25.1	23.3	23.3	21.5	19.6	18.8	17.0	16.1	14.3	13.5
72.5°	13.5	13.5	12.5	11.6	10.8	10.8	9.8	9.0	8.0	7.2	7.2
75°	6.3	6.3	6.3	5.3	5.3	5.3	4.5	4.5	4.5	3.5	3.5
77.5°	3.5	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	1.8	1.8
80°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
82.5°	1.8	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
85°	2.7	1.8	1.8	1.8	1.8	2.7	2.7	2.7	2.7	2.7	2.7
87.5°	2.7	2.7	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1191538

CATALOG NUMBER: LDA4A15930D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	381.5	381.5	381.5	381.5	381.5	381.5	381.5	381.5	381.5	381.5	381.5
2.5°	436.1	434.3	429.8	429.0	419.2	417.4	412.0	403.9	397.6	395.9	397.6
5°	501.5	493.5	480.0	477.4	461.2	455.9	444.3	431.7	421.0	414.7	412.0
7.5°	568.6	555.3	535.5	525.7	502.4	490.8	473.7	455.9	438.8	427.2	420.0
10°	633.1	611.7	575.9	567.8	539.2	520.4	497.0	472.9	451.4	435.3	423.7
12.5°	694.1	668.2	631.4	609.0	571.4	547.2	517.6	488.0	461.2	439.8	423.7
15°	756.8	722.7	677.0	645.7	602.7	570.5	534.7	500.6	469.2	442.4	422.7
17.5°	808.8	766.6	712.9	675.3	625.1	586.6	545.5	506.0	472.0	441.5	419.2
20°	847.2	798.0	737.0	693.1	637.6	594.7	550.0	506.9	469.2	436.1	412.0
22.5°	873.3	816.8	750.5	702.1	643.9	597.4	549.0	504.3	465.7	431.7	405.7
25°	885.7	824.9	755.9	703.9	643.1	594.7	544.5	498.8	459.4	424.5	399.4
27.5°	883.9	819.4	748.8	694.1	632.3	582.1	531.1	485.5	446.9	412.0	386.0
30°	858.0	794.5	722.7	667.2	606.3	556.2	505.1	460.4	422.7	386.9	362.7
32.5°	817.6	752.3	682.5	620.6	568.6	519.4	471.1	425.5	389.6	354.7	331.4
35°	763.1	700.4	633.1	580.4	523.9	476.5	429.8	386.9	352.9	318.8	297.3
37.5°	699.4	639.4	577.6	523.1	473.7	429.8	386.0	347.5	313.5	283.0	262.4
40°	626.0	570.5	514.1	467.5	419.2	378.8	338.6	301.0	273.1	245.5	227.5
42.5°	546.3	497.0	446.0	405.7	361.8	326.0	287.5	260.6	233.7	208.6	194.3
45°	463.1	420.0	377.0	340.4	304.5	273.1	240.0	214.9	194.3	173.7	161.2
47.5°	380.6	343.9	309.0	279.4	248.0	222.1	198.8	176.5	156.7	139.8	129.8
50°	297.3	273.1	245.5	221.2	196.1	174.7	153.1	137.0	121.8	109.2	103.0
52.5°	232.0	209.6	187.2	167.5	149.6	131.6	117.3	103.9	93.1	85.1	80.6
55°	172.9	154.9	137.9	122.7	108.4	96.7	86.9	78.8	71.6	65.3	63.5
57.5°	123.5	110.2	98.5	86.9	77.9	70.8	64.5	59.0	54.7	50.2	49.2
60°	85.9	76.1	69.0	61.8	56.5	51.0	47.5	43.9	40.4	37.6	36.7
62.5°	57.3	52.0	46.6	43.0	40.4	35.9	34.1	31.4	29.6	26.9	25.9
65°	36.7	33.1	30.4	27.8	25.9	24.1	22.4	20.6	18.8	17.0	17.0
67.5°	22.4	19.6	18.8	17.0	15.3	14.3	13.5	11.6	10.8	10.8	9.8
70°	12.5	10.8	9.8	9.0	8.0	8.0	7.2	6.3	6.3	5.3	5.3
72.5°	6.3	6.3	5.3	5.3	4.5	4.5	3.5	3.5	3.5	2.7	2.7
75°	3.5	3.5	2.7	2.7	2.7	2.7	2.7	2.7	1.8	1.8	1.8
77.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
80°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
82.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
85°	2.7	2.7	2.7	2.7	1.8	1.8	1.8	1.8	1.8	1.8	1.8
87.5°	2.7	2.7	2.7	2.7	2.7	1.8	1.8	1.8	1.8	1.8	1.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191538

CATALOG NUMBER: LDA4A15930D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	112.5°	135°	157.5°	180°
0°	381.5	381.5	381.5	381.5	381.5	381.5	381.5	381.5
2.5°	390.5	381.5	379.8	379.8	342.1	319.8	302.7	298.2
5°	399.4	386.9	380.6	377.0	309.8	270.4	244.5	237.3
7.5°	403.9	386.0	376.1	368.0	278.6	227.5	199.8	191.6
10°	402.1	380.6	367.2	356.5	249.8	194.3	165.7	158.5
12.5°	398.6	374.3	357.4	343.9	225.7	168.4	142.4	135.3
15°	394.9	367.2	347.5	331.4	206.0	150.4	127.2	121.0
17.5°	387.8	359.2	336.7	319.8	193.5	143.3	123.5	120.0
20°	379.8	350.2	326.9	309.8	189.8	150.4	138.8	138.8
22.5°	374.3	343.9	321.5	304.5	196.1	167.5	163.0	165.7
25°	367.2	338.6	316.1	300.0	202.4	181.0	178.2	181.8
27.5°	355.5	326.9	305.5	289.2	198.8	179.2	176.5	178.2
30°	332.3	304.5	285.7	268.6	184.5	165.7	161.2	162.1
32.5°	302.7	275.9	257.9	241.8	163.9	146.0	141.5	141.5
35°	270.4	245.5	228.4	214.1	144.1	128.0	123.5	122.7
37.5°	238.2	214.9	200.6	187.2	126.3	112.0	107.5	106.6
40°	206.0	185.5	172.0	161.2	111.0	99.4	94.9	94.1
42.5°	175.5	157.6	146.0	137.0	96.7	87.8	84.1	83.3
45°	145.1	130.8	121.8	114.7	84.1	75.3	74.3	74.3
47.5°	117.3	105.7	99.4	94.9	71.6	64.5	63.5	64.5
50°	94.1	85.9	81.5	77.9	61.0	54.7	52.0	52.0
52.5°	74.3	69.0	66.3	63.5	50.2	43.9	40.4	39.4
55°	59.0	54.7	52.8	51.0	39.4	32.2	28.6	27.8
57.5°	46.6	43.0	41.2	39.4	29.6	22.4	18.8	17.9
60°	34.9	32.2	30.4	29.6	20.6	13.5	10.8	9.8
62.5°	25.1	23.3	21.5	20.6	12.5	7.2	4.5	3.5
65°	15.3	15.3	13.5	12.5	6.3	2.7	1.8	1.0
67.5°	9.0	8.0	7.2	7.2	2.7	1.8	1.0	1.0
70°	4.5	4.5	3.5	3.5	1.8	1.0	1.0	1.0
72.5°	2.7	2.7	2.7	1.8	1.8	1.0	1.0	1.0
75°	1.8	1.8	1.8	1.8	1.8	1.0	1.0	1.0
77.5°	1.8	1.8	1.8	1.8	1.8	1.0	1.0	0.0
80°	1.8	1.8	1.8	1.8	1.8	1.0	1.0	0.0
82.5°	1.8	1.8	1.8	1.8	1.8	1.0	1.0	1.0
85°	1.8	1.8	1.8	1.8	1.8	1.0	1.0	0.0
87.5°	1.8	1.8	1.8	1.8	1.8	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)