

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212773

Luminaire Tested: **LDA4A20950D010TE LAR25NF 4LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212773
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26102)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A20950D010TE LAR25NF 4LLWW1
Description: PORTFOLIO 4" Lensed Wall Wash, Self-flanged, 25° Narrow Flood Optic,
at 30° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2037.2 lumens
Efficiency: N/A
Efficacy: 70.7 lumens/watt
Spacing Criteria (0/90/45): 2.11 / 1.09 / 1.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212773

CATALOG NUMBER: LDA4A20950D010TE LAR25NF 4LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212773

CATALOG NUMBER: LDA4A20950D010TE LAR25NF 4LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80		
3	97	89	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71		
4	90	80	73	67	88	79	72	67	77	71	66	74	69	65	72	68	65	63		
5	83	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56		
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	61	55	52	50		
7	72	60	53	47	71	60	52	47	58	52	47	57	51	47	56	50	46	45		
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40		
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36		
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	69666	69666	69666
5°	115905	69102	43497
10°	187647	66094	29383
15°	277485	62635	22870
20°	376931	60210	26987
25°	453788	60441	36637
30°	493781	56643	34183
35°	479317	47718	27345
40°	415213	38435	22413
45°	323790	29602	19188
50°	214727	22125	14776
55°	119759	16258	8838
60°	63104	10805	3602
65°	34060	5399	409
70°	16229	1911	505
75°	5671	1287	667
80°	1918	1918	0
85°	5661	3821	0

TEST NUMBER: P1212773

CATALOG NUMBER: LDA4A20950D010TE LAR25NF 4LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.2	3.0
10°-20°	237.8	11.7
20°-30°	489.0	24.0
30°-40°	584.1	28.7
40°-50°	431.3	21.2
50°-60°	181.5	8.9
60°-70°	44.6	2.2
70°-80°	6.1	0.3
80°-90°	2.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	787.0	38.6
0°-40°	1371.2	67.3
0°-60°	1984.0	97.4
0°-90°	2037.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2037.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	565	565	565	565	565	
5°	936	806	558	400	351	107
15°	2173	1395	490	223	179	638
25°	3334	1771	444	268	269	1525
35°	3183	1583	317	190	182	1952
45°	1856	976	170	112	110	1425
55°	557	362	76	48	41	531
65°	117	80	18	4	1	127
75°	12	7	3	1	1	17
85°	4	4	3	1	0	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212773

CATALOG NUMBER: LDA4A20950D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	564.8	564.8	564.8	564.8	564.8	564.8	564.8	564.8	564.8	564.8	564.8
2.5°	734.4	725.3	725.3	727.8	735.8	729.1	723.8	718.6	723.8	712.0	715.9
5°	936.1	934.8	934.8	924.0	933.4	934.8	924.0	914.9	917.4	900.2	900.2
7.5°	1201.1	1193.3	1190.6	1175.9	1186.6	1185.3	1168.0	1152.2	1152.2	1124.3	1117.7
10°	1498.2	1487.5	1482.3	1463.7	1473.0	1467.6	1442.5	1418.6	1411.9	1372.2	1357.6
12.5°	1825.6	1819.0	1811.1	1787.2	1795.1	1784.5	1748.7	1714.3	1699.7	1646.7	1621.5
15°	2173.0	2183.6	2170.3	2142.5	2147.7	2129.2	2082.8	2035.1	2012.5	1941.0	1903.9
17.5°	2530.9	2544.3	2529.6	2497.9	2496.5	2471.4	2407.6	2349.4	2316.3	2224.7	2175.6
20°	2871.6	2875.7	2857.2	2822.7	2814.7	2780.2	2703.3	2621.2	2589.3	2476.7	2414.3
22.5°	3139.6	3154.1	3131.5	3106.4	3081.2	3037.4	2947.3	2857.2	2812.0	2683.4	2607.8
25°	3334.3	3367.5	3341.0	3311.8	3284.1	3232.3	3131.5	3034.7	2979.2	2836.0	2749.8
27.5°	3463.0	3494.8	3465.7	3432.5	3403.4	3343.7	3233.7	3140.9	3073.3	2916.8	2824.0
30°	3466.9	3505.4	3474.8	3439.2	3411.3	3351.7	3238.9	3143.4	3067.8	2911.5	2814.7
32.5°	3371.6	3402.0	3371.6	3341.0	3309.3	3252.2	3139.6	3047.9	2968.5	2818.6	2721.9
35°	3183.2	3209.6	3179.3	3143.4	3121.0	3070.6	2963.2	2875.7	2796.1	2658.2	2573.5
37.5°	2923.4	2947.3	2919.4	2899.5	2866.3	2821.3	2723.1	2644.9	2569.4	2444.8	2369.2
40°	2578.7	2629.0	2602.5	2589.3	2558.8	2520.3	2434.1	2365.2	2296.3	2187.6	2125.2
42.5°	2234.0	2281.8	2257.8	2248.6	2222.2	2188.9	2117.3	2059.0	1995.3	1905.2	1852.1
45°	1856.2	1906.5	1883.9	1880.0	1857.4	1832.3	1755.4	1724.8	1669.2	1584.3	1559.2
47.5°	1500.8	1510.1	1488.9	1490.2	1474.3	1457.1	1394.7	1376.2	1348.4	1283.4	1254.2
50°	1119.0	1125.7	1108.3	1113.6	1103.1	1092.5	1050.1	1040.7	1023.6	979.8	962.6
52.5°	770.2	800.8	788.8	794.2	788.8	784.9	767.7	751.7	743.8	715.9	707.9
55°	556.9	559.4	550.3	555.6	551.5	550.3	539.6	530.4	526.3	509.2	506.5
57.5°	385.8	388.5	388.5	385.8	384.5	381.9	375.2	369.8	367.3	363.3	355.3
60°	255.8	266.6	262.5	265.2	263.8	263.8	258.5	254.5	253.3	245.3	245.3
62.5°	175.0	181.6	179.1	180.2	179.1	179.1	175.0	172.4	172.4	171.1	167.0
65°	116.7	120.6	118.0	119.3	119.3	119.3	116.7	114.0	114.0	112.6	110.0
67.5°	74.3	77.0	75.6	77.0	75.6	77.0	74.3	72.9	71.6	71.6	70.3
70°	45.0	46.4	45.0	46.4	45.0	45.0	43.8	43.8	42.4	41.1	41.1
72.5°	23.8	25.2	25.2	25.2	25.2	25.2	23.8	22.6	22.6	22.6	21.2
75°	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	10.5	10.5	10.5
77.5°	5.3	5.3	5.3	5.3	6.7	5.3	5.3	5.3	5.3	5.3	5.3
80°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
82.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
85°	4.0	4.0	4.0	4.0	4.0	4.0	5.3	5.3	5.3	5.3	4.0
87.5°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	6.7	6.7	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212773

CATALOG NUMBER: LDA4A20950D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	564.8	564.8	564.8	564.8	564.8	564.8	564.8	564.8	564.8	564.8	564.8
2.5°	705.3	698.8	696.1	690.8	684.1	680.1	676.1	677.6	668.2	661.5	652.4
5°	883.0	868.5	860.5	848.5	834.0	821.9	811.4	806.1	788.8	776.9	751.7
7.5°	1092.5	1067.2	1051.4	1030.2	1004.8	983.8	962.6	948.0	921.4	898.9	860.5
10°	1321.8	1283.4	1255.5	1223.7	1185.3	1150.9	1119.0	1092.5	1052.6	1018.2	967.8
12.5°	1572.5	1518.1	1478.2	1431.8	1377.5	1329.7	1272.8	1242.2	1187.9	1140.2	1075.3
15°	1838.8	1767.4	1711.6	1647.9	1576.4	1512.7	1439.8	1394.7	1323.1	1262.1	1181.2
17.5°	2094.8	2004.7	1931.6	1850.8	1762.1	1679.8	1593.6	1530.0	1442.5	1366.9	1270.0
20°	2317.4	2210.1	2121.2	2023.2	1918.4	1817.6	1723.5	1638.7	1536.6	1447.8	1337.6
22.5°	2499.2	2374.5	2272.4	2158.4	2037.8	1923.8	1816.3	1719.6	1602.8	1504.9	1384.0
25°	2630.4	2493.8	2379.8	2253.9	2121.2	1991.4	1877.3	1771.2	1644.0	1539.2	1410.6
27.5°	2699.3	2554.8	2434.1	2298.9	2158.4	2023.2	1899.9	1787.2	1653.3	1543.3	1410.6
30°	2687.5	2540.2	2415.6	2276.4	2134.5	1999.3	1870.6	1758.0	1620.0	1508.7	1376.2
32.5°	2595.8	2451.5	2329.5	2194.3	2054.9	1923.8	1795.1	1686.5	1548.6	1439.8	1311.2
35°	2444.8	2308.3	2192.9	2064.3	1932.9	1809.6	1693.1	1583.0	1450.5	1347.0	1226.4
37.5°	2248.6	2123.9	2019.2	1899.9	1779.2	1667.7	1552.4	1458.3	1340.5	1243.6	1125.7
40°	2013.9	1903.9	1811.1	1705.0	1596.3	1499.5	1402.8	1311.2	1195.8	1109.7	1009.0
42.5°	1755.4	1661.2	1581.6	1488.9	1394.7	1312.6	1229.0	1149.5	1053.9	975.8	881.7
45°	1477.0	1397.3	1332.4	1258.2	1180.0	1103.1	1042.1	975.8	887.0	828.7	749.0
47.5°	1189.2	1128.2	1079.1	1022.2	959.8	912.1	853.8	800.8	735.8	681.4	616.5
50°	916.2	873.7	839.3	799.4	754.3	710.6	676.1	635.0	585.9	542.3	490.5
52.5°	677.6	649.7	628.4	602.0	571.5	548.9	517.1	486.5	449.5	416.2	376.5
55°	485.2	469.4	456.1	440.1	418.9	399.0	383.1	361.9	335.4	310.2	281.0
57.5°	348.6	331.4	330.1	312.9	304.9	290.4	275.7	259.9	241.3	224.1	202.8
60°	241.3	229.3	224.1	217.5	208.1	199.0	192.3	181.6	168.4	156.4	140.5
62.5°	163.1	155.1	152.4	149.9	141.9	137.9	130.0	123.3	114.0	104.8	94.1
65°	107.3	102.1	99.4	95.5	91.4	88.8	84.8	79.6	71.6	66.2	59.6
67.5°	67.6	63.6	60.9	59.6	55.7	54.4	50.4	47.7	42.4	39.7	35.9
70°	38.4	37.2	34.5	34.5	31.8	29.2	27.9	25.2	23.8	21.2	19.9
72.5°	19.9	19.9	18.5	17.2	15.9	15.9	14.6	13.2	11.9	10.5	10.5
75°	9.4	9.4	9.4	8.0	8.0	8.0	6.7	6.7	6.7	5.3	5.3
77.5°	5.3	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	2.7	2.7
80°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
82.5°	2.7	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
85°	4.0	2.7	2.7	2.7	2.7	4.0	4.0	4.0	4.0	4.0	4.0
87.5°	4.0	4.0	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212773

CATALOG NUMBER: LDA4A20950D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	564.8	564.8	564.8	564.8	564.8	564.8	564.8	564.8	564.8	564.8	564.8
2.5°	645.7	643.0	636.4	635.0	620.5	617.9	609.9	598.0	588.6	585.9	588.6
5°	742.5	730.5	710.6	706.7	682.8	674.8	657.6	639.1	623.2	613.8	609.9
7.5°	842.0	821.9	792.9	778.2	743.8	726.6	701.3	674.8	649.7	632.5	621.8
10°	937.2	905.5	852.5	840.6	798.1	770.2	735.8	700.1	668.2	644.4	627.0
12.5°	1027.5	989.0	934.8	901.6	845.8	810.1	766.4	722.5	682.8	651.0	627.0
15°	1120.3	1070.0	1002.4	956.0	892.2	844.5	791.5	741.1	694.7	654.9	625.7
17.5°	1197.2	1134.8	1055.4	999.6	925.4	868.5	807.5	749.0	698.8	653.5	620.5
20°	1254.2	1181.2	1091.2	1026.2	943.9	880.4	814.1	750.4	694.7	645.7	609.9
22.5°	1292.7	1209.1	1111.0	1039.4	953.3	884.3	812.8	746.5	689.4	639.1	600.6
25°	1311.2	1221.0	1119.0	1042.1	951.9	880.4	806.1	738.5	680.1	628.4	591.3
27.5°	1308.6	1213.2	1108.3	1027.5	936.1	861.8	786.2	718.6	661.5	609.9	571.5
30°	1270.0	1175.9	1070.0	987.7	897.5	823.3	747.7	681.4	625.7	572.7	537.1
32.5°	1210.5	1113.6	1010.4	918.7	842.0	768.9	697.4	629.7	576.8	525.0	490.5
35°	1129.5	1036.8	937.2	859.1	775.5	705.3	636.4	572.7	522.4	472.0	440.1
37.5°	1035.4	946.6	855.2	774.4	701.3	636.4	571.5	514.4	463.9	418.9	388.5
40°	926.7	844.5	761.0	692.1	620.5	560.8	501.2	445.4	404.4	363.3	336.8
42.5°	808.7	735.8	660.2	600.6	535.7	482.7	425.6	385.8	346.0	308.9	287.7
45°	685.5	621.8	558.1	503.9	450.7	404.4	355.3	318.2	287.7	257.2	238.7
47.5°	563.5	509.2	457.4	413.7	367.3	328.7	294.2	261.1	232.0	206.8	192.3
50°	440.1	404.4	363.3	327.5	290.4	258.5	226.6	202.8	180.2	161.7	152.4
52.5°	343.3	310.2	277.1	247.8	221.4	194.9	173.7	153.7	137.9	125.9	119.3
55°	255.8	229.3	204.2	181.6	160.4	143.2	128.6	116.7	106.0	96.8	94.1
57.5°	182.9	163.1	145.8	128.6	115.3	104.8	95.5	87.5	80.9	74.3	72.9
60°	127.3	112.6	102.1	91.4	83.6	75.6	70.3	64.9	59.6	55.7	54.4
62.5°	84.8	77.0	69.0	63.6	59.6	53.0	50.4	46.4	43.8	39.7	38.4
65°	54.4	49.1	45.0	41.1	38.4	35.9	33.2	30.4	27.9	25.2	25.2
67.5°	33.2	29.2	27.9	25.2	22.6	21.2	19.9	17.2	15.9	15.9	14.6
70°	18.5	15.9	14.6	13.2	11.9	11.9	10.5	9.4	9.4	8.0	8.0
72.5°	9.4	9.4	8.0	8.0	6.7	6.7	5.3	5.3	5.3	4.0	4.0
75°	5.3	5.3	4.0	4.0	4.0	4.0	4.0	4.0	2.7	2.7	2.7
77.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
80°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
82.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
85°	4.0	4.0	4.0	4.0	2.7	2.7	2.7	2.7	2.7	2.7	2.7
87.5°	4.0	4.0	4.0	4.0	4.0	2.7	2.7	2.7	2.7	2.7	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212773

CATALOG NUMBER: LDA4A20950D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	112.5°	135°	157.5°	180°
0°	564.8	564.8	564.8	564.8	564.8	564.8	564.8	564.8
2.5°	578.1	564.8	562.1	562.1	506.5	473.3	448.1	441.6
5°	591.3	572.7	563.5	558.1	458.7	400.4	361.9	351.3
7.5°	598.0	571.5	556.9	544.9	412.4	336.8	295.6	283.7
10°	595.3	563.5	543.6	527.7	369.8	287.7	245.3	234.6
12.5°	590.0	554.2	529.0	509.2	334.2	249.2	210.8	200.1
15°	584.8	543.6	514.4	490.5	304.9	222.8	188.2	179.1
17.5°	574.1	531.5	498.5	473.3	286.4	212.2	182.9	177.7
20°	562.1	518.3	483.8	458.7	281.0	222.8	205.6	205.6
22.5°	554.2	509.2	476.0	450.7	290.4	247.8	241.3	245.3
25°	543.6	501.2	468.0	444.1	299.7	267.8	263.8	269.2
27.5°	526.3	483.8	452.1	428.3	294.2	265.2	261.1	263.8
30°	491.8	450.7	422.9	397.7	273.2	245.3	238.7	240.0
32.5°	448.1	408.4	381.9	358.0	242.6	216.1	209.5	209.5
35°	400.4	363.3	338.1	316.9	213.4	189.6	182.9	181.6
37.5°	352.7	318.2	296.9	277.1	186.9	165.8	159.0	157.8
40°	304.9	274.4	254.5	238.7	164.4	147.2	140.5	139.2
42.5°	259.9	233.4	216.1	202.8	143.2	130.0	124.7	123.3
45°	214.8	193.5	180.2	169.7	124.7	111.5	110.0	110.0
47.5°	173.7	156.4	147.2	140.5	106.0	95.5	94.1	95.5
50°	139.2	127.3	120.6	115.3	90.2	80.9	77.0	77.0
52.5°	110.0	102.1	98.1	94.1	74.3	64.9	59.6	58.2
55°	87.5	80.9	78.2	75.6	58.2	47.7	42.4	41.1
57.5°	69.0	63.6	60.9	58.2	43.8	33.2	27.9	26.5
60°	51.7	47.7	45.0	43.8	30.4	19.9	15.9	14.6
62.5°	37.2	34.5	31.8	30.4	18.5	10.5	6.7	5.3
65°	22.6	22.6	19.9	18.5	9.4	4.0	2.7	1.4
67.5°	13.2	11.9	10.5	10.5	4.0	2.7	1.4	1.4
70°	6.7	6.7	5.3	5.3	2.7	1.4	1.4	1.4
72.5°	4.0	4.0	4.0	2.7	2.7	1.4	1.4	1.4
75°	2.7	2.7	2.7	2.7	2.7	1.4	1.4	1.4
77.5°	2.7	2.7	2.7	2.7	2.7	1.4	1.4	0.0
80°	2.7	2.7	2.7	2.7	2.7	1.4	1.4	0.0
82.5°	2.7	2.7	2.7	2.7	2.7	1.4	1.4	1.4
85°	2.7	2.7	2.7	2.7	2.7	1.4	1.4	0.0
87.5°	2.7	2.7	2.7	2.7	2.7	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)