

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212755

Luminaire Tested: **LDA4A15950D010TE LAR25NF 4LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212755
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26102)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A15950D010TE LAR25NF 4LLWW1
Description: PORTFOLIO 4" Lensed Wall Wash, Self-flanged, 25° Narrow Flood Optic,
at 30° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1548.5 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 2.11 / 1.09 / 1.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212755

CATALOG NUMBER: LDA4A15950D010TE LAR25NF 4LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212755

CATALOG NUMBER: LDA4A15950D010TE LAR25NF 4LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95
2	104	98	93	88	102	96	91	87	93	89	85		90	86	84		87
3	97	89	82	77	95	87	81	76	84	79	75		82	77	74		79
4	90	80	73	67	88	79	72	67	77	71	66		74	69	65		72
5	83	73	65	60	82	72	65	59	70	63	59		68	62	58		66
6	78	66	58	53	76	65	58	53	64	57	52		62	56	52		61
7	72	60	53	47	71	60	52	47	58	52	47		57	51	47		56
8	67	55	48	43	66	55	47	42	53	47	42		52	46	42		51
9	63	51	43	38	62	50	43	38	49	43	38		48	42	38		47
10	59	47	40	35	58	46	39	35	45	39	35		45	39	34		44

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	52952	52952	52952
5°	88096	52535	33071
10°	142633	50225	22344
15°	210917	47605	17367
20°	286531	45771	20490
25°	344951	45960	27859
30°	375367	43056	25979
35°	364352	36259	20795
40°	315624	29208	17036
45°	246131	22520	14600
50°	163223	16829	11206
55°	91029	12344	6709
60°	48006	8215	2714
65°	25859	4086	292
70°	12370	1443	361
75°	4289	953	477
80°	1421	1421	0
85°	4246	2830	0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212755

CATALOG NUMBER: LDA4A15950D010TE LAR25NF 4LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.8	3.0
10°-20°	180.8	11.7
20°-30°	371.7	24.0
30°-40°	444.0	28.7
40°-50°	327.9	21.2
50°-60°	138.0	8.9
60°-70°	33.9	2.2
70°-80°	4.6	0.3
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	598.3	38.6
0°-40°	1042.3	67.3
0°-60°	1508.1	97.4
0°-90°	1548.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1548.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	429	429	429	429	429	
5°	712	613	424	304	267	81
15°	1652	1060	373	169	136	485
25°	2535	1346	338	204	205	1159
35°	2420	1203	241	144	138	1484
45°	1411	742	129	85	84	1083
55°	423	275	57	36	31	404
65°	89	60	14	3	1	96
75°	9	5	2	1	1	13
85°	3	3	2	1	0	3
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212755

CATALOG NUMBER: LDA4A15950D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3
2.5°	558.4	551.2	551.2	553.3	559.3	554.2	550.3	546.3	550.3	541.2	544.1
5°	711.5	710.5	710.5	702.4	709.5	710.5	702.4	695.3	697.4	684.3	684.3
7.5°	913.0	907.1	904.9	893.9	902.0	901.0	888.0	875.7	875.7	854.6	849.7
10°	1138.8	1130.7	1126.7	1112.6	1119.7	1115.7	1096.6	1078.4	1073.3	1043.1	1032.0
12.5°	1387.7	1382.7	1376.6	1358.4	1364.6	1356.5	1329.2	1303.0	1292.0	1251.6	1232.5
15°	1651.7	1659.8	1649.8	1628.6	1632.6	1618.6	1583.3	1547.0	1529.8	1475.4	1447.3
17.5°	1923.9	1934.0	1923.0	1898.6	1897.7	1878.6	1830.2	1785.8	1760.7	1691.0	1653.7
20°	2182.9	2185.9	2171.8	2145.6	2139.6	2113.4	2054.9	1992.4	1968.2	1882.5	1835.2
22.5°	2386.5	2397.6	2380.5	2361.3	2342.2	2308.8	2240.3	2171.8	2137.5	2039.8	1982.3
25°	2534.6	2559.9	2539.7	2517.4	2496.3	2457.0	2380.5	2306.8	2264.6	2155.6	2090.1
27.5°	2632.3	2656.6	2634.4	2609.2	2587.1	2541.7	2458.0	2387.5	2336.0	2217.2	2146.6
30°	2635.5	2664.6	2641.4	2614.2	2593.0	2547.8	2462.1	2389.5	2332.1	2213.1	2139.6
32.5°	2562.8	2586.1	2562.8	2539.7	2515.4	2472.2	2386.5	2316.9	2256.5	2142.6	2069.0
35°	2419.7	2439.8	2416.8	2389.5	2372.3	2334.1	2252.3	2185.9	2125.4	2020.6	1956.1
37.5°	2222.2	2240.3	2219.2	2204.0	2178.9	2144.6	2070.0	2010.5	1953.1	1858.4	1801.0
40°	1960.2	1998.5	1978.4	1968.2	1945.0	1915.8	1850.3	1798.0	1745.5	1662.9	1615.4
42.5°	1698.1	1734.4	1716.3	1709.2	1689.1	1663.8	1609.5	1565.1	1516.7	1448.2	1407.8
45°	1411.0	1449.2	1432.1	1429.1	1411.9	1392.8	1334.3	1311.1	1268.8	1204.3	1185.2
47.5°	1140.8	1147.8	1131.7	1132.7	1120.6	1107.6	1060.3	1046.0	1024.9	975.5	953.3
50°	850.6	855.6	842.5	846.6	838.4	830.4	798.2	791.0	778.0	744.8	731.6
52.5°	585.5	608.7	599.6	603.7	599.6	596.6	583.5	571.4	565.4	544.1	538.2
55°	423.3	425.4	418.2	422.3	419.2	418.2	410.2	403.0	400.1	387.0	385.0
57.5°	293.3	295.3	295.3	293.3	292.2	290.3	285.2	281.2	279.1	276.1	270.0
60°	194.6	202.5	199.6	201.6	200.5	200.5	196.6	193.4	192.4	186.5	186.5
62.5°	133.0	138.1	136.0	137.0	136.0	136.0	133.0	131.0	131.0	130.0	126.9
65°	88.6	91.7	89.6	90.8	90.8	90.8	88.6	86.6	86.6	85.7	83.7
67.5°	56.5	58.4	57.4	58.4	57.4	58.4	56.5	55.4	54.5	54.5	53.5
70°	34.3	35.4	34.3	35.4	34.3	34.3	33.3	33.3	32.2	31.2	31.2
72.5°	18.2	19.1	19.1	19.1	19.1	19.1	18.2	17.2	17.2	17.2	16.1
75°	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	8.1	8.1	8.1
77.5°	4.0	4.0	4.0	4.0	5.1	4.0	4.0	4.0	4.0	4.0	4.0
80°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
82.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
85°	3.0	3.0	3.0	3.0	3.0	3.0	4.0	4.0	4.0	4.0	3.0
87.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	5.1	5.1	4.0	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212755

CATALOG NUMBER: LDA4A15950D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3
2.5°	536.2	531.1	529.2	525.0	520.0	516.9	514.0	514.9	508.0	502.8	495.8
5°	671.2	660.2	654.1	645.0	633.9	624.8	616.7	612.8	599.6	590.5	571.4
7.5°	830.4	811.3	799.1	783.1	764.0	747.8	731.6	720.6	700.4	683.3	654.1
10°	1004.7	975.5	954.4	930.2	901.0	874.7	850.6	830.4	800.2	774.1	735.8
12.5°	1195.3	1154.0	1123.6	1088.5	1047.1	1010.9	967.5	944.3	902.9	866.6	817.3
15°	1397.8	1343.5	1301.0	1252.7	1198.2	1149.8	1094.4	1060.3	1005.8	959.4	898.0
17.5°	1592.3	1523.8	1468.4	1406.8	1339.3	1276.9	1211.4	1163.0	1096.6	1039.1	965.5
20°	1761.7	1680.0	1612.5	1537.8	1458.3	1381.7	1310.1	1245.6	1168.0	1100.5	1016.8
22.5°	1899.7	1804.9	1727.3	1640.7	1549.0	1462.2	1380.7	1307.2	1218.4	1143.9	1052.2
25°	1999.5	1895.7	1809.1	1713.3	1612.5	1513.7	1427.0	1346.4	1249.7	1170.0	1072.2
27.5°	2051.8	1942.1	1850.3	1747.5	1640.7	1537.8	1444.1	1358.4	1256.6	1173.1	1072.2
30°	2042.8	1931.0	1836.2	1730.4	1622.5	1519.8	1422.0	1336.4	1231.6	1146.9	1046.0
32.5°	1973.3	1863.4	1770.7	1668.0	1562.1	1462.2	1364.6	1281.9	1177.1	1094.4	996.7
35°	1858.4	1754.6	1666.9	1569.0	1469.4	1375.6	1287.0	1203.3	1102.5	1023.9	932.2
37.5°	1709.2	1614.5	1534.9	1444.1	1352.5	1267.9	1180.1	1108.6	1018.8	945.4	855.6
40°	1530.8	1447.3	1376.6	1296.0	1213.4	1139.8	1066.2	996.7	909.1	843.5	767.0
42.5°	1334.3	1262.8	1202.3	1131.7	1060.3	997.7	934.1	873.7	801.1	741.7	670.3
45°	1122.7	1062.3	1012.9	956.4	897.0	838.4	792.2	741.7	674.2	629.8	569.4
47.5°	904.0	857.6	820.2	777.0	729.7	693.4	649.0	608.7	559.3	518.0	468.5
50°	696.3	664.1	637.9	607.7	573.4	540.2	514.0	482.8	445.4	412.2	372.8
52.5°	514.9	493.8	477.7	457.5	434.4	417.2	393.0	369.8	341.6	316.4	286.2
55°	368.9	356.8	346.7	334.6	318.6	303.4	291.3	275.1	255.0	235.9	213.7
57.5°	265.1	252.0	250.8	237.8	231.7	220.7	209.6	197.6	183.4	170.4	154.1
60°	183.4	174.3	170.4	165.3	158.3	151.2	146.1	138.1	127.9	119.0	106.8
62.5°	124.0	117.8	115.9	113.9	107.7	104.8	98.7	93.7	86.6	79.6	71.7
65°	81.6	77.6	75.6	72.6	69.5	67.5	64.5	60.4	54.5	50.3	45.3
67.5°	51.4	48.4	46.4	45.3	42.2	41.3	38.3	36.3	32.2	30.2	27.2
70°	29.2	28.2	26.2	26.2	24.2	22.2	21.1	19.1	18.2	16.1	15.2
72.5°	15.2	15.2	14.0	13.0	12.1	12.1	11.0	10.1	9.0	8.1	8.1
75°	7.1	7.1	7.1	6.1	6.1	6.1	5.1	5.1	5.1	4.0	4.0
77.5°	4.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	2.0	2.0
80°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
82.5°	2.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
85°	3.0	2.0	2.0	2.0	2.0	3.0	3.0	3.0	3.0	3.0	3.0
87.5°	3.0	3.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212755

CATALOG NUMBER: LDA4A15950D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3
2.5°	490.9	488.8	483.7	482.8	471.6	469.7	463.6	454.5	447.4	445.4	447.4
5°	564.3	555.4	540.2	537.2	519.1	512.9	499.9	485.7	473.7	466.5	463.6
7.5°	639.9	624.8	602.7	591.6	565.4	552.2	533.1	512.9	493.8	480.8	472.7
10°	712.5	688.4	647.9	638.9	606.7	585.5	559.3	532.1	508.0	489.8	476.6
12.5°	781.0	751.8	710.5	685.3	643.0	615.8	582.4	549.2	519.1	494.8	476.6
15°	851.7	813.3	761.8	726.6	678.2	642.0	601.6	563.3	528.1	497.7	475.7
17.5°	910.0	862.7	802.3	759.8	703.5	660.2	613.8	569.4	531.1	496.8	471.6
20°	953.3	898.0	829.4	780.0	717.6	669.2	618.8	570.4	528.1	490.9	463.6
22.5°	982.7	919.2	844.5	790.1	724.6	672.3	617.8	567.4	524.1	485.7	456.6
25°	996.7	928.2	850.6	792.2	723.5	669.2	612.8	561.3	516.9	477.7	449.4
27.5°	994.8	922.1	842.5	781.0	711.5	655.1	597.6	546.3	502.8	463.6	434.4
30°	965.5	893.9	813.3	750.8	682.2	625.9	568.4	518.0	475.7	435.3	408.2
32.5°	920.1	846.6	767.9	698.5	639.9	584.6	530.1	478.6	438.4	399.0	372.8
35°	858.7	788.1	712.5	653.1	589.6	536.2	483.7	435.3	397.1	358.8	334.6
37.5°	787.1	719.6	650.1	588.5	533.1	483.7	434.4	391.0	352.7	318.6	295.3
40°	704.4	642.0	578.4	526.0	471.6	426.3	381.0	338.6	307.3	276.1	255.9
42.5°	614.7	559.3	501.9	456.6	407.2	366.9	323.4	293.3	263.1	234.8	218.7
45°	521.0	472.7	424.3	382.9	342.7	307.3	270.0	241.8	218.7	195.5	181.4
47.5°	428.3	387.0	347.8	314.4	279.1	249.9	223.8	198.5	176.4	157.2	146.1
50°	334.6	307.3	276.1	248.9	220.7	196.6	172.3	154.1	137.0	122.9	115.9
52.5°	261.0	235.9	210.6	188.4	168.4	148.2	132.1	116.9	104.8	95.7	90.8
55°	194.6	174.3	155.2	138.1	122.0	108.8	97.8	88.6	80.6	73.6	71.7
57.5°	139.2	124.0	110.9	97.8	87.7	79.6	72.6	66.6	61.4	56.5	55.4
60°	96.7	85.7	77.6	69.5	63.5	57.4	53.5	49.4	45.3	42.2	41.3
62.5°	64.5	58.4	52.5	48.4	45.3	40.2	38.3	35.4	33.3	30.2	29.2
65°	41.3	37.3	34.3	31.2	29.2	27.2	25.3	23.1	21.1	19.1	19.1
67.5°	25.3	22.2	21.1	19.1	17.2	16.1	15.2	13.0	12.1	12.1	11.0
70°	14.0	12.1	11.0	10.1	9.0	9.0	8.1	7.1	7.1	6.1	6.1
72.5°	7.1	7.1	6.1	6.1	5.1	5.1	4.0	4.0	4.0	3.0	3.0
75°	4.0	4.0	3.0	3.0	3.0	3.0	3.0	3.0	2.0	2.0	2.0
77.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
80°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
82.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
85°	3.0	3.0	3.0	3.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
87.5°	3.0	3.0	3.0	3.0	3.0	2.0	2.0	2.0	2.0	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212755

CATALOG NUMBER: LDA4A15950D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	112.5°	135°	157.5°	180°
0°	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3
2.5°	439.4	429.3	427.3	427.3	385.0	359.8	340.6	335.5
5°	449.4	435.3	428.3	424.3	348.7	304.3	275.1	267.1
7.5°	454.5	434.4	423.3	414.2	313.5	255.9	224.7	215.7
10°	452.5	428.3	413.3	401.0	281.2	218.7	186.5	178.4
12.5°	448.4	421.2	402.1	387.0	254.0	189.5	160.3	152.2
15°	444.5	413.3	391.0	372.8	231.7	169.3	143.1	136.0
17.5°	436.4	404.1	379.0	359.8	217.7	161.2	139.2	135.0
20°	427.3	394.2	367.8	348.7	213.7	169.3	156.1	156.1
22.5°	421.2	387.0	361.8	342.7	220.7	188.4	183.4	186.5
25°	413.3	381.0	355.8	337.7	227.8	203.5	200.5	204.7
27.5°	400.1	367.8	343.6	325.5	223.8	201.6	198.5	200.5
30°	373.9	342.7	321.5	302.3	207.6	186.5	181.4	182.4
32.5°	340.6	310.4	290.3	272.2	184.4	164.2	159.2	159.2
35°	304.3	276.1	257.0	240.8	162.2	144.0	139.2	138.1
37.5°	268.0	241.8	225.8	210.6	142.1	125.9	121.0	120.0
40°	231.7	208.6	193.4	181.4	124.9	111.9	106.8	105.8
42.5°	197.6	177.4	164.2	154.1	108.8	98.7	94.7	93.7
45°	163.3	147.2	137.0	129.1	94.7	84.7	83.7	83.7
47.5°	132.1	119.0	111.9	106.8	80.6	72.6	71.7	72.6
50°	105.8	96.7	91.7	87.7	68.5	61.4	58.4	58.4
52.5°	83.7	77.6	74.6	71.7	56.5	49.4	45.3	44.4
55°	66.6	61.4	59.4	57.4	44.4	36.3	32.2	31.2
57.5°	52.5	48.4	46.4	44.4	33.3	25.3	21.1	20.2
60°	39.3	36.3	34.3	33.3	23.1	15.2	12.1	11.0
62.5°	28.2	26.2	24.2	23.1	14.0	8.1	5.1	4.0
65°	17.2	17.2	15.2	14.0	7.1	3.0	2.0	1.0
67.5°	10.1	9.0	8.1	8.1	3.0	2.0	1.0	1.0
70°	5.1	5.1	4.0	4.0	2.0	1.0	1.0	1.0
72.5°	3.0	3.0	3.0	2.0	2.0	1.0	1.0	1.0
75°	2.0	2.0	2.0	2.0	2.0	1.0	1.0	1.0
77.5°	2.0	2.0	2.0	2.0	2.0	1.0	1.0	0.0
80°	2.0	2.0	2.0	2.0	2.0	1.0	1.0	0.0
82.5°	2.0	2.0	2.0	2.0	2.0	1.0	1.0	1.0
85°	2.0	2.0	2.0	2.0	2.0	1.0	1.0	0.0
87.5°	2.0	2.0	2.0	2.0	2.0	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)