

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1191628

Luminaire Tested: **LDA4A20930D010TE LAR25NF 4LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1191628
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26102)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A20930D010TE LAR25NF 4LLWW1
Description: PORTFOLIO 4" Lensed Wall Wash, Self-flanged, 25° Narrow Flood Optic,
at 30° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1810.3 lumens
Efficiency: N/A
Efficacy: 62.9 lumens/watt
Spacing Criteria (0/90/45): 2.11 / 1.09 / 1.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1191628

CATALOG NUMBER: LDA4A20930D010TE LAR25NF 4LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191628

CATALOG NUMBER: LDA4A20930D010TE LAR25NF 4LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	108	105	102	109	106	103	101		102	100	98		98	96	95		95	93	92
2	104	98	93	88	102	96	91	87		93	89	85		90	86	84		87	84	82
3	97	89	82	77	95	87	81	76		84	79	75		82	77	74		79	76	73
4	90	80	73	67	88	79	72	67		77	71	66		74	69	65		72	68	65
5	83	73	65	60	82	72	65	59		70	63	59		68	62	58		66	61	58
6	78	66	58	53	76	65	58	53		64	57	52		62	56	52		61	55	52
7	72	60	53	47	71	60	52	47		58	52	47		57	51	47		56	50	46
8	67	55	48	43	66	55	47	42		53	47	42		52	46	42		51	46	42
9	63	51	43	38	62	50	43	38		49	43	38		48	42	38		47	42	38
10	59	47	40	35	58	46	39	35		45	39	35		45	39	34		44	38	34

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	61907	61907	61907
5°	103003	61426	38656
10°	166756	58729	26114
15°	246583	55676	20304
20°	334967	53502	23968
25°	403282	53717	32554
30°	438818	50348	30380
35°	425953	42403	24318
40°	368985	34152	19918
45°	287751	26323	17043
50°	190798	19669	13106
55°	106405	14451	7849
60°	56073	9621	3207
65°	30266	4816	350
70°	14462	1731	433
75°	5052	1096	572
80°	1634	1634	0
85°	4953	3255	0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191628

CATALOG NUMBER: LDA4A20930D010TE LAR25NF 4LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.5	3.0
10°-20°	211.3	11.7
20°-30°	434.6	24.0
30°-40°	519.1	28.7
40°-50°	383.3	21.2
50°-60°	161.3	8.9
60°-70°	39.6	2.2
70°-80°	5.4	0.3
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	699.4	38.6
0°-40°	1218.5	67.3
0°-60°	1763.1	97.4
0°-90°	1810.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1810.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	502	502	502	502	502	
5°	832	716	496	356	312	95
15°	1931	1240	436	198	159	567
25°	2963	1574	395	238	239	1355
35°	2829	1407	282	168	162	1735
45°	1650	867	151	99	98	1266
55°	495	322	67	42	36	472
65°	104	71	16	4	1	113
75°	11	6	2	1	1	15
85°	4	4	2	1	0	3
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191628

CATALOG NUMBER: LDA4A20930D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	652.8	644.5	644.5	646.8	653.9	648.0	643.3	638.6	643.3	632.6	636.2
5°	831.9	830.6	830.6	821.2	829.4	830.6	821.2	812.9	815.4	800.0	800.0
7.5°	1067.5	1060.4	1058.0	1045.0	1054.4	1053.3	1038.1	1023.9	1023.9	999.1	993.2
10°	1331.4	1322.0	1317.2	1300.7	1309.0	1304.2	1281.9	1260.6	1254.8	1219.5	1206.5
12.5°	1622.3	1616.5	1609.4	1588.2	1595.3	1585.8	1554.0	1523.4	1510.4	1463.3	1440.9
15°	1931.0	1940.5	1928.7	1904.0	1908.7	1892.2	1851.0	1808.5	1788.6	1724.8	1691.8
17.5°	2249.2	2261.0	2248.0	2219.8	2218.6	2196.2	2139.6	2087.7	2058.3	1977.1	1933.5
20°	2551.9	2555.6	2539.1	2508.4	2501.3	2470.7	2402.4	2329.2	2301.0	2200.9	2145.5
22.5°	2790.0	2802.9	2782.9	2760.6	2738.1	2699.2	2619.1	2539.1	2498.9	2384.7	2317.5
25°	2963.2	2992.7	2969.1	2943.2	2918.4	2872.5	2782.9	2696.9	2647.4	2520.2	2443.6
27.5°	3077.4	3105.8	3079.9	3050.3	3024.4	2971.4	2873.7	2791.1	2731.1	2592.0	2509.5
30°	3081.0	3115.2	3088.1	3056.3	3031.5	2978.5	2878.3	2793.5	2726.4	2587.3	2501.3
32.5°	2996.2	3023.3	2996.2	2969.1	2940.7	2890.2	2790.0	2708.8	2637.9	2504.9	2418.9
35°	2828.8	2852.4	2825.3	2793.5	2773.5	2728.7	2633.3	2555.6	2484.9	2362.3	2287.0
37.5°	2598.0	2619.1	2594.4	2576.7	2547.3	2507.2	2420.0	2350.5	2283.3	2172.6	2105.4
40°	2291.6	2336.3	2312.9	2301.0	2273.9	2239.8	2163.2	2101.9	2040.7	1944.1	1888.6
42.5°	1985.3	2027.6	2006.5	1998.2	1974.6	1945.2	1881.5	1829.7	1773.2	1693.1	1645.9
45°	1649.6	1694.3	1674.2	1670.7	1650.7	1628.3	1559.9	1532.8	1483.3	1407.9	1385.6
47.5°	1333.7	1342.0	1323.2	1324.3	1310.1	1294.8	1239.5	1223.0	1198.2	1140.4	1114.5
50°	994.3	1000.3	984.9	989.7	980.3	970.9	933.1	924.8	909.6	870.7	855.3
52.5°	684.5	711.7	701.0	705.8	701.0	697.5	682.1	668.1	661.0	636.2	629.2
55°	494.8	497.2	489.0	493.6	490.1	489.0	479.6	471.3	467.7	452.5	450.0
57.5°	342.9	345.2	345.2	342.9	341.7	339.3	333.5	328.7	326.4	322.8	315.8
60°	227.3	236.7	233.3	235.6	234.4	234.4	229.8	226.2	225.0	217.9	217.9
62.5°	155.5	161.5	159.0	160.3	159.0	159.0	155.5	153.2	153.2	152.0	148.4
65°	103.7	107.2	104.8	106.0	106.0	106.0	103.7	101.4	101.4	100.2	97.7
67.5°	66.0	68.3	67.2	68.3	67.2	68.3	66.0	64.9	63.6	63.6	62.4
70°	40.1	41.3	40.1	41.3	40.1	40.1	39.0	39.0	37.6	36.5	36.5
72.5°	21.1	22.4	22.4	22.4	22.4	22.4	21.1	20.0	20.0	20.0	18.8
75°	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	9.4	9.4	9.4
77.5°	4.8	4.8	4.8	4.8	5.9	4.8	4.8	4.8	4.8	4.8	4.8
80°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
82.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
85°	3.5	3.5	3.5	3.5	3.5	3.5	4.8	4.8	4.8	4.8	3.5
87.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	5.9	5.9	4.8	4.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1191628

CATALOG NUMBER: LDA4A20930D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	626.8	620.9	618.6	613.8	608.0	604.4	600.9	602.1	593.8	587.9	579.6
5°	784.7	771.8	764.7	754.1	741.1	730.5	721.1	716.3	701.0	690.4	668.1
7.5°	970.9	948.4	934.2	915.4	893.1	874.3	855.3	842.4	818.8	798.9	764.7
10°	1174.6	1140.4	1115.8	1087.4	1053.3	1022.7	994.3	970.9	935.5	904.8	860.1
12.5°	1397.3	1349.1	1313.8	1272.5	1224.1	1181.7	1131.0	1103.9	1055.7	1013.3	955.5
15°	1634.2	1570.5	1521.1	1464.5	1400.9	1344.3	1279.6	1239.5	1175.9	1121.6	1049.8
17.5°	1861.5	1781.5	1716.6	1644.8	1565.9	1492.7	1416.1	1359.7	1281.9	1214.7	1128.7
20°	2059.5	1964.1	1885.1	1798.0	1704.9	1615.4	1531.7	1456.2	1365.6	1286.5	1188.8
22.5°	2220.9	2110.2	2019.5	1918.2	1810.9	1709.6	1614.1	1528.1	1424.4	1337.2	1230.1
25°	2337.5	2216.1	2114.9	2003.0	1885.1	1769.6	1668.4	1574.1	1461.0	1367.9	1253.7
27.5°	2398.9	2270.4	2163.2	2043.0	1918.2	1798.0	1688.4	1588.2	1469.3	1371.4	1253.7
30°	2388.2	2257.4	2146.6	2023.0	1896.9	1776.7	1662.4	1562.2	1439.7	1340.8	1223.0
32.5°	2306.9	2178.5	2070.0	1949.9	1826.2	1709.6	1595.3	1498.7	1376.2	1279.6	1165.2
35°	2172.6	2051.2	1948.7	1834.5	1717.8	1608.3	1504.6	1406.7	1289.0	1197.1	1089.9
37.5°	1998.2	1887.5	1794.3	1688.4	1581.2	1482.2	1379.6	1296.0	1191.1	1105.1	1000.3
40°	1789.7	1691.8	1609.4	1515.2	1418.6	1332.6	1246.6	1165.2	1062.7	986.2	896.6
42.5°	1559.9	1476.2	1405.6	1323.2	1239.5	1166.4	1092.2	1021.6	936.7	867.2	783.5
45°	1312.5	1241.8	1184.0	1118.1	1048.6	980.3	926.1	867.2	788.3	736.4	665.6
47.5°	1056.9	1002.6	959.0	908.3	853.0	810.6	758.7	711.7	653.9	605.5	547.9
50°	814.2	776.4	745.9	710.4	670.4	631.5	600.9	564.4	520.7	481.9	436.0
52.5°	602.1	577.3	558.5	534.9	507.8	487.8	459.4	432.4	399.4	370.0	334.6
55°	431.2	417.0	405.3	391.1	372.3	354.6	340.6	321.6	298.1	275.7	249.8
57.5°	309.9	294.5	293.4	278.0	270.9	258.0	245.0	231.0	214.4	199.1	180.3
60°	214.4	203.9	199.1	193.2	184.9	176.8	170.9	161.5	149.6	139.0	125.0
62.5°	144.9	137.8	135.5	133.1	126.1	122.5	115.4	109.6	101.4	93.1	83.7
65°	95.4	90.8	88.3	84.9	81.2	78.9	75.4	70.7	63.6	58.9	53.0
67.5°	60.1	56.6	54.2	53.0	49.5	48.4	44.7	42.4	37.6	35.3	31.9
70°	34.2	33.0	30.7	30.7	28.2	25.9	24.8	22.4	21.1	18.8	17.7
72.5°	17.7	17.7	16.5	15.3	14.2	14.2	13.0	11.7	10.6	9.4	9.4
75°	8.3	8.3	8.3	7.1	7.1	7.1	5.9	5.9	5.9	4.8	4.8
77.5°	4.8	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	2.3	2.3
80°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
82.5°	2.3	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
85°	3.5	2.3	2.3	2.3	2.3	3.5	3.5	3.5	3.5	3.5	3.5
87.5°	3.5	3.5	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1191628

CATALOG NUMBER: LDA4A20930D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	573.8	571.4	565.6	564.4	551.4	549.1	542.0	531.4	523.2	520.7	523.2
5°	659.8	649.1	631.5	628.0	606.7	599.8	584.4	567.9	553.7	545.5	542.0
7.5°	748.2	730.5	704.6	691.6	661.0	645.7	623.2	599.8	577.3	562.0	552.6
10°	833.0	804.6	757.6	747.0	709.2	684.5	653.9	622.1	593.8	572.5	557.3
12.5°	913.1	878.9	830.6	801.2	751.7	719.9	681.0	642.2	606.7	578.5	557.3
15°	995.6	950.8	890.7	849.5	792.9	750.5	703.4	658.5	617.4	582.1	556.2
17.5°	1064.0	1008.5	937.9	888.3	822.3	771.8	717.5	665.6	620.9	580.8	551.4
20°	1114.5	1049.8	969.7	911.9	838.8	782.3	723.4	666.8	617.4	573.8	542.0
22.5°	1148.7	1074.6	987.4	923.7	847.1	785.8	722.3	663.3	612.6	567.9	533.7
25°	1165.2	1085.1	994.3	926.1	845.9	782.3	716.3	656.2	604.4	558.5	525.5
27.5°	1162.9	1078.0	984.9	913.1	831.9	765.8	698.7	638.6	587.9	542.0	507.8
30°	1128.7	1045.0	950.8	877.8	797.7	731.7	664.5	605.5	556.2	509.0	477.1
32.5°	1075.7	989.7	897.8	816.5	748.2	683.3	619.7	559.6	512.6	466.5	436.0
35°	1003.9	921.4	833.0	763.5	689.2	626.8	565.6	509.0	464.2	419.5	391.1
37.5°	920.2	841.3	759.9	688.1	623.2	565.6	507.8	457.1	412.4	372.3	345.2
40°	823.6	750.5	676.4	615.0	551.4	498.4	445.4	395.9	359.4	322.8	299.3
42.5°	718.6	653.9	586.7	533.7	476.0	428.9	378.2	342.9	307.6	274.5	255.7
45°	609.2	552.6	496.1	447.7	400.7	359.4	315.8	282.8	255.7	228.6	212.1
47.5°	500.7	452.5	406.5	367.6	326.4	292.2	261.5	232.1	206.2	183.7	170.9
50°	391.1	359.4	322.8	291.0	258.0	229.8	201.4	180.3	160.3	143.8	135.5
52.5°	305.1	275.7	246.3	220.4	196.8	173.2	154.4	136.7	122.5	111.9	106.0
55°	227.3	203.9	181.4	161.5	142.6	127.3	114.2	103.7	94.3	86.0	83.7
57.5°	162.6	144.9	129.6	114.2	102.5	93.1	84.9	77.8	71.8	66.0	64.9
60°	113.1	100.2	90.8	81.2	74.3	67.2	62.4	57.8	53.0	49.5	48.4
62.5°	75.4	68.3	61.2	56.6	53.0	47.1	44.7	41.3	39.0	35.3	34.2
65°	48.4	43.6	40.1	36.5	34.2	31.9	29.4	27.1	24.8	22.4	22.4
67.5°	29.4	25.9	24.8	22.4	20.0	18.8	17.7	15.3	14.2	14.2	13.0
70°	16.5	14.2	13.0	11.7	10.6	10.6	9.4	8.3	8.3	7.1	7.1
72.5°	8.3	8.3	7.1	7.1	5.9	5.9	4.8	4.8	4.8	3.5	3.5
75°	4.8	4.8	3.5	3.5	3.5	3.5	3.5	3.5	2.3	2.3	2.3
77.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
80°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
82.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
85°	3.5	3.5	3.5	3.5	2.3	2.3	2.3	2.3	2.3	2.3	2.3
87.5°	3.5	3.5	3.5	3.5	3.5	2.3	2.3	2.3	2.3	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191628

CATALOG NUMBER: LDA4A20930D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	112.5°	135°	157.5°	180°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	513.7	501.9	499.6	499.6	450.0	420.6	398.2	392.4
5°	525.5	509.0	500.7	496.1	407.6	355.8	321.6	312.2
7.5°	531.4	507.8	494.8	484.2	366.5	299.3	262.8	252.1
10°	529.0	500.7	483.0	468.9	328.7	255.7	217.9	208.5
12.5°	524.3	492.5	470.2	452.5	296.8	221.5	187.4	178.0
15°	519.5	483.0	457.1	436.0	270.9	197.9	167.2	159.0
17.5°	510.1	472.5	442.9	420.6	254.6	188.5	162.6	157.8
20°	499.6	460.6	430.1	407.6	249.8	197.9	182.6	182.6
22.5°	492.5	452.5	423.0	400.7	258.0	220.4	214.4	217.9
25°	483.0	445.4	415.9	394.7	266.3	238.0	234.4	239.2
27.5°	467.7	430.1	401.8	380.5	261.5	235.6	232.1	234.4
30°	437.1	400.7	375.9	353.5	242.7	217.9	212.1	213.3
32.5°	398.2	362.9	339.3	318.1	215.6	192.0	186.2	186.2
35°	355.8	322.8	300.5	281.6	189.7	168.5	162.6	161.5
37.5°	313.3	282.8	264.0	246.3	166.1	147.3	141.3	140.2
40°	270.9	243.8	226.2	212.1	146.1	130.8	125.0	123.7
42.5°	231.0	207.4	192.0	180.3	127.3	115.4	110.8	109.6
45°	190.8	172.0	160.3	150.9	110.8	98.9	97.7	97.7
47.5°	154.4	139.0	130.8	125.0	94.3	84.9	83.7	84.9
50°	123.7	113.1	107.2	102.5	80.1	71.8	68.3	68.3
52.5°	97.7	90.8	87.2	83.7	66.0	57.8	53.0	51.8
55°	77.8	71.8	69.5	67.2	51.8	42.4	37.6	36.5
57.5°	61.2	56.6	54.2	51.8	39.0	29.4	24.8	23.6
60°	45.9	42.4	40.1	39.0	27.1	17.7	14.2	13.0
62.5°	33.0	30.7	28.2	27.1	16.5	9.4	5.9	4.8
65°	20.0	20.0	17.7	16.5	8.3	3.5	2.3	1.2
67.5°	11.7	10.6	9.4	9.4	3.5	2.3	1.2	1.2
70°	5.9	5.9	4.8	4.8	2.3	1.2	1.2	1.2
72.5°	3.5	3.5	3.5	2.3	2.3	1.2	1.2	1.2
75°	2.3	2.3	2.3	2.3	2.3	1.2	1.2	1.2
77.5°	2.3	2.3	2.3	2.3	2.3	1.2	1.2	0.0
80°	2.3	2.3	2.3	2.3	2.3	1.2	1.2	0.0
82.5°	2.3	2.3	2.3	2.3	2.3	1.2	1.2	1.2
85°	2.3	2.3	2.3	2.3	2.3	1.2	1.2	0.0
87.5°	2.3	2.3	2.3	2.3	2.3	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)